

# Conductivity assembly Dipfit CLA111

## Immersion assembly for water, wastewater and utilities



### Benefits:

- Easy installation and removal of sensor thanks to bayonet lock mounting method
- Flexible immersion depth thanks to adjustable flange
- Made of environmentally-compatible polypropylene material
- Reduced condensation of water due to breathable Goretex® filter

### Specs at a glance

- **Process temperature** Max. 80 °C (176 °F)
- **Process pressure** Max. 4 bar at 20 °C (Max. 58 psi at 68 °F)

**Field of application:** The Dipfit CLA111 immersion assembly is designed for application in open basins, channels and tanks. It is suitable for conductive and toroidal sensors that can be easily mounted and removed via the bayonet lock. The adjustable flange gives you the required flexibility for universal use. Dipfit is the time and cost-effective solution for standard water and wastewater treatment.

More information and current pricing:

[www.de.endress.com/CLA111](http://www.de.endress.com/CLA111)

## Features and specifications

### Conductivity

#### Measuring principle

Conductive

#### Application

Water, waste water, process

#### Characteristic

Open and closed tank, open channel

## Conductivity

### Design

For use with G1" or G3/4" thread-bayonet-type holder system  
Variable holder length  
Process connection with fixed or sliding flange

---

### Material

Sensor holder: PP-GF 20  
Immersion tube: PP

---

### Dimension

Length: 500 to 3000 mm (19.7 to 118 inch), special lengths on request

---

### Process temperature

Max. 80 °C (176 °F)

---

### Process pressure

Max. 4 bar at 20 °C  
(Max. 58 psi at 68 °F)

---

More information [www.de.endress.com/CLA111](http://www.de.endress.com/CLA111)