

# Combined pH/ORP sensor Memosens CPS76E

## Memosens 2.0 combined electrode for chemical processes and poisoning media



More information and current pricing:

[www.de.endress.com/CPS76E](http://www.de.endress.com/CPS76E)

### Benefits:

- Memosens 2.0 offers extended storage of calibration and process data, enabling better trend identification and providing a future-proof basis for predictive maintenance and enhanced IIoT services.
- Simultaneous measurement of pH, ORP and rH values (in rH mode) provides a better process overview and allows for a tighter process control.
- Its optional pressurized reference ensures reliable measurement in blocking media, such as dispersions.
- Unique ion trap prevents poisoning of the electrode's junction and reference ensuring a long sensor lifetime.
- Flexible installation thanks to optional upside-down mounting.
- Maximum process safety through non-contact, inductive signal transmission.
- Reduced operating costs thanks to minimized process downtime and extended sensor lifetime.

### Specs at a glance

- **Measurement range** ORP: -1 500 to 1 500 mV Application B ■ pH: 0 to 14 Application H ■ pH: 0 to 12
- **Process temperature** Application B and H: 0 to 140 °C (32 to 284 °F) Version TB: 0 to 140 °C (32 to 284 °F) Version TU, TP (pressurized reference): 0 to 140 °C (32 to 284 °F) (140 °C (284 °F) for sterilization only) maximum 100 °C (212 °F) in continuous operation due to increasing pressure drop at T > 100 °C (212 °F)
- **Process pressure** Application B: 0.8 to 14 bar (11.6 to 203 psi) absolute Application H: 0.8 to 7 bar (11.6 to 101,5 psi) absolute

**Field of application:** Memosens CPS76E is the heavy-duty specialist for simultaneous pH and ORP measurement. Its unique, contamination-resistant reference guarantees stable measurement in polluted, poisoning media and in media with low conductivity. Thanks to Memosens 2.0 digital technology, CPS76E combines maximum process integrity with simple operation. It resists moisture, enables lab calibration and offers extended storage of calibration and process data providing the perfect basis for predictive maintenance.

## Features and specifications

### ORP / Redox

#### Measuring principle

Sensor ORP / Redox

#### Application

Process technology and monitoring of processes with:

- Rapidly changing pH values
- High levels of electrode poisons, such as H<sub>2</sub>S

#### Characteristic

Digital pH/ORP electrode for chemical process with an ion trap for poison-resistant reference

#### Measurement range

ORP: -1 500 to 1 500 mV

Application B

- pH: 0 to 14

Application H

- pH: 0 to 12

#### Measuring principle

Gel compact electrode with ceramic junction and ion trap for simultaneous measurement of pH, ORP and rH value (in rH mode)

#### Design

All shaft lengths with temperature sensor

Advanced gel technology

## ORP / Redox

**Material**

Sensor shaft: Glass to suit process  
pH membrane glass: Type B, Type N  
Metal lead: Ag/AgCl  
Open aperture: Ceramic junction,  
zirconium dioxide  
ORP measuring element: Platinum  
O-ring: FKM  
Process coupling: PPS fiber-glass reinforced  
Nameplate: Ceramic metal oxide

---

**Dimension**

Diameter: 12 mm (0.46 inch)  
Shaft lengths: 120, 225, 360 and 425 mm  
(4.68, 8.77, 14.04 and 16,57 inch)

---

**Process temperature**

Application B and H:  
0 to 140 °C (32 to 284 °F)  
Version TB:  
0 to 140 °C (32 to 284 °F)  
Version TU, TP (pressurized reference):  
0 to 140 °C (32 to 284 °F) (140 °C (284 °F) for sterilization only)  
maximum 100 °C (212 °F) in continuous operation due to increasing  
pressure drop at T > 100 °C (212 °F)

---

**Process pressure**

Application B: 0.8 to 14 bar (11.6 to 203 psi) absolute  
Application H: 0.8 to 7 bar (11.6 to 101,5 psi) absolute

---

**Temperature sensor**

NTC 30k

---

**Ex certification**

With ATEX, IECEx, CSA C/US, NEPSI, Japan Ex and INMETRO approvals  
for use in  
hazardous areas Zone 0, Zone 1 and Zone 2

---

## ORP / Redox

**Connection**

Inductive, digital connection head with Memosens 2.0 technology

---

**Ingres protection**

IP68

---

## pH

**Measuring principle**

Potentiometric

---

**Application**

Process technology and monitoring of processes with:

- Rapidly changing pH values
  - High levels of electrode poisons, such as H<sub>2</sub>S
- 

**Characteristic**

Digital pH/ORP electrode for chemical process with an ion trap for poison-resistant reference

---

**Measurement range**

ORP: -1 500 to 1 500 mV

Application B

- pH: 0 to 14

Application H

- pH: 0 to 12
- 

**Measuring principle**

Gel compact electrode with ceramic junction and ion trap for simultaneous measurement of pH, ORP and rH value (in rH mode)

---

**Design**

All shaft lengths with temperature sensor

Advanced gel technology

---

## pH

**Material**

Sensor shaft: Glass to suit process  
pH membrane glass: Type B, Type N  
Metal lead: Ag/AgCl  
Open aperture: Ceramic junction,  
zirconium dioxide  
ORP measuring element: Platinum  
O-ring: FKM  
Process coupling: PPS fiber-glass reinforced  
Nameplate: Ceramic metal oxide

---

**Dimension**

Diameter: 12 mm (0.46 inch)  
Shaft lengths: 120, 225, 360 and 425 mm  
(4.68, 8.77, 14.04 and 16,57 inch)

---

**Process temperature**

Application B and H:  
0 to 140 °C (32 to 284 °F)  
Version TB:  
0 to 140 °C (32 to 284 °F)  
Version TU, TP (pressurized reference):  
0 to 140 °C (32 to 284 °F) (140 °C (284 °F) for sterilization only)  
maximum 100 °C (212 °F) in continuous operation due to increasing  
pressure drop at T > 100 °C (212 °F)

---

**Process pressure**

Application B: 0.8 to 14 bar (11.6 to 203 psi) absolute  
Application H: 0.8 to 7 bar (11.6 to 101,5 psi) absolute

---

**Temperature sensor**

NTC 30k

---

**Ex certification**

With ATEX, IECEx, CSA C/US, NEPSI, Japan Ex and INMETRO approvals  
for use in  
hazardous areas Zone 0, Zone 1 and Zone 2

---

pH

**Connection**

Inductive, digital connection head with Memosens 2.0 technology

---

**Ingres protection**

IP68

---

More information [www.de.endress.com/CPS76E](http://www.de.endress.com/CPS76E)