

Proline Promag W 300 electromagnetic flowmeter

Specialist for demanding water & wastewater applications with compact, easily accessible transmitter



Fordele:

- Reliable measurement at constant accuracy with 0 x DN inlet run and no pressure loss
- Flexible engineering – sensor with welded or lap-joint process connections
- Long-term operation – robust and completely welded sensor
- Improved plant availability – sensor compliant with industry-specific requirements
- Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses
- Reduced complexity and variety – freely configurable I/O functionality
- Integrated verification – Heartbeat Technology

Yderligere oplysninger og aktuel pris::

www.dk.endress.com/5W3B

Oversigt over specifikationer

- **Max. measurement error** Volume flow (standard): $\pm 0.5\%$ o.r. ± 1 mm/s (0.04 in/s) Volume flow (option): $\pm 0.2\%$ o.r. ± 2 mm/s (0.08 in/s), Flat Spec
- **Measuring range** 0.5 m³/h to 263000 m³/h (2.5gal/min to 1665 Mgal/d)
- **Medium temperature range** Liner material hard rubber: 0 to +80 °C (+32 to +176 °F) Liner material polyurethane: -20 to +50 °C (-4 to +122 °F) Liner material PTFE: -20 to +90 °C (-4 to +194 °F)
- **Max. process pressure** PN 40, Class 300, 20K
- **Wetted materials** Liner: Polyurethane; Hard rubber, PTFE
Electrodes: 1.4435 (316L); Alloy C22, 2.4602 (UNS N06022); Tantalum

Anvendelsesområde: The premium device for water and wastewater measurement Promag W 300 was designed for reliable use in hazardous areas and under harsh conditions. Its compact transmitter offers high flexibility in terms of operation and system integration: access from one side, remote display and improved connectivity options. Heartbeat Technology ensures measurement reliability and compliant verification.

Funktioner og specifikationer

Liquids

Measuring principle

Electromagnetic

Product headline

Specialist for demanding water and wastewater applications with a compact, easily accessible transmitter.

Reliable measurement at constant accuracy with 0 x DN inlet run and no pressure loss.

Dedicated to the measurement of industrial or municipal water and wastewater .

Sensor features

Flexible engineering – sensor with fixed or lap-joint process connections.

Long-term operation – robust and completely welded sensor. Improved plant availability – sensor compliant with industry-specific requirements.

International drinking water approvals.

Transmitter features

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology.

Compact dual-compartment housing with up to 3 I/Os. Backlit display with touch control and WLAN access. Remote display available.

Nominal diameter range

DN 25 to 3000(1 to 120")

Liquids

Wetted materials

Liner: Polyurethane; Hard rubber, PTFE

Electrodes: 1.4435 (316L); Alloy C22, 2.4602 (UNS N06022); Tantalum

Measured variables

Volume flow, conductivity, mass flow

Max. measurement error

Volume flow (standard): ± 0.5 % o.r. ± 1 mm/s (0.04 in/s)

Volume flow (option): ± 0.2 % o.r. ± 2 mm/s (0.08 in/s), Flat Spec

Measuring range

0.5 m³/h to 263000 m³/h (2.5gal/min to 1665 Mgal/d)

Max. process pressure

PN 40, Class 300, 20K

Medium temperature range

Liner material hard rubber: 0 to +80 °C (+32 to +176 °F)

Liner material polyurethane: -20 to +50 °C (-4 to +122 °F)

Liner material PTFE: -20 to +90 °C (-4 to +194 °F)

Ambient temperature range

Flange material carbon steel: -10 to +60 °C (+14 to +140 °F)

Flange material stainless steel: -40 to +60 °C (-40 to +140 °F)

Sensor housing material

DN 25 to 300 (1 to 12"): AlSi10Mg, coated

DN 25 to 2400 (1 to 90"): Carbon steel with protective varnish

Sensor connection housing (standard): AlSi10Mg, coated

Sensor connection housing (option): Polycarbonate; 1.4409 (CF3M) similar to 316L

Transmitter housing material

AlSi10Mg, coated; 1.4409 (CF3M) similar to 316L; stainless steel for hygienic transmitter design

Liquids

Display/Operation

4-line backlit display with touch control (operation from outside)
Configuration via local display and operating tools possible
Remote display available

Outputs

3 outputs:
4-20 mA HART (active/passive)
4-20 mA WirelessHART
4-20 mA (active/passive)
Pulse/frequency/switch output (active/passive)
Double pulse output (active/passive)
Relay output

Inputs

Status input 4-20 mA input

Digital communication

HART, PROFIBUS DP, PROFIBUS PA, FOUNDATION Fieldbus, Modbus
RS485, Profinet, Ethernet/IP, OPC-UA

Power supply

DC 24 V
AC 100 to 230 V
AC 100 to 230 V / DC 24 V (non-hazardous area)

Hazardous area approvals

ATEX, IECEx, cCSAus, Nepsi, INMETRO, UK Ex

Product safety

CE, C-tick, EAC marking

Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

Liquids

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025), NAMUR

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

Marine approvals and certificates

LR approval, DNV GL approval, ABS approval, BV approval

Pressure approvals and certificates

CRN, PED

Material certificates

3.1 material

Hygienic approvals and certificates

ACS, KTW/W270, NSF 61, WRAS BS 6920

Yderligere information www.dk.endress.com/5W3B