

# Dosimag electromagnetic flowmeter

Flowmeter with hygienic design, highest repeatability and an ultra-compact sensor



Yderligere oplysninger og aktuel pris::

[www.dk.endress.com/5BH](http://www.dk.endress.com/5BH)

## Fordele:

- High process safety – high measuring accuracy and repeatability in shortest filling time
- Energy-saving flow measurement – no pressure loss due to cross-section constriction
- Maintenance-free – no moving parts
- Versatile and time-saving wiring – plug connector
- Industry-optimized – ultra-compact design
- For hygiene requirements – stainless steel housing

## Oversigt over specifikationer

- **Max. measurement error**  $\pm 0.25\%$  o.r.  $\pm 1$  to 4 m/s (3.3 to 13 ft/s)  $\pm 0.5\%$  o.r.  $\pm 1$  mm/s (0.04 in/s)  $\pm 5\%$  o.r.
- **Measuring range** 0.14 to 1.66 l/s (0.035 to 0.44 gal/s)
- **Medium temperature range** Seal material EPDM:  $-20$  to  $+130\text{ }^{\circ}\text{C}$  ( $-4$  to  $+266\text{ }^{\circ}\text{F}$ ) Seal material Silicone:  $-20$  to  $+130\text{ }^{\circ}\text{C}$  ( $-4$  to  $+266\text{ }^{\circ}\text{F}$ ) Seal material Viton:  $0$  to  $+150\text{ }^{\circ}\text{C}$  ( $+32$  to  $+302\text{ }^{\circ}\text{F}$ )
- **Max. process pressure** PN 16
- **Wetted materials** Liner: PFA Electrodes: 1.4435 (316L); Alloy C22, 2.4602 (UNS N06022), Tantalum, Platinum

**Anvendelsesområde:** Dosimag is specially designed for filling and bottling applications of conductive liquids. It measures volume directly. Designed for applications where space is a premium, Dosimag will be the preferred choice for system integrators, skid builders and equipment manufacturers.

## Funktioner og specifikationer

## Liquids

### Measuring principle

Electromagnetic

---

### Product headline

Flowmeter with hygienic design, highest repeatability and an ultra-compact sensor.

For demanding dosing and filling applications.

---

### Sensor features

High process safety – high measuring accuracy and repeatability in shortest filling time. Energy-saving flow measurement – no pressure loss due to cross section constriction. Maintenance-free – no moving parts. Wetted materials CIP, SIP cleanable. Nominal diameter: DN 4 to 25 ( $\frac{1}{8}$  to 1"). Measuring device conform to FDA.

---

### Transmitter features

Versatile and time-saving wiring – plug connector. Industry-optimized – ultra-compact design. For hygienic requirements – stainless steel housing.

Pulse/frequency/switch output, Modbus RS485. Custody transfer approvals (MID, NTEP). Excellent, easily cleanable transmitter.

---

### Nominal diameter range

DN 4 ( $\frac{5}{32}$ "), 8 ( $\frac{5}{16}$ "), 15 ( $\frac{1}{2}$ "), 25 (1")

---

### Wetted materials

Liner: PFA

Electrodes: 1.4435 (316L); Alloy C22, 2.4602 (UNS N06022),

Tantalum,

Platinum

---

### Measured variables

Volume flow

---

### Max. measurement error

$\pm 0.25$  % o.r.  $\pm 1$  to 4 m/s (3.3 to 13 ft/s)

$\pm 0.5$  % o.r.  $\pm 1$  mm/s (0.04 in/s)

$\pm 5$  % o.r.

---

---

## Liquids

**Measuring range**

0.14 to 1.66 l/s (0.035 to 0.44 gal/s)

---

**Max. process pressure**

PN 16

---

**Medium temperature range**

Seal material EPDM: -20 to +130 °C (-4 to +266 °F)

Seal material Silicone: -20 to +130 °C (-4 to +266 °F)

Seal material Viton: 0 to +150 °C (+32 to +302 °F)

---

**Ambient temperature range**

-40 to +60 °C (-40 to +140 °F)

---

**Sensor housing material**

1.4308 (304)

---

**Transmitter housing material**

1.4308 (304)

---

**Degree of protection**

IP66/67, type 4X enclosure

---

**Display/Operation**

No local Operation

Configuration via operating tools possible

---

**Outputs**

Pulse/frequency/switch output (passive)

---

**Inputs**

None

---

**Digital communication**

Modbus RS485

---

**Power supply**

DC 20 to 30 V

---

## Liquids

### **Hazardous area approvals**

ATEX, IECEx, cCSAus

---

### **Product safety**

CE

---

### **Metrological approvals and certificates**

Calibration performed on accredited calibration facilities (acc.to ISO/IEC 17025)

NTEP

---

### **Material certificates**

3.1 material

---

### **Hygienic approvals and certificates**

Sanitary approval: 3-A, EHEDG, seals acc. to FDA (except EPDM)

---

Yderligere information [www.dk.endress.com/5BH](http://www.dk.endress.com/5BH)