

Promag 53W



Yderligere oplysninger og aktuel pris::

www.dk.endress.com/53W

Fordele:

- Secure, reliable long-term operation – robust and completely welded sensor
- Energy-saving flow measurement – no pressure loss due to cross-section constriction
- Maintenance-free – no moving parts
- Quality – software for filling and dosing, density, electrode cleaning and also advanced diagnostics
- Easy calculation – bidirectional totalizers
- Automatic recovery of data for servicing

Oversigt over specifikationer

- **Max. measurement error** $\pm 0.2\%$
- **Measuring range** 0...110'000 m³/h
- **Medium temperature range** -20...+80°C (-4...+176°F)
- **Max. process pressure** PN6...40 CI 150...300 JIS 10...20K AWWA Class D AS 2129 Table E AS 4087 PN16

Anvendelsesområde: Promag W is the specialized sensor for all applications in the water industry. Combined with the Promag 53 transmitter with touch control, 4-line display and extended functionality like software options for filling and dosing, electrode cleaning or advanced diagnostics, Promag 53W offers highest accuracy in the most complex and demanding measuring tasks. Promag 53W is available as compact or remote version.

Funktioner og specifikationer

Liquids

Measuring principle

Electromagnetic

Liquids

Product headline

std_productprofile_product_usp_34667_1508941375.

The specialist in the water and wastewater industry for the most demanding applications.

Sensor features

Secure, reliable long-term operation – robust and completely welded sensor saving flow measurement – no pressure loss due to cross section constrict
Maintenance-free – no moving parts.

International drinking water approvals. Degree of protection IP68 (Type 6 enclosure).

Transmitter features

std_productprofile_product_benefits_34656_1508940491.

std_productprofile_product_benefits_34658_1508940614.

std_productprofile_product_benefits_34657_1508940613.

std_successorproducts_product_differentiating_tech_features_35324_1

std_successorproducts_product_differentiating_tech_features_35325_1

std_successorproducts_product_differentiating_tech_features_35326_1

Nominal diameter range

DN 25...2000

1"...78"

Max. measurement error

±0.2%

Measuring range

0...110'000 m³/h

Max. process pressure

PN6...40

CI 150...300

JIS 10...20K

AWWA Class D

AS 2129 Table E

AS 4087 PN16

Liquids

Medium temperature range

-20...+80°C
(-4...+176°F)

Ambient temperature range

-20...+60°C
-40...+60°C (optional)

Degree of protection

IP 67 (NEMA 4x)
IP 68 (Nema 6P)

Display/Operation

Four line display with backlit
Touch control

Outputs

4...20 mA
Pulse/Frequency (active/passive)
Relays
Status

Inputs

Status
Current input

Digital communication

HART
PROFIBUS PA
Profibus DP
FOUNDATION Fieldbus

Hazardous area approvals

ATEX, FM, CSA

Product safety

CE, C-tick, EAC marking

Yderligere information www.dk.endress.com/53W