

# Proline Promass H 100 Coriolis flowmeter

## The chemically resistant single-tube flowmeter with an ultra-compact transmitter



More information and current pricing:

[www.dk.endress.com/8H1B](http://www.dk.endress.com/8H1B)

### Benefits:

- Maximum safety for chemically aggressive fluids – corrosion-resistant wetted parts
- Fewer process measuring points – multivariable measurement (flow, density, temperature)
- Space-saving installation – no in/outlet run needs
- Space-saving transmitter – full functionality on the smallest footprint
- Time-saving local operation without additional software and hardware – integrated web server
- Integrated verification – Heartbeat Technology

### Specs at a glance

- **Max. measurement error** Mass flow (liquid):  $\pm 0.1\%$  Volume flow (liquid):  $\pm 0.1\%$  Mass flow (gas, Tantalum only):  $\pm 0.5\%$  Density (liquid):  $\pm 0.0005 \text{ g/cm}^3$
- **Measuring range** 0 to 70 000 kg/h (0 to 2570 lb/min)
- **Medium temperature range** Tantalum:  $-50$  to  $+150$  °C ( $-58$  to  $+302$  °F) Zirconium:  $-50$  to  $+205$  °C ( $-58$  to  $+401$  °F)
- **Max. process pressure** PN 40, Class 300, 20K
- **Wetted materials** Measuring tube: Tantalum 2.5W; 702 (UNS R60702) Connection: Tantalum; 702 (UNS R60702)

**Field of application:** The chemically resistant single-tube design of the Promass H is destined for applications requiring highest corrosion resistance. Combined with the smallest transmitter housing available today it delivers full performance on the smallest footprint. Designed for applications where space is a premium, Promass H 100 will be the preferred choice for system integrators, skid builders and equipment manufacturers.

---

## Features and specifications

---

### Liquids

**Measuring principle**

Coriolis

---

**Product headline**

Chemically resistant single-tube flowmeter with an ultra-compact transmitter.

Measuring highly accurately liquids and gases in applications requiring highest corrosion resistance.

---

**Sensor features**

Maximum safety for chemically aggressive fluids – corrosion-resistant wetted parts. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space-saving installation – no in-/outlet run needs.

Measuring tube made of Tantalum, Zirconium. Nominal diameter: DN 8 to 50 ( $\frac{3}{8}$  to 2"). Medium temperature up to +205 °C (+401 °F).

---

**Transmitter features**

Space-saving transmitter – full functionality on the smallest footprint. Time-saving local operation without additional software and hardware – integrated web server. Integrated verification – Heartbeat Technology. Robust, ultra-compact transmitter housing. Highest degree of protection: IP69. Local display available.

---

**Nominal diameter range**

DN 8 to 50 ( $\frac{3}{8}$  to 2")

---

**Wetted materials**

Measuring tube: Tantalum 2.5W; 702 (UNS R60702)

Connection: Tantalum; 702 (UNS R60702)

---

**Measured variables**

Mass flow, density, temperature, volume flow, corrected volume flow, reference density, concentration

---

## Liquids

**Max. measurement error**

Mass flow (liquid):  $\pm 0.1\%$

Volume flow (liquid):  $\pm 0.1\%$

Mass flow (gas, Tantalum only):  $\pm 0.5\%$

Density (liquid):  $\pm 0.0005\text{ g/cm}^3$

---

**Measuring range**

0 to 70 000 kg/h (0 to 2570 lb/min)

---

**Max. process pressure**

PN 40, Class 300, 20K

---

**Medium temperature range**

Tantalum:  $-50$  to  $+150\text{ }^\circ\text{C}$  ( $-58$  to  $+302\text{ }^\circ\text{F}$ )

Zirconium:  $-50$  to  $+205\text{ }^\circ\text{C}$  ( $-58$  to  $+401\text{ }^\circ\text{F}$ )

---

**Ambient temperature range**

Standard:  $-40$  to  $+60\text{ }^\circ\text{C}$  ( $-40$  to  $+140\text{ }^\circ\text{F}$ )

Option:  $-50$  to  $+60\text{ }^\circ\text{C}$  ( $-58$  to  $+140\text{ }^\circ\text{F}$ )

---

**Sensor housing material**

1.4301 (304), corrosion resistant

---

**Transmitter housing material**

Compact: AlSi10Mg, coated

Compact/ultra-compact: 1.4301 (304)

---

**Degree of protection**

Standard: IP66/67, type 4X enclosure

Option: IP69

---

**Display/Operation**

4-line backlit display available (no local operation)

Configuration via web browser and operating tools possible

---

**Outputs**

4-20 mA HART (active)

Pulse/frequency/switch output (passive)

---

---

## Liquids

**Inputs**

None

---

**Digital communication**

HART, Modbus RS485, EtherNet/IP, PROFIBUS DP, PROFINET

---

**Power supply**

DC 20 to 30 V

---

**Hazardous area approvals**

ATEX, IECEx, cCSAus, INMETRO, NEPSI, EAC

---

**Product safety**

CE, C-Tick, EAC marking

---

**Metrological approvals and certificates**

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for traceable verification according to ISO 9001:2008 – Section 7.6a (TÜV SÜD attestation)

---

**Pressure approvals and certificates**

PED, CRN

---

**Material certificates**

3.1 material

---

## Gas

**Measuring principle**

Coriolis

---

**Product headline**

Chemically resistant single-tube flowmeter with an ultra-compact transmitter.

Measuring highly accurately liquids and gases in applications requiring highest corrosion resistance.

---

## Gas

**Sensor features**

Maximum safety for chemically aggressive fluids – corrosion-resistant wetted parts. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space-saving installation – no in-/outlet run needs.

Measuring tube made of Tantalum, Zirconium. Nominal diameter: DN 8 to 50 ( $\frac{3}{8}$  to 2"). Medium temperature up to +205 °C (+401 °F).

**Transmitter features**

Space-saving transmitter – full functionality on the smallest footprint. Time-saving local operation without additional software and hardware – integrated web server. Integrated verification – Heartbeat Technology. Robust, ultra-compact transmitter housing. Highest degree of protection: IP69. Local display available.

**Nominal diameter range**

DN 8 to 50 ( $\frac{3}{8}$  to 2")

**Wetted materials**

Measuring tube: Tantalum 2.5W; 702 (UNS R60702)

Connection: Tantalum; 702 (UNS R60702)

**Measured variables**

Mass flow, density, temperature, volume flow, corrected volume flow, reference density, concentration

**Max. measurement error**

Mass flow (liquid):  $\pm 0.1$  %

Volume flow (liquid):  $\pm 0.1$  %

Mass flow (gas, Tantalum only):  $\pm 0.5$  %

Density (liquid):  $\pm 0.0005$  g/cm<sup>3</sup>

**Measuring range**

0 to 70 000 kg/h (0 to 2570 lb/min)

**Max. process pressure**

PN 40, Class 300, 20K

## Gas

**Medium temperature range**

Tantalum: -50 to +150 °C (-58 to +302 °F)

Zirconium: -50 to +205 °C (-58 to +401 °F)

**Ambient temperature range**

Standard: -40 to +60 °C (-40 to +140 °F)

Option: -50 to +60 °C (-58 to +140 °F)

**Sensor housing material**

1.4301 (304), corrosion resistant

**Transmitter housing material**

Compact: AlSi10Mg, coated

Compact/ultra-compact: 1.4301 (304)

**Degree of protection**

Standard: IP66/67, type 4X enclosure

Option: IP69

**Display/Operation**

4-line backlit display available (no local operation)

Configuration via web browser and operating tools possible

**Outputs**

4-20 mA HART (active)

Pulse/frequency/switch output (passive)

**Inputs**

None

**Digital communication**

HART, Modbus RS485, EtherNet/IP, PROFIBUS DP, PROFINET

**Power supply**

DC 20 to 30 V

**Hazardous area approvals**

ATEX, IECEx, cCSAus, INMETRO, NEPSI

---

**Gas****Product safety**

CE, C-Tick, EAC marking

---

**Metrological approvals and certificates**

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025), NAMUR

Heartbeat Technology complies with the requirements for traceable verification according to ISO 9001:2008 – Section 7.6a (TÜV SÜD attestation)

---

**Pressure approvals and certificates**

PED, CRN

---

**Material certificates**

3.1 material

---

**Density/Concentration****Measuring principle**

Coriolis

---

**Product headline**

Chemically resistant single-tube flowmeter with an ultra-compact transmitter.

Measuring highly accurately liquids and gases in applications requiring highest corrosion resistance.

---

**Sensor features**

Maximum safety for chemically aggressive fluids – corrosion-resistant wetted parts. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space-saving installation – no in-/outlet run needs.

Measuring tube made of Tantalum, Zirconium. Nominal diameter: DN 8 to 50 ( $\frac{3}{8}$  to 2"). Medium temperature up to +205 °C (+401 °F).

---

## Density/Concentration

### Transmitter features

Space-saving transmitter – full functionality on the smallest footprint.  
Time-saving local operation without additional software and hardware – integrated web server. Integrated verification – Heartbeat Technology.  
Robust, ultra-compact transmitter housing. Highest degree of protection: IP69. Local display available.

---

### Nominal diameter range

DN 8 to 50 ( $\frac{3}{8}$  to 2")

---

### Wetted materials

Measuring tube: Tantalum 2.5W; 702 (UNS R60702)

Connection: Tantalum; 702 (UNS R60702)

---

### Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow, reference density, concentration

---

### Max. measurement error

Mass flow (liquid):  $\pm 0.1$  %

Volume flow (liquid):  $\pm 0.1$  %

Mass flow (gas, Tantalum only):  $\pm 0.5$  %

Density (liquid):  $\pm 0.0005$  g/cm<sup>3</sup>

---

### Measuring range

0 to 70 000 kg/h (0 to 2570 lb/min)

---

### Max. process pressure

PN 40, Class 300, 20K

---

### Medium temperature range

Tantalum:  $-50$  to  $+150$  °C ( $-58$  to  $+302$  °F)

Zirconium:  $-50$  to  $+205$  °C ( $-58$  to  $+401$  °F)

---

### Ambient temperature range

Standard:  $-40$  to  $+60$  °C ( $-40$  to  $+140$  °F)

Option:  $-50$  to  $+60$  °C ( $-58$  to  $+140$  °F)

---



---

**Density/Concentration****Sensor housing material**1.4301 (304), corrosion resistant

---

**Transmitter housing material**

Compact: AlSi10Mg, coated

Compact/ultra-compact: 1.4301 (304)

---

**Degree of protection**

Standard: IP66/67, type 4X enclosure

Option: IP69

---

**Display/Operation**

4-line backlit display available (no local operation)

Configuration via web browser and operating tools possible

---

**Outputs**

4-20 mA HART (active)

Pulse/frequency/switch output (passive)

---

**Inputs**None

---

**Digital communication**HART, Modbus RS485, EtherNet/IP, PROFIBUS DP, PROFINET

---

**Power supply**DC 20 to 30 V

---

**Hazardous area approvals**ATEX, IECEx, cCSAus, INMETRO, NEPSI, EAC

---

**Product safety**CE, C-Tick, EAC marking

---

## Density/Concentration

### **Metrological approvals and certificates**

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for traceable verification according to ISO 9001:2008 – Section 7.6a (TÜV SÜD attestation)

---

### **Pressure approvals and certificates**

PED, CRN

---

### **Material certificates**

3.1 material

---

More information [www.dk.endress.com/8H1B](http://www.dk.endress.com/8H1B)