

# TA565

## Barstock thermowell

Made of drilled barstock material. Mainly used in heavy duty or general purpose applications.



More information and current pricing:

[www.easc.endress.com/TA565](http://www.easc.endress.com/TA565)

### Benefits:

- The extension and the immersion length as well as the bar dimensions can be chosen according to process requirements
- A wide choice of standard diameters and materials is available; other versions can be ordered according to specification
- Different grades of surface finishing are also available
- The process connection is threaded. The thermowell stem shape can be straight or conical

### Specs at a glance

- **Max. process pressure (static)** 500 bar (7252 psi)
- **Maximum standard immersion length** 150 mm (5,91")
- **Max. immersion length on request** 300 mm (11,81")

**Field of application:** Due to the challenging process conditions by heavy duty applications the load capacity of a thermowell must be calculated exactly. Dye penetration tests, ultrasound test, helium leakage test, pressure endurance test as well as various, non-destructive material tests prove the quality of materials and processing.

## Features and specifications

Thermowell

### Measuring principle

Bar stock Thermowell

## Thermowell

**Characteristic / Application**

metric style  
threaded process connection  
hexagonal extension

---

**Head connection**

internal thread:  
1/2" NPT

---

**Maximum standard immersion****length**

150 mm (5,91")

---

**Max. immersion length on request**

300 mm (11,81")

---

**Process connection**

Thread 1" NPT

---

**Thermowell root diameter**

19,5 mm (0,78")  
20 mm (0,79")  
25 mm (0,98")  
27 mm (1,06")

---

**Medium contact material**

1.4401 (316)  
1.4404 (316L)  
1.4571 (316Ti)

---

**Wetted part finishing (Ra)**

< 0,8  $\mu\text{m}$  (31,50  $\mu\text{in}$ )  
< 1,6  $\mu\text{m}$  (63,00  $\mu\text{in}$ )

---

**Tip shape**

straight  
conical

---

Thermowell

**Temperature range**

-200...700 °C (-328...1.292 °F)

---

**Max. process pressure (static)**

500 bar (7252 psi)

---

**Max. process pressure at 400 °C**

300 bar (4351 psi)

---

More information [www.easc.endress.com/TA565](http://www.easc.endress.com/TA565)