

Raman electro-optical (EO) fiber optic cables

Innovative Raman fiber optics designed for maximum laser safety and easy installation



Дополнительная информация и актуальные цен:

www.easc.endress.com/KFOC1

Преимущества:

- Simple plug and lock design
- Integrated safety interlock to prevent laser exposure
- Certified for hazardous area environments
- Indoor/outdoor rated cable - flame retardant, fungus resistant, internal strength member
- Available in different fiber lengths to meet your installation requirements

Краткие характеристики

- **Температура** Диапазон: -40–70 °C

Назначение: Our Raman embedded analyzers and probes are connected by electro-optical (EO) fiber optic cables with integrated low-voltage electrical interlock and optical fiber cable components bundled into one CSA-rated assembly. Rated for indoor/outdoor use, the EO connector is designed to protect the connection from external influences, avoid breakage, and ensure a secure connection. EO fiber cables are available in several size lengths with extension cables to simplify installation and remote analysis.

Характеристики и спецификации

Принцип измерения

Рамановская спектроскопия

Температура

Диапазон: -40–70 °C

Оптоволоконный кабель

Длина: 5 м (по запросу возможны варианты)

Радиус изгиба: 152,4 мм

Дополнительная информация www.easc.endress.com/KFOC1