

# TR62

## Explosion-proof Pt100 Thermometer

Safe monitoring of process temperatures in challenging applications e. g. in the Oil & Gas industry



More information and current pricing:

[www.endress.com/TR62](http://www.endress.com/TR62)

### Benefits:

- Types of protection for use in hazardous locations: Intrinsic safety (Ex i.a.), flameproof (Ex d), non-sparking (Ex nA)
- High degree of flexibility thanks to modular design with standard terminal heads as per DIN EN 50446 and customer-specific immersion lengths
- High degree of insert compatibility and design as per DIN 43772
- Extension neck, nipple union version, to protect the head transmitter from overheating

### Specs at a glance

- **Accuracy** class A acc. to IEC 60751 class AA acc. to IEC 60751
- **Response time** depending on configuration  $t_{50} = 4\text{ s}$   $t_{90} = 8\text{ s}$
- **Max. process pressure (static)** at 20 °C: 500 bar (7.252 psi)
- **Operating temperature range** PT100 TF StrongSens: -50 °C ...500 °C (-58 °F ...932 °F) PT100 WW: -200 °C ...600 °C (-328 °F ...1.112 °F) PT100 TF: -50 °C ...400 °C (-58 °F ...752 °F)
- **Max. immersion length on request** up to 30.000,00 mm (1.181,10")

**Field of application:** The robust thermometer is designed for use in demanding and safety relevant applications e.g. in the Chemical, Oil & Gas, Energy industry. The sensor is designed for use in a separate thermowell. An optional head transmitter with all common communication protocols makes the device ready to use with enhanced measurement accuracy and reliability compared to directly wired sensors.

The modular design with a variety of options can be adapted to the measurement task. Flexible configuration possible.

## Features and specifications

### Thermometer

**Measuring principle**

Resistance Temperature Detector

**Characteristic / Application**

US style metrical

modular temperature assembly

for heavy duty applications

suitable for hazardous areas

with neck

to be used with thermowell

**Thermowell / protection tube**

to be used with thermowell

**Insert / probe**

mineral insulated (MI), flexible

**Outer diameter protection tube / Insert**

Insert Diameter

3,0 mm (0,12")

6,0 mm (0,24")

**Max. immersion length on request**

up to 30.000,00 mm (1.181,10")

## Thermometer

**Material protection tube/ thermowell**

Not defined

**Optional coating**

Not defined

**Process connection**

Thermometer connection

male thread:

NPT1/2"

**Tip shape**

Not defined

**Operating temperature range**

PT100 TF StrongSens:

-50 °C ...500 °C

(-58 °F ...932 °F)

PT100 WW:

-200 °C ...600 °C

(-328 °F ...1.112 °F)

PT100 TF:

-50 °C ...400 °C

(-58 °F ...752 °F)

**Max. process pressure (static)**

at 20 °C: 500 bar (7.252 psi)

## Thermometer

### Accuracy

class A acc. to IEC 60751

class AA acc. to IEC 60751

---

### Response time

depending on configuration

t50 = 4 s

t90 = 8 s

---

### Integration head transmitter

yes (4 ... 20 mA; HART; PROFIBUS PA; FOUNDATION  
FIELDBUS)

---

### Ex - approvals

ATEX II

IECEX

NEPSI

EAC Ex

Explosion proof

---

### Certification

Gost Metrology

SIL (transmitter only)

---

More information [www.endress.com/TR62](http://www.endress.com/TR62)