

RNB22 system power supply unit

Safely power system interfaces on the DIN rail bus



优势:

- Safe and reliable, single-phase output in the power range up to 100 W
- Smart system function monitoring for fault prevention for high system availability
- Powerful reserve capacity for lower power ranges
- Transient surge protection, short-circuit proof, no-load proof
- Tool-free installation, suited for vertical or horizontal mounting

产品规格参数

- 输出 24...28 V DC
- 电源 100...240 V AC/DC

详细信息和最新价格参见:

www.endress.com.cn/RNB22

应用领域: The RNB22 is a compact, high-efficiency primary switch mode power supply for DIN rail interface systems. It delivers a reliable, single-phase, **24 V_{DC} / 2.5 A** output and runs on a wide-range input from 100 to 240 V_{AC} / 110 to 250 V_{DC}, with a dynamic and static boost of 5 A and 3.125 A respectively. When run in parallel with the **RNF22** error message module, the RNB22 provides redundancy, increased capacity, as well as function monitoring to report critical operating states before errors occur.

特征和规格

电源和安全栅

测量原理

有源安全栅

测量原理

Power supply

电源和安全栅

功能

System power supply 24 V
DC

回路供电

24...28 V DC

电源

100...240 V AC/DC

输出

24...28 V DC

证书

DNV

操作

Rotary selector

更多信息 www.endress.com.cn/RNB22