

Vibronic

Point level detection

Liquiphant FTL51C

Point level switch for liquids with highly corrosion-resistant coating



More information and current pricing:

www.es.endress.com/FTL51C

Benefits:

- Use in safety systems requiring functional safety to SIL2/SIL3 in accordance with IEC 61508/IEC 61511-1
- Different plastic coating (PFA) and enamel coating for applications with aggressive medias
- International explosion protection certificates and overfill prevention certificate (WHG)
- No calibration required, easy to start up
- No mechanically moving parts: no maintenance, no wear, long operating life.
Monitoring of fork for damage: guaranteed function
- Second line of defense to protect the environment
- Variety of standardized process connections for all applications

Specs at a glance

- **Process temperature** -50 °C...+150 °C (-58 °F...+302 °F) up to 230 °C / 450°F on request
- **Process pressure / max. overpressure limit** Vacuum...40 bar (Vacuum...580 psi)
- **Min. density of medium** 0.5g/cm³ (0.4g/cm³ optional)

Field of application: Liquiphant FTL51C is a point level switch with extension tube and highly corrosion resistant coating. For use in hazardous areas with all international certificates. Useable in all industries. FTL51 offers functional safety SIL2/SIL3. With the second line of defense highest degree of safety and availability of the device can be guaranteed. Reliable measurement values, not affected by: changing

media properties, flow, turbulences, gas bubbles, foam, vibrations or build-up.

Features and specifications

Point Level / Liquids

Measuring principle

Vibration Liquids

Characteristic / Application

High protection against aggressive media by using antistatic coating
Modular housing concept
wide range of process connections
Analogue and bus interfaces
Extensive certificate range (e.g.Ex,WHG)
pipe extension up to 3m (6m option)

Specialities

Foam detection
Detect a density change
second line of defense

Supply / Communication

PROFIBUS PA
19...253V AC, 2-wire
10...55V DC-PNP, 3-wire
DPDT, 19...253V AC, 10...55V DC
8/16mA, 11...36V DC
NAMUR
PFM, 2-wire
NAMUR with testbutton

Ambient temperature

-50 °C...+70 °C
(-58 °C...+158 °F)

Point Level / Liquids**Process temperature**

-50 °C...+150 °C
(-58 °F...+302 °F)
up to 230 °C / 450°F on request

Process pressure / max. overpressure limit

Vacuum...40 bar
(Vacuum...580 psi)

Min. density of medium

0.5g/cm³ (0.4g/cm³ optional)

Main wetted parts

ECTFE
PFA (Edlon)
PFA (Rubyred)
PFA (conductive)
Enamel

Process connection

Flange:
DN25...DN100,
ASME 1"...3",
JIS RF10 K 50

Process connection hygienic

FDA conform with PFA (Edlon)

Sensor length

ECTFE, PFA 130mm, 148mm...3000mm
(ECTFE, PFA 5.12", 5.83"...118")
Enamel 130mm, 148mm...1200mm
(Enmal 5.12", 5.83"...47.24")

Point Level / Liquids**Communication**

PROFIBUS PA
19...253V AC
10...55V DC-PNP
19...253V AC bzw 10...55V DC
8/16mA, 11...36V DC
NAMUR
PFM

Certificates / Approvals

ATEX, FM, CSA C/US, IEC Ex, TIIS, INMETRO, NEPSI

Safety approvals

SIL2/ SIL3

Design approvals

EN 10204-3.1

Marine approval

GL/ ABS/ DNV

Options

Heavy duty stainless steel housing mainly for the oil and gas industry

Components

FTL325P/FTL375P Interface PFM
FTL325N/FTL375N Interface NAMUR

Density**Measuring principle**

Vibration Density

Density

Characteristic / Application

Liquiphant M Density
with Density Computer FML621
Temperature and pressure measurement
High protection against aggressive media by using antistatic coating
Modular housing concept
Wide range of process connections
Pipe extension up to 3 m (6 m option)

Supply / Communication

Transmitter power supply (MUS)

Ambient temperature

-50...80°C
-50...60°C for hazardous applications

Process temperature

0...80 °C (validity of accuracy data)
-50...0°C / 80...150 °C (with reduced technical data)

Process pressure

0...25 bar
>25...40 bar (with reduced technical data)

Wetted parts

ECTFE, PFA and Enamel

Sensor length

115...3000 mm
(depends by the covering)

Output

Pulse

Certificates / Approvals

ATEX, FM, CSA C/US, IEC Ex, TIIS, INMETRO, NEPSI

Density

Specialities

Commissioning with ReadWin2000

Components

Density Computer FML621

Measuring range

Density range: 0.3 to 2 g/cm³

Other approvals and certificates

SIL2/ SIL3

More information www.es.endress.com/FTL51C