

## Radar measurement Micropilot FMR532

For high accurate non-contact level measurement in stilling well applications in custody transfer



More information and current pricing:

[www.fi.endress.com/FMR532](http://www.fi.endress.com/FMR532)

### Benefits:

- 0.8mm accuracy ( $2\sigma$  value)
- National approvals (NMI, PTB) for custody transfer
- Applicable as stand-alone system or integrated into tank gauging systems via the Tank Side Monitor NRF590
- Easy on-site operation via menu-driven alphanumeric display
- Easy commissioning, documentation and diagnostics via FDT/DTM technology (FieldCare)
- Cost-effective and simple installation via 4-wire cable with HART and 24 V DC intrinsically safe power supply
- Unique drip-off antenna design eliminates measurement error due to condensation build-up

### Specs at a glance

- **Accuracy** +/- 1 mm, custody transfer
- **Process temperature** -40 °C ... 150 °C (-40 °F ... 302 °F)
- **Process pressure absolute / max. overpressure limit** Vacuum ... 25 bar (Vacuum ... 362 psi)
- **Max. measurement distance** 40 m (131 ft)
- **Main wetted parts** 316L + PTFE

**Field of application:** The Micropilot FMR532 is used for custody transfer and inventory control applications with NMI- and PTB-approvals. It meets the relevant requirements according to OIML R85 and API 3.1B. The FMR532 free space radar with planar antenna is specifically suited for stilling well applications. Micropilot FMR532 offers cost-effective and

simple installation via 4-wire cable with HART and 24 V DC intrinsically safe power supply.

## Features and specifications

### Continuous / Liquids

**Measuring principle**

Level radar

**Characteristic / Application**

Characteristic / Application

**Supply / Communication**

4-wire (HART)

**Frequency**

C-band (~6 GHz)

**Accuracy**

+/- 1 mm, custody transfer

**Ambient temperature**

Standard:

-40 °C ... 80 °C

(-40 °F ... 176 °F)

For calibration to regulatory standards:

-25 °C ... 60 °C

(-13 °F ... 131 °F)

**Process temperature**

-40 °C ... 150 °C

(-40 °F ... 302 °F)

**Process pressure absolute / max. overpressure limit**

Vacuum ... 25 bar

(Vacuum ... 362 psi)

**Main wetted parts**

316L + PTFE

---

**Continuous / Liquids****Process connection**

DN150 ... DN300 / 6" ... 12"

**Max. measurement distance**

40 m (131 ft)

**Communication**

4 ... 20 mA

**Certificates / Approvals**

ATEX, FM, CSA, IEC Ex, NEPSI

**Design approvals**

EN 10204-3.1

NACE MR0175, MR0103

**Marine approval**

GL/ ABS

**Application limits**

Maximum measuring range is dependent on the tank form and/or application

Free space and many baffles

FMR540

---

More information [www.fi.endress.com/FMR532](http://www.fi.endress.com/FMR532)