

## RNB130

### Primary switched-mode power supply for DIN rail

Power supply for one 4 wire sensor or transmitter.



#### Benefits:

- Small housing, 35 mm width
- High availability
- Wide range input - can be used world-wide
- Power reserve (Power Boost)
- Power supply without wiring: Supply via DIN rail bus connector
- Space saving DIN rail mounting as per IEC 60715

#### Specs at a glance

- **Output** 24 VDC, 1,5 A
- **Power Supply** 100...240 V AC (wide range power supply) 45...65 Hz

from **€348.00**

Price as of 17.08.2022

More information and current pricing:

[www.fi.endress.com/RNB130](http://www.fi.endress.com/RNB130)

**Field of application:** The power supply has one output for supplying voltage to 4 wire sensors and transmitters. Connection to mono-phased a.c. networks or to two phase conductors of three-phase supply networks (TN-, TT- or IT-networks as per VDE 0100 T 300/IEC 364-3) with 100-240 V AC nominal voltage possible.

### Features and specifications

#### Power supplies & barrier

##### Measuring principle

Power supply

##### Measuring principle

Power supply

---

**Power supplies & barrier****Function**

Power supply for one 4-wire sensor or transmitter

---

**Loop power supply**

24 V DC

---

**Power Supply**

100...240 V AC (wide range power supply)  
45...65 Hz

---

**Auxiliary power supply / Loop power supply**

85...250 V AC  
45...65 Hz

---

**Output**

24 VDC, 1,5 A

---

**Operation**

DIP switch

---

**Acquisition / Evaluation****Measuring principle**

Power supply

---

**Function**

Power

---

**Output**

24 VDC, 1,5 A

---

**Auxiliary power supply / Loop power supply**

85...250 V AC  
45...65 Hz

---

Acquisition / Evaluation

**Dimensions (wxhxd)**

35 x 99 x 102.5 mm  
(1.39" x 3.9" x 4.04")

---

**Operation**

DIP switch

---

More information [www.fi.endress.com/RNB130](http://www.fi.endress.com/RNB130)