

## RNB130

### Primary switched-mode power supply for DIN rail

Power supply for one 4 wire sensor or transmitter.



#### Edut:

- Small housing, 35 mm width
- High availability
- Wide range input - can be used world-wide
- Power reserve (Power Boost)
- Power supply without wiring: Supply via DIN rail bus connector
- Space saving DIN rail mounting as per IEC 60715

#### Tärkeimmät tekniset tiedot

- **Output** 24 VDC, 1,5 A
- **Power Supply** 100...240 V AC (wide range power supply) 45...65 Hz

alk. **146,00 €**

Hinta 16.10.2021

Lisätietoja ja ajankohtainen hinnasto:

[www.fi.endress.com/RNB130](http://www.fi.endress.com/RNB130)

**Käyttöalue:** The power supply has one output for supplying voltage to 4 wire sensors and transmitters. Connection to mono-phased a.c. networks or to two phase conductors of three-phase supply networks (TN-, TT- or IT-networks as per VDE 0100 T 300/IEC 364-3) with 100-240 V AC nominal voltage possible.

#### Ominaisuudet ja tiedot

Acquisition / Evaluation

Mittausperiaate

Power supply

Function

Power

**Acquisition / Evaluation****Output**24 VDC, 1,5 A

---

**Auxiliary power supply / Loop power supply**

85...250 V AC

45...65 Hz

---

**Dimensions (wxhxd)**

35 x 99 x 102.5 mm

(1.39" x 3.9" x 4.04")

---

**Operation**DIP switch

---

**Power supplies & barrier****Mittausperiaate**Power supply

---

**Measuring principle**Power supply

---

**Function**Power supply for one 4-wire sensor or transmitter

---

**Loop power supply**24 V DC

---

**Power Supply**

100...240 V AC (wide range power supply)

45...65 Hz

---

Power supplies & barrier

**Auxiliary power supply / Loop power supply**

85...250 V AC

45...65 Hz

---

**Output**

24 VDC, 1,5 A

---

**Operation**

DIP switch

---

Lisätietoja [www.fi.endress.com/RNB130](http://www.fi.endress.com/RNB130)