

# Vibronic

## Point level detection

### Liquiphant FTL81

Point level switch for liquids for FailSafe overfill prevention



Lisätietoja ja ajankohtainen hinnasto:

[www.fi.endress.com/FTL81](http://www.fi.endress.com/FTL81)

#### Edut:

- Use in safety systems requiring functional safety to SIL3 in accordance with IEC 61508 Ed.2.0/ IEC 61511-1/ISA 84-1 and DIN EN ISO 13849
- Proof test: proof testing interval up to 12 years, Slave devices tested at the press of a button
- Permanent self-monitoring/internal redundancy
- 4-20mA interface (acc. to NAMUR NE 06/NE 43): easy integration via the switching unit (Nivotester FailSafe FTL825) with a two-channel output (safety contacts) and locking function or direct integration into a safety PLC
- No adjustment: quick, low-cost startup
- No mechanically moving parts: no maintenance, no wear, long operating life
- Monitoring of fork for damage, corrosion, build-up and mechanical blocking

#### Tärkeimmät tekniset tiedot

- **Process temperature** -60°C...+280°C (-76°F...+540°F)
- **Process pressure absolute / max. overpressure limit**  
Vacuum...100 bar (1450 psi)
- **Min. density of medium** Density from 0.4 g/cm<sup>3</sup> (0.4 SGU)

**Käyttöalue:** Liquiphant FTL81 is a point level switch for use in hazardous areas with all international certificates. FailSafe overfill prevention in applications with functional safety up to SIL3 with one device. Reliable

measurement values, not affected by: changing media properties, flow, turbulences, gas bubbles, foam, vibrations or build-up.

## Ominaisuudet ja tiedot

### Point Level / Liquids

#### **Mittausperiaate**

Vibration Liquids

#### **Characteristic / Application**

Reliable point level switch with extension pipe for MIN and MAX safety applications up to SIL3.

Dual Sealing / Second line of defense

Modular housing concept

#### **Specialities**

Outstanding features:

- permanent LIVE signal monitors function safety
- failsafe design and
- high availability of the measuring values

#### **Supply / Communication**

2-wire 4...20 mA

#### **Ambient temperature**

-60°C...+70°C

(-76°F...+160°F)

#### **Process temperature**

-60°C...+280°C

(-76°F...+540°F)

#### **Process pressure absolute / max. overpressure limit**

Vacuum...100 bar

(1450 psi)

#### **Min. density of medium**

Density from 0.4 g/cm<sup>3</sup>

(0.4 SGU)

---

## Point Level / Liquids

---

### Main wetted parts

316L  
Alloy C

---

### Process connection

Flange:  
DN25...DN100,  
ASME 1"...4",  
JIS 10K...20K  
Thread:  
G3/4, G1, R3/4,  
R1, MNPT3/4, MNPT1

---

### Sensor length

Extension pipe up to 3 m (9.8 ft)

---

### Communication

2-wire 4...20 mA

---

### Certificates / Approvals

ATEX, FM, CSA, CSA C/US, IEC Ex, NEPSI, EAC

---

### Safety approvals

Overfill protection WHG  
Leakage Detection  
SIL3

---

### Design approvals

EN 10204-3.1  
NACE MR0175, MR0103  
ASME B31.3  
AD2000

---

### Marine approval

GL/ ABS/ LR/ BV/ DNV

---

## Point Level / Liquids

### Options

PWIS free  
Pressure tight feed through  
Weather protection

---

### Components

Nivotester FTL825, Transmitter

---

Lisätietoja [www.fi.endress.com/FTL81](http://www.fi.endress.com/FTL81)