

# RN42 active barrier, wide range power supply

1-channel wide range supply and active barrier for safe isolation of 4 to 20 mA standard signal circuits



## Benefits:

- Wide range power supply of 19.2 to 253 V<sub>AC/DC</sub>
- Quick and easy wiring thanks to plug-in terminals
- Optional for safety-oriented applications up to SIL 2 (SC3) in accordance with IEC 61508
- Optional installation in Ex Zone 2
- Compact housing width with 17.5 mm (0.69 in) for efficient use of space
- Option for installation rotated by 180° (terminals for power supply at top or bottom)

## Specs at a glance

- **Input** 0/4...20 mA / HART feeding/not feeding
- **Output** 0/4...20 mA / HART active/passive
- **Power Supply** 20...250 V AC/DC

from **€260.40**

Price as of 09.08.2022

More information and current pricing:

[www.fr.endress.com/RN42](http://www.fr.endress.com/RN42)

**Field of application:** The active barrier is used for transmission and galvanic isolation of 4 to 20 mA/HART signals. The device has an active / passive current input to which a 2- or 4-wire transmitter can be connected directly. The output of the device can be operated actively or passively. The current signal is then available to the PLC / controller or for further instrumentation at pluggable screw or optional push-in terminals.

## Features and specifications

---

**Power supplies & barrier****Measuring principle**Active barrier

---

**Measuring principle**Active barrier

---

**Function**1-channel

---

**Loop power supply**17,5 V  $\pm$  1 V bei 20 mAopen circuit voltage: 24,5 V  $\pm$  5 %

---

**Power Supply**20...250 V AC/DC

---

**Input**

0/4...20 mA / HART

feeding/not feeding

---

**Output**

0/4...20 mA / HART

active/passive

---

**Certificates**

ATEX

IECEX

CSA

DNV

Non-hazardous area + EAC

marking

---

**SIL**SIL 2 SC 3

---

**Operation**HART

---

More information [www.fr.endress.com/RN42](http://www.fr.endress.com/RN42)