

Promass 83P



More information and current pricing:

www.fr.endress.com/83P

Benefits:

- Highest process quality – fully compliant to industry requirements
- Fewer process measuring points – multivariable measurement (flow, density, temperature)
- Space-saving installation – no in/outlet run needs
- Quality – software for filling & dosing, density & concentration, advanced diagnostics
- Flexible data transfer options – numerous communication types
- Automatic recovery of data for servicing

Specs at a glance

- **Max. measurement error** Mass flow (liquid): $\pm 0.1\%$ Volume flow (liquid): $\pm 0.1\%$ Mass flow (gas): $\pm 0.5\%$ Density (liquid): $\pm 0.0005 \text{ g/cm}^3$
- **Measuring range** 0 to 70 000 kg/h (0 to 2570 lb/min)
- **Medium temperature range** -50 to $+200 \text{ }^\circ\text{C}$ (-58 to $+392 \text{ }^\circ\text{F}$)
- **Max. process pressure** PN 63, Class 300, 40K
- **Wetted materials** Measuring tube: 1.4435 (316L) Connection: 1.4435 (316L); 1.4404 (316/316L)

Field of application: Promass P offers the enhanced performance of a bent tube meter and the drainability of a straight tube meter without any compromise. Combined with the Promass 83 transmitter with touch control, and extended functionality like software options for filling and dosing, concentration measurement or advanced diagnostics, Promass 83P offers highly accurate measurement for demanding applications in sterile environments in the life sciences industry.

Features and specifications

Liquids

Measuring principle

Coriolis

Liquids

Product headline

The specialist for life sciences with extended transmitter functionality. Dedicated for applications under sterile conditions in the life sciences industry.

Sensor features

Highest process quality – fully compliant to industry requirements. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space - saving installation – no in/outlet run needs. ASME BPE, 3-A and EHEDG conform & low delta ferrite. Electropolished measuring tube in 1.4435 (316L).

Transmitter features

Quality – software for filling & dosing, density & concentration, advanced diagnostics. Flexible data transfer options – numerous communication types. Automatic recovery of data for servicing. 4 - line backlit display with touch control. Device in compact or remote version.

Nominal diameter range

DN 8 to 50 ($\frac{3}{8}$ to 2")

Wetted materials

Measuring tube: 1.4435 (316L)

Connection: 1.4435 (316L); 1.4404 (316/316L)

Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow, reference density, concentration

Max. measurement error

Mass flow (liquid): ± 0.1 %

Volume flow (liquid): ± 0.1 %

Mass flow (gas): ± 0.5 %

Density (liquid): ± 0.0005 g/cm³

Measuring range

0 to 70 000 kg/h (0 to 2570 lb/min)

Liquids

Max. process pressure

PN 63, Class 300, 40K

Medium temperature range

-50 to +200 °C (-58 to +392 °F)

Ambient temperature range

Standard: -20 to +60 °C (-4 to +140 °F)

Option: -40 to +60 °C (-40 to +140 °F)

Sensor housing material

1.4301 (304), corrosion resistant

Transmitter housing material

Powder - coated die - cast aluminium

1.4301 (304), sheet

CF3M (316L), cast

Degree of protection

IP67, type 4X enclosure. Remote transmitter: IP67, type 4X enclosure

Display/Operation

4 - line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Outputs

4 modular outputs:

0 - 20 mA (active)/4 - 20 mA (active/passive)

Pulse/frequency/switch output (passive)

Relay

Inputs

2 modular inputs:

Status

0 - 20 mA (active)/4 - 20 mA (active/passive)

Digital communication

HART, PROFIBUS PA/DP, FOUNDATION Fieldbus, Modbus

RS485, EtherNet/IP

Liquids

Power supply

DC 16 to 62 V

AC 85 to 260 V (45 to 65 Hz)

AC 20 to 55 V (45 to 65 Hz)

Hazardous area approvals

ATEX, IECEx, FM, CSA, NEPSI

Other approvals and certificates

3.1 material, calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025), NAMUR, SIL

PED, CRN

3-A, FDA, ASME BPE, ISPE

Product safety

CE, C-tick, EAC marking

Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025), NAMUR

Pressure approvals and certificates

PED, CRN

Material certificates

3.1 material

Hygienic approvals and certificates

3-A, FDA, ASME BPE, ISPE

Gas

Measuring principle

Coriolis

Gas

Product headline

The specialist for life sciences with extended transmitter functionality. Dedicated for applications under sterile conditions in the life sciences industry.

Sensor features

Highest process quality – fully compliant to industry requirements. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space - saving installation – no in/outlet run needs. ASME BPE and 3-A conform & low delta ferrite. Electropolished measuring tube in 1.4435 (316L).

Transmitter features

Quality – software for filling & dosing, density & concentration, advanced diagnostics. Flexible data transfer options – numerous communication types. Automatic recovery of data for servicing. 4 - line backlit display with touch control. Device in compact or remote version.

Nominal diameter range

DN 8 to 50 ($\frac{3}{8}$ to 2")

Wetted materials

Measuring tube: 1.4435 (316L)

Connection: 1.4435 (316L); 1.4404 (316/316L)

Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow, reference density, concentration

Max. measurement error

Mass flow (liquid): ± 0.1 %

Volume flow (liquid): ± 0.1 %

Mass flow (gas): ± 0.5 %

Density (liquid): ± 0.0005 g/cm³

Measuring range

0 to 70 000 kg/h (0 to 2570 lb/min)

Gas

Max. process pressure

PN 63, Class 300, 40K

Medium temperature range

-50 to +200 °C (-58 to +392 °F)

Ambient temperature range

Standard: -20 to +60 °C (-4 to +140 °F)

Option: -40 to +60 °C (-40 to +140 °F)

Sensor housing material

1.4301 (304), corrosion resistant

Transmitter housing material

Powder - coated die - cast aluminium

1.4301 (304), sheet

CF3M (316L), cast

Degree of protection

IP67, type 4X enclosure. Remote transmitter: IP67, type 4X enclosure

Display/Operation

4 - line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Outputs

4 modular outputs:

0 - 20 mA (active)/4 - 20 mA (active/passive)

Pulse/frequency/switch output (passive)

Relay

Inputs

2 modular inputs:

Status

0 - 20 mA (active)/4 - 20 mA (active/passive)

Digital communication

HART, PROFIBUS PA/DP, FOUNDATION Fieldbus, Modbus

RS485, EtherNet/IP

Gas

Power supply

DC 16 to 62 V

AC 85 to 260 V (45 to 65 Hz)

AC 20 to 55 V (45 to 65 Hz)

Hazardous area approvals

ATEX, IECEx, FM, CSA, NEPSI

Other approvals and certificates

3.1 material, calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025), NAMUR, SIL

PED, CRN

3-A, FDA, ASME BPE, ISPE

Product safety

CE, C-tick, EAC marking

Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025), NAMUR

Pressure approvals and certificates

PED, CRN

Material certificates

3.1 material

Hygienic approvals and certificates

3-A, FDA, ASME BPE, ISPE

Density

Measuring principle

Coriolis

Density

Characteristic / Application

Coriolis mass flowmeter complying with ASME BPE, ISPE, FDA, 3-A

Ambient temperature

-20...+65°C
(-4...+140°F)

Process temperature

-50...+200°C
(-58...+392°F)

Process pressure

PN 16...40
CI 150...300
JIS 20...40K

Wetted parts

316L/1.4435

Output

4...20mA
Pulse/Frequency (10KHz, active/passive)
Relays/Status

Certificates / Approvals

ATEX
FM
CSA IECEx TIIS NEPSI

Density/Concentration

Measuring principle

Coriolis

Product headline

The specialist for life sciences with extended transmitter functionality. Dedicated for applications under sterile conditions in the life sciences industry.

Density/Concentration

Sensor features

Highest process quality – fully compliant to industry requirements. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space - saving installation – no in/outlet run needs. ASME BPE, 3-A and EHEDG conform & low delta ferrite. Electropolished measuring tube in 1.4435 (316L).

Transmitter features

Quality – software for filling & dosing, density & concentration, advanced diagnostics. Flexible data transfer options – numerous communication types. Automatic recovery of data for servicing. 4 - line backlit display with touch control. Device in compact or remote version.

Nominal diameter range

DN 8 to 50 ($\frac{3}{8}$ to 2")

Wetted materials

Measuring tube: 1.4435 (316L)

Connection: 1.4435 (316L); 1.4404 (316/316L)

Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow, reference density, concentration

Max. measurement error

Mass flow (liquid): ± 0.1 %

Volume flow (liquid): ± 0.1 %

Mass flow (gas): ± 0.5 %

Density (liquid): ± 0.0005 g/cm³

Measuring range

0 to 70 000 kg/h (0 to 2570 lb/min)

Max. process pressure

PN 63, Class 300, 40K

Medium temperature range

-50 to +200 °C (-58 to +392 °F)

Density/Concentration**Ambient temperature range**

Standard: -20 to +60 °C (-4 to +140 °F)

Option: -40 to +60 °C (-40 to +140 °F)

Sensor housing material1.4301 (304), corrosion resistant

Transmitter housing material

Powder - coated die - cast aluminium

1.4301 (304), sheet

CF3M (316L), cast

Degree of protectionIP67, type 4X enclosure. Remote transmitter: IP67, type 4X enclosure

Display/Operation

4 - line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Outputs

4 modular outputs:

0 - 20 mA (active)/4 - 20 mA (active/passive)

Pulse/frequency/switch output (passive)

Relay

Inputs

2 modular inputs:

Status

0 - 20 mA (active)/4 - 20 mA (active/passive)

Digital communication

HART, PROFIBUS PA/DP, FOUNDATION Fieldbus, Modbus

RS485, EtherNet/IP

Power supply

DC 16 to 62 V

AC 85 to 260 V (45 to 65 Hz)

AC 20 to 55 V (45 to 65 Hz)

Density/Concentration

Hazardous area approvals

ATEX, IECEx, FM, CSA, NEPSI

Product safety

CE, C-tick, EAC marking

Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025), NAMUR

Pressure approvals and certificates

PED, CRN

Material certificates

3.1 material

Hygienic approvals and certificates

3-A, FDA, ASME BPE, ISPE

More information www.fr.endress.com/83P