

EngyCal RH33

BTU meter

Custody transfer BTU meter for recording heat quantities of water



More information and current pricing:

www.id.endress.com/RH33

Benefits:

- Transparent energy consumption helps you save on energy costs
- Calibrated, electronically paired temperature sensors ensure the highest accuracy and enable replacement of individual temperature sensors even for certified devices in the field (without reapproval!)
- Tariff counter for requirements-based billing
- Detailed data logging of current and counter values and of error messages, off-limit conditions and changes to operating parameters
- Standard models are suitable for connecting and supplying all common volume flow transmitters and temperature measuring points
- Remote readout via Ethernet and fieldbuses
- Verified and certified reliability and accuracy

Specs at a glance

- **Input** 1x Puls/Analog 2x RTD/Analog Loop power supply 24V DC (+/-16%)
- **Output** 1x 4...20mA 2x digital (Open Collector)
- **Display** 160 x 80 Dot-Matrix LCD with white backlit colour change in case of alarm event active display area 70 x 34 mm
- **Calculations** heat quantity and heat quantity difference

Field of application: The BTU meter RH33 is used in applications with liquid energy carriers. It calculates the thermal energy of water acc. to EN1434, glycol/water mixtures or other fluids such as thermal oils. Temperature sensor matching using calibrated temperature sensors is done in the device. Potential for cost savings can be shown by using the software available as an accessory. The device has a custody transfer approval and allows bi-directional measurement, e.g. charging/discharging of a heat accumulator.

Features and specifications

Energy & Application Manager	Measuring principle
	Energy manager
	Measuring principle
	Energy manager
	Function
	Monitoring and billing of energy in heating and cooling applications as well as combined heating-and cooling circles. Typical applications can be found in industries, district heating and building automation.
	Calculations
	heat quantity and heat quantity difference
	Number of applications
	1
Data storage	
yes	
Calculation standards	
IAPWS-97	
Communication	
web server USB Ethernet Modbus RTU/TCP Slave M-Bus	
Power supply	
Not defined	

Energy & Application Manager Loop power supply

Low voltage power supply:
100 bis 230 V AC (-15% / +10%)
Small voltage power supply:
24 V DC (-50% / +75%)
24 V AC (\pm 50%)

Protection class

IP65

Input

1x Puls/Analog
2x RTD/Analog
Loop power supply 24V DC (+/-16%)

Output

1x 4...20mA
2x digital (Open Collector)

Dimensions (WxHxD)

144 x 144 x 103.1 mm (5.67" x 5.67" x 4.06")

Operation

3 button on site or via FieldCare
read out of historical / logged data via Field Data Manager Software
(SQL database and visualization interface)
selectable language

Display

160 x 80 Dot-Matrix LCD with white backlit
colour change in case of alarm event
active display area 70 x 34 mm

Energy & Application Manager **Software functions**

Calculated Values:

Energy, volume, density, enthalpy & enthalpy difference, DP-Flow-Compensation, mass, temperature difference

Counters:

Volume, mass, energy, counter in case of failure

Optional:

tariff 1, tariff 2 or seperated heating energy, cooling energy, bilance energy

Certificates

CE

CSA GP

MID 004 (custody transfer) according EN1434 (water/other liquids)

OIML R75

Thermal Energy Measurement **Measuring principle**

Energy manager

Function

Monitoring and billing of energy in heating and cooling applications as well as combined heating-and cooling circles.

Typical applications can be found in industries, district heating and building automation.

Certification

CE, UL listed, CSA GP, MID 004 (custody transfer) according EN1434 (water/other liquids) and OIML R75

Input

1x Puls/Analog,

2x RTD/Analog,

Loop power supply 24V DC (+/-16%)

Thermal Energy Measurement**Output**

1x 4...20mA,
2x digital (Open Collector)

Relay output

2x

Auxiliary power supply

Low voltage power supply: 100 bis 230 V AC (-15% / +10%); Small voltage power supply: 24 V DC (-50% / +75%), 24 V AC ($\pm 50\%$)

Dimensions (wxhxd)

144 x 144 x 103.1 mm
(5.67" x 5.67" x 4.06")

Software

Calculated Values:

Energy, volume, density, enthalpy & enthalpy difference,
DP-Flow-Compensation,
mass,

temperature difference;

Counters: volume, mass, energy, counter in case of failure

Optional: tariff 1, tariff 2 or seperated heating energy, cooling energy,
balance energy

Operation

3 button on site or via FieldCare; read out of historical / logged data via Field Data Manager Software (SQL database and visualization interface), selectable language

Display

160 x 80 Dot-Matrix LCD with white backlit, colour change in case of alarm event, active display area 70 x 34 mm

Others

electronic temperature sensor matching via CvD coefficients, logbook measured values, custody transfer logbook, event logbook, limit monitoring

Thermal Energy Measurement **Calculations**
IAPWS-IF97

More information www.id.endress.com/RH33