

# Picomag

## Electromagnetic flowmeter

Smart magmeter for utilities – intuitive · convenient · multivariable



innen **415,00 EUR**

23.04.2021 -i ár

További információk és az aktuális árak elérhetők: [www.hu.endress.com/DMA](http://www.hu.endress.com/DMA)

### Előnyök:

- Time-saving, easy configuration even in places difficult to reach – secure Bluetooth connection
- Fewer measuring points necessary – simultaneous flow, conductivity and temperature measurement
- Cost-efficient specialist for use in tight spaces e.g. skids – sensor and transmitter in one housing
- Quick offline configuration check – unique, comfortable knock functionality
- Simple device access through its whole lifecycle – no manual needed due to intuitive SmartBlue App
- Instant local process monitoring – large, user-friendly display of all measurement activities
- Flexible integration into all fieldbus systems – plug-and-play device with IO-Link

### Specifikációk áttekintése

- **Max. measurement error** Volume flow: +/-0.8% o.r. +/- 0.2% o.f.s
- **Measuring range** up to 750 l/min
- **Medium temperature range** -10 to 85 °C
- **Max. process pressure** 16 bar
- **Wetted materials** PEEK, Stainless Steel, FKM, EPDM Electrodes: 1.4404/316L

**Alkalmazási terület:** Picomag is the economical magmeter for many applications in secondary circuits with conductive liquids in all industries. End customers, skid builders, equipment manufacturers and system integrators value the space-saving Picomag for its flexible installation

capabilities. Additionally, its future-oriented, intuitive operation via SmartBlue app on every Bluetooth-enabled smartphone or tablet ensures fast, secure and simple commissioning.

## Tulajdonságok és jellemzők

### Liquids

#### **Mérési elv**

Electromagnetic

#### **Product headline**

Smart magmeter for utilities – intuitive · convenient · multivariable. Time-saving, easy configuration even in places difficult to reach – secure Bluetooth connection. Ideal for process quality control and monitoring due to temperature and conductivity measurement in utilities.

#### **Sensor features**

Fewer measuring points necessary – simultaneous flow, conductivity and temperature measurement. Cost-efficient specialist for use in tight spaces e.g. skids – sensor and transmitter in one housing.

#### **Transmitter features**

Quick offline configuration check – unique, comfortable knock functionality. Simple device access through its whole lifecycle – no manual needed due to intuitive SmartBlue app. Effortless configuration of several devices – settings can be saved and loaded into other meters. Flexible integration into all fieldbus systems – plug-and-play device with IOLink.

#### **Nominal diameter range**

DN15 to 50 (1/2 to 2")

#### **Wetted materials**

PEEK, Stainless Steel, FKM, EPDM

Electrodes: 1.4404/316L

#### **Measured variables**

Volume flow, Temperature, Conductivity

---

## Liquids

**Max. measurement error**

Volume flow: +/-0.8% o.r. +/- 0.2% o.f.s

---

**Measuring range**

up to 750 l/min

---

**Max. process pressure**

16 bar

---

**Medium temperature range**

-10 to 85 °C

---

**Ambient temperature range**

-10 to 60 °C

---

**Sensor housing material**

1.4404/316L, Polycarbonate

---

**Transmitter housing material**

1.4404/316L, Polycarbonate

---

**Degree of protection**

IP 65/67

---

**Display/Operation**

Integrated display, operation via SmartBlue app

---

**Outputs**

Current (4 to 20mA)

Pulse

Switch

Voltage (2 to 10V)

---

**Inputs**

Status

---

## Liquids

### Digital communication

IO-Link

---

### Power supply

18 to 30V DC

---

### Product safety

cULus listing

---

### Hygienic approvals and certificates

Drinking water approvals: NSF

---

További információk [www.hu.endress.com/DMA](http://www.hu.endress.com/DMA)