

## RNB130

### Primary switched-mode power supply for DIN rail

Power supply for one 4 wire sensor or transmitter.



#### Előnyök:

- Small housing, 35 mm width
- High availability
- Wide range input - can be used world-wide
- Power reserve (Power Boost)
- Power supply without wiring: Supply via DIN rail bus connector
- Space saving DIN rail mounting as per IEC 60715

#### Specifikációk áttekintése

- **Input** Not defined
- **Output** 24 VDC, 1,5 A
- **Power Supply** Not defined

innen **142,23 EUR**

23.04.2021 -i ár

További információk és az aktuális árak elérhetők:

[www.hu.endress.com/RNB130](http://www.hu.endress.com/RNB130)

**Alkalmazási terület:** The power supply has one output for supplying voltage to 4 wire sensors and transmitters. Connection to mono-phased a.c. networks or to two phase conductors of three-phase supply networks (TN-, TT- or IT-networks as per VDE 0100 T 300/IEC 364-3) with 100-240 V AC nominal voltage possible.

#### Tulajdonságok és jellemzők

Power supplies & barrier

Mérési elv

Power supply

Measuring principle

Power supply

## Power supplies &amp; barrier

**Function**

Power supply for one 4-wire sensor or transmitter

**Loop power supply**

85...250 V AC

45...65 Hz

**Power Supply**

Not defined

**Auxiliary power supply / Loop power supply**

85...250 V AC

45...65 Hz

**Input**

Not defined

**Output**

24 VDC, 1,5 A

**Software functions**

Not defined

**Certificates**

Not defined

**SIL**

Not defined

**Operation**

DIP switch

## Acquisition / Evaluation

**Mérési elv**

Power supply

## Acquisition / Evaluation

---

### Function

Power

---

### Output

24 VDC, 1,5 A

---

### Auxiliary power supply / Loop power supply

85...250 V AC

45...65 Hz

---

### Dimensions (wxhxd)

35 x 99 x 102.5 mm

(1.39" x 3.9" x 4.04")

---

### Operation

DIP switch

---

További információk [www.hu.endress.com/RNB130](http://www.hu.endress.com/RNB130)