

# Compact conductivity device Smartec CLD18

## Toroidal conductivity measuring system for hygienic applications



More information and current pricing:

[www.id.endress.com/CLD18](http://www.id.endress.com/CLD18)

### Benefits:

- Unique hygienic design avoids contamination
- 3-A approval
- Compliant with EG 2023/2006 and 1935/2004
- Suitable for cleaning-in-place (CIP)
- Smart and easy integration into your plant infrastructure thanks to optional IO-Link protocol
- Compact design permits installation in small tubes without restricting the flow

### Specs at a glance

- **Measurement range** 200  $\mu\text{S}/\text{cm}$  to 1000  $\text{mS}/\text{cm}$  Cell constant k: 11.0  $1/\text{cm}$
- **Process temperature** -10 °C to 110 °C (14 °F to 230 °F)  
Sterilization: max. 130 °C at 6 bar abs up to 60 min (Max. 266 °F at 87 psi up to 60 min)
- **Process pressure** 13 bar abs up to 50 °C (188.5 psi up to 122 °F)  
7.75 bar abs at 110 °C (112 psi at 230 °F) 6.0 bar abs at 130 °C for max. 60 minutes (87 psi at 266 °F for max. 60 minutes)

**Field of application:** Smartec CLD18 is the cost-effective solution for all applications in beverage plants where small tubes are used and where the toroidal measurement is used as a switch function. The combination of a transmitter and a sensor is interference-free, easy-to-use and features a hygienic design that protects your products and processes from contamination. Smartec CLD18 ensures the Overall Equipment Effectiveness (OEE) of your plant thanks to fast and reliable CIP and optional IO-Link protocol.

---

## Features and specifications

---

### Conductivity

**Measuring principle**

Inductive

---

**Application**

Food and beverage industries

---

**Characteristic**

Specifically intended for use in beverage industry applications and especially suitable for:

Phase separation, control of CIP, concentration control, product monitoring, leakage monitoring

---

**Measurement range**

200  $\mu\text{S}/\text{cm}$  to 1000  $\text{mS}/\text{cm}$

Cell constant k: 11.0  $1/\text{cm}$

---

**Measuring principle**

Inductive conductivity measurement

---

**Design**

Hygienic design with FDA certified virgin PEEK

---

**Material**

Sensor: PEEK

Process connection 1.4435 (316L)

Seal: EPDM

---

**Process temperature**

-10 °C to 110 °C (14 °F to 230 °F)

Sterilization: max. 130 °C at 6 bar abs up to 60 min

(Max. 266 °F at 87 psi up to 60 min)

---

**Process pressure**

13 bar abs up to 50 °C (188.5 psi up to 122 °F)

7.75 bar abs at 110 °C (112 psi at 230 °F)

6.0 bar abs at 130 °C for max. 60 minutes

(87 psi at 266 °F for max. 60 minutes)

---

---

## Conductivity

---

**Temperature sensor**

Pt 1000 (class B)

---

**Connection**

Dairy pipe, aseptic-fitting DN40 and DN50, Clamp 2"  
ISO 2852, SMS-2", Varivent N DN 40-125  
Thread G1 1/2 SS, G1 1/2 PVC , Union nut 2 1/4 Inch PVC

---

**Ingres protection**

IP69

---

**Output / communication**

0/4...20mA  
IO-Link (option)

---

**Additional certifications**

3A, FDA, EHEDG  
EC Regulation No. 1935/2004

---

More information [www.id.endress.com/CLD18](http://www.id.endress.com/CLD18)