

# iTHERM ModuLine TM101

RTD or thermocouple temperature probe for direct installation in various industrial applications



from ₹26,998.60

Price as of 21.10.2021

More information and current pricing:

[www.in.endress.com/TM101](http://www.in.endress.com/TM101)

## Benefits:

- Excellent value for money and fast global delivery
- User-friendly product selection, smart design for easy maintenance
- Wide range of process connections
- Bluetooth® connectivity (optional)

## Specs at a glance

- **Accuracy** Class A acc. to IEC 60751 Class B acc. to IEC 60751 Class standard acc. to ASTM E230 Class 2 acc. to IEC 60584-2
- **Response time**  $t_{90}$  around 17 s depending on configuration
- **Max. process pressure (static)** depending on the configuration
- **Operating temperature range** Basic PT100 TF: -50 °C ...200 °C (-58 °F ...392 °F) Thermocouple: Typ K up to 600 °C (1.112 °F)
- **Max. immersion length on request** up to 1.000,0 mm (39")

**Field of application:** Basic thermometers offer reliable temperature measurement performance with basic sensor technology, a standard extension neck and a fixed, non-replaceable insert for use in non-hazardous areas. The devices are available with optional Bluetooth®-enabled head transmitters with 4 to 20 mA output or HART® communication, providing enhanced measurement accuracy and reliability compared to directly wired sensors.

## Features and specifications

Thermometer

Measuring principle

Resistance Temperature Detector

---

**Thermometer****Characteristic / Application**

Basic technologie

metric style

universal range of application

direct process contact

---

**Thermowell / protection tube**

without, direct process contact

---

**Insert / probe**

Basis Sensortechnologie

---

**Outer diameter protection tube / Insert**

Insert:

6,0 mm

---

**Max. immersion length on request**

up to 1.000,0 mm (39")

---

**Material protection tube/ thermowell**

Insert Material:

316L (1.4404)

Alloy 600 (2.4816)

---

**Thermometer****Process connection**

Thread:

G1/2", G1/4"

NPT1/2"

M18x1.5, M20x1.5

Cap-nut:

G1/2", G3/4"

Compression fitting, also spring  
load:

NPT1/2", G1/2"

---

**Tip shape**

straight

---

**Operating temperature range**

Basic PT100 TF:

-50 °C ...200 °C

(-58 °F ...392 °F)

Thermocouple:

Typ K up to 600 °C (1.112 °F)

---

**Max. process pressure (static)**

depending on the configuration

**Thermometer****Accuracy**

Class A acc. to IEC 60751

Class B acc. to IEC 60751

Class standard acc. to ASTM E230

Class 2 acc. to IEC 60584-2

---

**Response time**t<sub>90</sub> around 17 s

depending on configuration

---

**Integration head transmitter**

yes (4 ... 20 mA; HART)

---

More information [www.in.endress.com/TM101](http://www.in.endress.com/TM101)