

Digital 4-electrode conductivity sensor Memosens CLS82D

Memosens conductive conductivity sensor for hygienic applications in Life Sciences, Pharma and Food



More information and current pricing:

www.jp.endress.com/CLS82D

Benefits:

- Broad measurement range
- Hygienic design certified by EHEDG and 3-A
- Absolute loop safety thanks to Memosens and unique electrode connection surveillance
- Sterilizable and autoclavable
- Quality certificate stating the individual cell constant
- Logging of sensor-specific data for easy traceability and predictive maintenance
- Convenient maintenance strategy with Memobase Plus for easy calibration and sensor management

Specs at a glance

- **Measurement range** 1 μ S/cm to 500 mS/cm
- **Process temperature** -5 to 120 °C (23 to 248 °F) Sterilization: max. 140 °C at 6 bar for max. 45 min (Max. 284 °F at 87 psi for max. 45 min)
- **Process pressure** 17 bar abs at 20 °C (247 psi at 68 °F) 9 bar abs at 120 °C (131 psi at 248 °F)

Field of application: Memosens CLS82D is a hygienic, digital sensor for applications with widely varying conductivity values, where it performs reliably, safe and fast. Numerous certificates, various process connections and a small compact design ensure the perfect fit for your process. Memosens CLS82D is not the latest Memosens generation. To get information on the new Memosens CLS82E sensor with extended functionality, click [here](#).

Features and specifications

Conductivity

Measuring principle

Conductive

Application

Phase separation, chromatography, fermentation, CIP monitoring in small pipes, ultrafiltration

Characteristic

Conductivity sensor with a broad measurement range for all hygienic applications with advanced requirements to process safety

Measurement range

1 $\mu\text{S}/\text{cm}$ to 500 mS/cm

Measuring principle

4-electrode conductive conductivity sensor

Design

Certified hygienic design with FDA compliant materials, available as 120 mm sensor with PG13.5 and in many other standard process connections

Material

Process connection: stainless steel 1.4435 (316L)
Sensor element: platinum and ceramic

Dimension

Sensor diameter: 12 mm (0.47 inch)
Electrode length: depending on process connection

Process temperature

-5 to 120 °C (23 to 248 °F)
Sterilization: max. 140 °C at 6 bar for max. 45 min
(Max. 284 °F at 87 psi for max. 45 min)

Process pressure

17 bar abs at 20 °C (247 psi at 68 °F)
9 bar abs at 120 °C (131 psi at 248 °F)

Conductivity

Temperature sensor

Pt1000

Connection

Clamp 1,5", Clamp 2", Varivent F DN25, Varivent N DN40-DN125,
BioControl DN25, PG13,5, DN25 standard/40mm, DN25 B.Braun port/
65mm, Threat G1", Thread NPT 1"

Cable: Memosens connector

Ingres protection

IP 68 / NEMA type 6P

Additional certifications

3-A, hygienic design EHEDG, ASME BPE-2002

Pharma CoC, FDA, Regulation (EC) No.

1935/2004

More information www.jp.endress.com/CLS82D