

Proline Promass P 500 Coriolis flowmeter

Specialist for life sciences, as remote version
with up to 4 I/Os



More information and current pricing:

www.jp.endress.com/8P5B

Benefits:

- Highest process quality – fully compliant to industry requirements
- Fewer process measuring points – multivariable measurement (flow, density, temperature)
- Space-saving installation – no in/outlet run needs
- Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses
- Reduced complexity and variety – freely configurable I/O functionality
- Integrated verification – Heartbeat Technology

Specs at a glance

- **Max. measurement error** Mass flow (liquid): $\pm 0.10\%$ Volume flow (liquid): $\pm 0.10\%$ Mass flow (gas): $\pm 0.50\%$ Density (liquid): $\pm 0.0005 \text{ g/cm}^3$
- **Measuring range** 0 to 70 000 kg/h (0 to 2570 lb/min)
- **Medium temperature range** Standard: -50 to $+150$ °C (-58 to $+302$ °F) Option: -50 to $+205$ °C (-58 to $+401$ °F)
- **Max. process pressure** PN 40, Class 150, 20K
- **Wetted materials** Measuring tube: 1.4435 (316L) Connection: 1.4435 (316L); 1.4404 (316/316L)

Field of application: Promass P is the specialist for sterile processes in the life sciences industry. It is dedicated to biotech applications requiring highest compliance with guidelines and regulations. With its innovative remote transmitter Promass P 500 maximizes installation flexibility and operational safety in demanding environments. Heartbeat Technology ensures compliance and process safety at all times.

Features and specifications

Density/Concentration

Measuring principle

Coriolis

Product headline

Specialist for life sciences, as remote version with up to 4 I/Os. Dedicated to applications under sterile conditions in the life sciences industry.

Sensor features

Highest process quality – fully compliant to industry requirements. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space - saving installation – no in-/outlet run needs. ASME BPE, 3 - A and EHEDG conform & low delta ferrite. Electropolished measuring tube in 1.4435 (316L).

Transmitter features

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology.

Fast recovery from CIP/SIP. Remote version with up to 4 I/Os; hygienic sensor connection housing with IP69. Backlit display with touch control and WLAN access.

Nominal diameter range

DN 8 to 50 ($\frac{3}{8}$ to 2")

Wetted materials

Measuring tube: 1.4435 (316L)

Connection: 1.4435 (316L); 1.4404 (316/316L)

Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow, reference density, concentration

Density/Concentration**Max. measurement error**Mass flow (liquid): $\pm 0.10\%$ Volume flow (liquid): $\pm 0.10\%$ Mass flow (gas): $\pm 0.50\%$ Density (liquid): $\pm 0.0005\text{ g/cm}^3$

Measuring range0 to 70 000 kg/h (0 to 2570 lb/min)

Max. process pressurePN 40, Class 150, 20K

Medium temperature rangeStandard: -50 to $+150\text{ }^\circ\text{C}$ (-58 to $+302\text{ }^\circ\text{F}$)Option: -50 to $+205\text{ }^\circ\text{C}$ (-58 to $+401\text{ }^\circ\text{F}$)

Ambient temperature rangeStandard: -40 to $+60\text{ }^\circ\text{C}$ (-40 to $+140\text{ }^\circ\text{F}$)Option: -50 to $+60\text{ }^\circ\text{C}$ (-58 to $+140\text{ }^\circ\text{F}$)

Sensor housing material

1.4301 (304), corrosion resistant

Sensor connection housing (standard): AlSi10Mg, coated

Sensor connection housing (option): 1.4301 (304); 1.4404 (316L)

Transmitter housing materialAlSi10Mg, coated; 1.4409 (CF3M) similar to 316L; Polycarbonat

Degree of protection

Sensor remote version (standard): IP66/67, type 4X enclosure

Sensor remote version (option): IP69. Transmitter remote version:

IP66/67, Type 4X enclosure

Display/Operation

4-line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Density/Concentration

Outputs

4 outputs:

4-20 mA HART (active/passive)

4-20 mA WirelessHART

4-20 mA (active/passive)

Pulse/frequency/switch output (active/passive)

Double pulse output (active/passive)

Relay output

Inputs

Status input

4-20 mA input

Digital communication

HART, PROFIBUS DP, PROFIBUS PA, FOUNDATION Fieldbus, Modbus RS485, Profinet, Ethernet/IP, OPC-UA

Power supply

DC 24 V

AC 100 to 230 V

AC 100 to 230 V / DC 24 V (non-hazardous area)

Hazardous area approvals

ATEX, IECEx, cCSAus, NEPSI, INMETRO, EAC

Product safety

CE, C-tick, EAC marking

Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

Density/Concentration

Pressure approvals and certificates

PED, CRN

Material certificates

3.1 material

Hygienic approvals and certificates

3-A, EHEDG, ASME BPE, ISPE, cGMP

Liquids

Measuring principle

Coriolis

Product headline

Specialist for life sciences, as remote version with up to 4 I/Os. Dedicated to applications under sterile conditions in the life sciences industry.

Sensor features

Highest process quality – fully compliant to industry requirements. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space - saving installation – no in-/outlet run needs. ASME BPE, 3 - A and EHEDG conform & low delta ferrite. Electropolished measuring tube in 1.4435 (316L).

Transmitter features

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology.

Fast recovery from CIP/SIP. Remote version with up to 4 I/Os; hygienic sensor connection housing with IP69. Backlit display with touch control and WLAN access.

Nominal diameter range

DN 8 to 50 ($\frac{3}{8}$ to 2")

Liquids

Wetted materials

Measuring tube: 1.4435 (316L)

Connection: 1.4435 (316L); 1.4404 (316/316L)

Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow, reference density, concentration

Max. measurement error

Mass flow (liquid): ± 0.10 %

Volume flow (liquid): ± 0.10 %

Mass flow (gas): ± 0.50 %

Density (liquid): ± 0.0005 g/cm³

Measuring range

0 to 70 000 kg/h (0 to 2570 lb/min)

Max. process pressure

PN 40, Class 150, 20K

Medium temperature range

Standard: -50 to $+150$ °C (-58 to $+302$ °F)

Option: -50 to $+205$ °C (-58 to $+401$ °F)

Ambient temperature range

Standard: -40 to $+60$ °C (-40 to $+140$ °F)

Option: -50 to $+60$ °C (-58 to $+140$ °F)

Sensor housing material

1.4301 (304), corrosion resistant

Sensor connection housing (standard): AISi10Mg, coated

Sensor connection housing (option): 1.4301 (304); 1.4404 (316L)

Transmitter housing material

AISi10Mg, coated; 1.4409 (CF3M) similar to 316L; Polycarbonat

Liquids

Degree of protection

Sensor remote version (standard): IP66/67, type 4X enclosure

Sensor remote version (option): IP69. Transmitter remote version:
IP66/67, Type 4X enclosure

Display/Operation

4-line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Outputs

4 outputs:

4-20 mA HART (active/passive)

4-20 mA WirelessHART

4-20 mA (active/passive)

Pulse/frequency/switch output (active/passive)

Double pulse output (active/passive)

Relay output

Inputs

Status input

4-20 mA input

Digital communication

HART, PROFIBUS DP, PROFIBUS PA, FOUNDATION Fieldbus, Modbus
RS485, Profinet, Ethernet/IP, OPC-UA

Power supply

DC 24 V

AC 100 to 230 V

AC 100 to 230 V / DC 24 V (non-hazardous area)

Hazardous area approvals

ATEX, IECEx, cCSAus, NEPSI, INMETRO, EAC

Product safety

CE, C-tick, EAC marking

Liquids

Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

Pressure approvals and certificates

PED, CRN

Material certificates

3.1 material

Hygienic approvals and certificates

3-A, EHEDG, ASME BPE, ISPE, cGMP

Density

Measuring principle

Coriolis

Product Headline

Specialist for life sciences, as remote version with up to 4 I/Os.

Dedicated to applications under sterile conditions in the life sciences industry.

Sensor features

Highest process quality – fully compliant to industry requirements. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space - saving installation – no in-/outlet run needs.

ASME BPE, 3 - A and EHEDG conform & low delta ferrite.

Electropolished measuring tube in 1.4435 (316L).

Density

Transmitter features

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology.

Fast recovery from CIP/SIP. Remote version with up to 4 I/Os; hygienic sensor connection housing with IP69. Backlit display with touch control and WLAN access.

Gas

Measuring principle

Coriolis

Product headline

Specialist for life sciences, as remote version with up to 4 I/Os. Dedicated to applications under sterile conditions in the life sciences industry.

Hygienic approvals and certificates

cGMP

More information www.jp.endress.com/8P5B