

## iTHERM ModuLine TM101

RTD or thermocouple temperature probe for direct installation in various industrial applications



from **€54.00**

Price as of 09.08.2022

More information and current pricing:

[www.lasc.endress.com/TM101](http://www.lasc.endress.com/TM101)

### Benefits:

- Excellent value for money and fast global delivery
- User-friendly product selection, smart design for easy maintenance
- Wide range of process connections
- Bluetooth® connectivity (optional)

### Specs at a glance

- **Accuracy** Class A acc. to IEC 60751 Class B acc. to IEC 60751 Class standard acc. to ASTM E230 Class 2 acc. to IEC 60584-2
- **Response time**  $t_{90}$  around 17 s depending on configuration
- **Max. process pressure (static)** depending on the configuration
- **Operating temperature range** Basic PT100 TF: -50 °C ...200 °C (-58 °F ...392 °F) Thermocouple: Typ K up to 600 °C (1.112 °F)
- **Max. immersion length on request** up to 1.000,0 mm (39")

**Field of application:** Basic thermometers offer reliable temperature measurement performance with basic sensor technology, a standard extension neck and a fixed, non-replaceable insert for use in non-hazardous areas. The devices are available with optional Bluetooth®-enabled head transmitters with 4 to 20 mA output or HART® communication, providing enhanced measurement accuracy and reliability compared to directly wired sensors.

### Features and specifications

Thermometer

Measuring principle

Resistance Temperature Detector

---

## Thermometer

### **Characteristic / Application**

Basic technologie  
metric style  
universal range of application  
direct process contact

---

### **Thermowell / protection tube**

without, direct process contact

---

### **Insert / probe**

Basis Sensortechnologie

---

### **Outer diameter protection tube / Insert**

Insert:  
6,0 mm

---

### **Max. immersion length on request**

up to 1.000,0 mm (39")

---

### **Material protection tube/ thermowell**

Insert Material:  
316L (1.4404)  
Alloy 600 (2.4816)

---

### **Process connection**

Thread:  
G1/2", G1/4"  
NPT1/2"  
M18x1.5, M20x1.5  
Cap-nut:  
G1/2", G3/4"  
Compression fitting, also spring  
load:  
NPT1/2", G1/2"

---

### **Tip shape**

straight

---

## Thermometer

### Operating temperature range

Basic PT100 TF:

-50 °C ...200 °C

(-58 °F ...392 °F)

Thermocouple:

Typ K up to 600 °C (1.112 °F)

---

### Max. process pressure (static)

depending on the configuration

---

### Accuracy

Class A acc. to IEC 60751

Class B acc. to IEC 60751

Class standard acc. to ASTM E230

Class 2 acc. to IEC 60584-2

---

### Response time

t90 around 17 s

depending on configuration

---

### Integration head transmitter

yes (4 ... 20 mA; HART)

---

More information [www.lasc.endress.com/TM101](http://www.lasc.endress.com/TM101)