

## RIA15

### Loop-powered indicator for 4 to 20 mA or HART signals

For the indication of the 4 to 20 mA signal or the HART® values in the field or in the panel!



from **€136.00**

Price as of 23.04.2021

More information and current pricing:

[www.lasc.endress.com/RIA15](http://www.lasc.endress.com/RIA15)

#### Benefits:

- Display of 4 to 20 mA measured values or optionally up to four of a sensor's HART® process variables in all industries; Use as primary or secondary HART® master
- 5-digit measured value display with 17 mm (0.67") character height with dimension and bargraph; backlight can be activated
- Panel-mount housing (IP65) or field housing (IP66; Ex approval) as local display; Minimal installation depth
- No external power supply required; Voltage drop  $\leq 1$  V (HART®  $\leq 1.9$  V)
- Easy 3-key operation for configuring the device
- International approvals; marine approval
- SIL interference freeness acc. to EN 60508

#### Specs at a glance

- **Input** 1 x analogue 4...20 mA/HART®
- **Output** Not defined
- **Display** LCD 17 mm (0.67") 5-digit 7-segment bargraph Plain text display for unit/TAG Activatable backlight
- **Power Supply** Loop powered

**Field of application:** The process indicator is available with 4 to 20 mA or with HART® protocol. In the HART® version up to 4 measured values of one sensor can be indicated in alternation. For this the indicator can be set as primary or secondary HART® master and actively inquire the values from the sensor. The small voltage drop of  $< 1$  V ( $< 1.9$  V with HART®) is a huge advantage especially in Ex-applications, where in most cases only a reduced voltage is available.

---

## Features and specifications

---

### Process indicator & control units

**Measuring principle**

Loop powered indicators

---

**Measuring principle**

Loop-powered field indicator

---

**Function**

Display

---

**Display**

LCD 17 mm (0.67")

5-digit

7-segment bargraph

Plain text display for unit/TAG

Activatable backlight

---

**Power Supply**

Loop powered

---

**Input**

1 x analogue 4...20 mA/  
HART®

---

**Output**

Not defined

---

**Output**

Not defined

---

**Software functions**

Not defined

---

Process indicator & control units

**Certificates**

Non-hazardous area

ATEX

CSA

FM IS

EAC

IECEX

JPN Ex

NEPSI

---

**SIL**

Not defined

---

**Panel mounting**

field

panel mounting

---

Acquisition / Evaluation

**Measuring principle**

Display

---

**Function**

Display

---

**Acquisition / Evaluation****Certification**

ATEX II2(1)G Ex ib [ia Ga] IIC T6 Gb

CSA Ex ia, Cl. I, Div. 1, Gr. ABCD

FM IS, Cl. I, Div. 1, Gr. ABCD

IECEX Ex ib [ia Ga] IIC T6 Gb

Marine approval

---

**Input**1 x analogue 4...20 mA/HART®

---

**Auxiliary power supply / Loop power supply**Loop powered

---

**Dimensions (wxhxd)**

Panel housing:

96 x 48 x 41.5 mm

(3.78" x 1.89" x 1.64")

Plastic or aluminum field housing:

131 x 81.5 x 55.5 mm

(5.16" x 3.21" x 2.19")

---

**Operation**3 keys

---

Acquisition / Evaluation

**Display**

LCD 17 mm (0.67")

5-digit

7-segment bargraph

Plain text display for unit/TAG

Activatable backlight

---

More information [www.lasc.endress.com/RIA15](http://www.lasc.endress.com/RIA15)