

TAF16

High temperature TC thermometer

Applicable for cement production, steel treatment, incinerators and fluidized bed furnaces



Mais informações e preço atual:

www.pt.endress.com/TAF16

Benefícios:

- Long lifetime by usage of innovative thermowell materials with increased wear and chemical resistance
- Long term stable measurement due to sensor protection with non-porous materials
- Flexible product selection by modular design
- Optimized life cycle costs by means of replaceable spare parts

Especificações resumidas

- **Accuracy** class 2 acc. to IEC 60584
- **Max. process pressure (static)** at 20 °C: 1 bar (15 psi)
- **Operating temperature range** Type K: -40 C ...1.100 C (-40 F ...2.012 F) Type J: -40 C ...750 C (-40 F ...1.382 F) Type N: -40 C ...1.150 C (-40 F ...2.102 F) Type S: 0 C ...1.400 C (32 F ...2.552 F)
- **Max. immersion length on request** up to 4.525,00 mm (178,15")

Campo de aplicação: Measuring points with extremely high process temperatures require these special thermometers with ceramic or metal thermowells as well as thermocouples made from special metals, such as platinum and rhodium. The thermowell made from special materials protects from mechanical and chemical damages in the process and increases the life span of the used sensors. This leads to: Cost savings for maintenance of the measuring point, quality improvements of the products and increased plant safety.

Características e especificações

Thermometer

Measuring principle

Thermocouple

Characteristic / Application

metric style

modular temperature assembly

high temperature probe (furnace)

incl. thermowell / protection tube (metal)

Thermowell / protection tube

welded protection tube

ceramic protection tube

Insert / probe

mineral insulated (MI), flexible

ceramic capillary, rigid

Outer diameter protection tube / Insert

14,0 mm (0,55")

15,0 mm (0,59")

17,2 mm (0,68")

18,0 mm (0,71")

21,3 mm (0,84")

22,0 mm (0,87")

26,7 mm (1,05")

28,0 mm (1,10")

Max. immersion length on request

up to 4.525,00 mm (178,15")

Thermometer

Material protection tube/ thermowell

1.4401 (316)
1.4749 (~446)
1.4841 (310)
Alloy 600 (2.4816)
Alloy 601 (2.4851)
Incoloy 800HT (1.4959)
Kanthal AF
Kanthal Super
NiCo
Siliciumnitrid(SiN)

Process connection

compression fitting:
G1/2"
G3/4"
G1"
G1 1/4"
G1 1/2"
adjustable Flange

Tip shape

straight

Operating temperature range

Type K:
-40 C ...1.100 C
(-40 F ...2.012 F)
Type J:
-40 C ...750 C
(-40 F ...1.382 F)
Type N:
-40 C ...1.150 C
(-40 F ...2.102 F)
Type S:
0 C ...1.400 C
(32 F ...2.552 F)

Thermometer

Max. process pressure (static)

at 20 °C: 1 bar (15 psi)

Accuracy

class 2 acc. to IEC 60584

Integration head transmitter

yes (4 ... 20 mA; HART; PROFIBUS PA; FOUNDATION
FIELDBUS)

Certification

SIL (transmitter only)

Mais informações www.pt.endress.com/TAF16