

iTHERM CompactLine TM311 - Pt100 temperature sensor

Compact, accurate and fast RTD sensor with IO-Link for sterile applications



FLEX

Benefits:

- Fast installation and easy commissioning:
 - Compact dimensions for installation in tight spaces
 - Standard M12 connector with IP69 for easy electrical connection
 - Recommended process immersion lengths for optimum measurement
 - Preset temperature range
- Excellent temperature measurement performance:
 - Short response times as low as 1.5 s (t90)
 - High sensor accuracy even with short immersion lengths
 - Improved measuring accuracy with transmitter-sensor matching
- Safe and reliable operation:
 - Device safety to EN 610101-1 and CSA C/US
 - Electromagnetic compatibility (NAMUR NE 21)
 - Device diagnostic information (NAMUR NE 43)
 - Hygienic design manufactured from high-grade stainless steel
 - Marine approval

from **€64.00**

Price as of 28.05.2022

More information and current pricing:

www.pt.endress.com/TM311

Specs at a glance

- **Accuracy** class A acc. to IEC 60751
- **Response time** t50 = 1 s t90 = 1.5 s
- **Max. process pressure (static)** at 20 °C: 50 bar (725 psi)
- **Operating temperature range** PT 100: -50 °C ...200 °C (-58 °F ...392 °F)
- **Max. immersion length on request** up to 600,00 mm (23,62")

Field of application: iTHERM CompactLine TM311 sanitary thermometer provides accurate and fast process temperature measurements in hygienic and aseptic applications. Its temperature

sensor offers a 4-wire connection or feeds into a smart temperature transmitter with 4 to 20 mA, IO-Link (auto-detect) or switch output. Featuring TipSens technology, the RTD (Pt100; Class A) delivers response times as low as 1.5 s (t90) for optimum process control. This versatile device is a great choice to drive plant standardization.

Features and specifications

Thermometer

Measuring principle

Resistance Temperature Detector

Characteristic / Application

metric and imperial style
compact temperature probe
fast response time
high accuracy
standard and hygienic design
hygienic process connection
threaded process connection

Thermowell / protection tube

without
incl. thermowell
incl. T-/ellbow thermowell

Insert / probe

pipe version, isolated wires, not flexible

Outer diameter protection tube / Insert

3,0 mm (0,12")
6,0 mm (0,24")

Max. immersion length on request

up to 600,00 mm (23,62")

Material protection tube/ thermowell

1.4435 Delta-Ferrit < 1%
316L

Thermometer

Process connection

compression fitting

Thread

weld in adapter

clamp connections acc. to ISO2852

screwed pipe joint acc. to DIN 11851

aseptic screwed pipe joint acc. to DIN 11864-1

metallic sealing system

thread acc. to ISO 228 for liquid adaptor

Varivent

SMS 1147

T- and elbow pieces

Tip shape

straight

reduced

Surface roughness Ra

0,76 µm (29,92 µin)

0,38 µm (14,96 µin)

0,38 µm (14,96 µin) electropolished

Operating temperature range

PT 100:

-50 °C ...200 °C

(-58 °F ...392 °F)

Max. process pressure (static)

at 20 °C: 50 bar (725 psi)

Accuracy

class A acc. to IEC 60751

Response time

t₅₀ = 1 s

t₉₀ = 1.5 s

Thermometer

Integration head transmitter

no (4...20mA Signal, IO-Link)

Certification

3A, EHEDG, ASME BPE, FDA, TSE
1935/2004, 2023/2006, 10/2011

DNVGL, BV

cCSAus

EAC

RCM

More information www.pt.endress.com/TM311