

TR63

Explosion-proof Pt100 Thermometer

Safe monitoring of process temperatures in challenging applications e. g. in the Oil & Gas industry



More information and current pricing:

www.sg.endress.com/TR63

Benefits:

- Types of protection for use in hazardous locations: Intrinsic safety (Ex i.a.), flameproof (Ex d), non-sparking (Ex nA)
- High degree of flexibility thanks to modular design with standard terminal heads as per DIN EN 50446 and customer-specific immersion lengths
- Optionally fast response time with tapered tip form
- Variable selection of process connections: thread, compression fitting or flange
- Extension neck, nipple union version, to protect the head transmitter from overheating
- Marine approval

Specs at a glance

- **Accuracy** class A acc. to IEC 60751 class AA acc. to IEC 60751
- **Response time** depending on configuration $t_{50} = 4\text{ s}$ $t_{90} = 8\text{ s}$
- **Max. process pressure (static)** at 20 °C: 100 bar (1.450 psi)
- **Operating temperature range** PT100 TF StrongSens: -50 °C ...500 °C (-58 °F ...932 °F) PT100 WW: -200 °C ...600 °C (-328 °F ...1.112 °F) PT100 TF: -50 °C ...400 °C (-58 °F ...752 °F)
- **Max. immersion length on request** up to 10.000,00 mm (393,70")

Field of application: The robust thermometer is designed for use in demanding and safety relevant applications e.g. in the Chemical, Oil & Gas and Energy industry. Harsh environments, corrosive substances and highest pressures can be handled by the use of robust protection tubes and special materials. An optional head transmitter with all common

communication protocols makes the device ready to use with enhanced measurement accuracy and reliability compared to directly wired sensors. Flexible configuration possible.

Features and specifications

Thermometer

Measuring principle

Resistance Temperature Detector

Characteristic / Application

US style

modular temperature assembly

for heavy duty applications

suitable for hazardous areas

flanged process connection

with neck

incl. thermowell / protection tube (metal)

Thermowell / protection tube

welded protection tube

Insert / probe

mineral insulated (MI), flexible

Thermometer

Outer diameter protection tube / Insert

1/4" SCH80

1/2" SCH80

1/2" SCH40

3/4" SCH80

3/4" SCH40

Max. immersion length on request

up to 10.000,00 mm (393,70")

Material protection tube/ thermowell

1.4404 (316)

1.4749 (~446)

Optional coating

Not defined

Thermometer

Process connection

male thread:

NPT1/2"

NPT3/4"

NPT1"

flange:

ASME 1" 150 RF (B16.5)

ASME 1" 300 RF (B16.5)

ASME 1" 600 RF (B16.5)

ASME 1,5" 150 RF (B16.5)

ASME 1,5" 300 RF (B16.5)

ASME 1,5" 600 RF (B16.5)

ASME 2" 300 RF (B16.5)

ASME 2" 600 RF (B16.5)

Tip shape

straight

reduced

Surface roughness Ra

Not defined

Thermometer**Operating temperature range**

PT100 TF StrongSens:

-50 °C ...500 °C

(-58 °F ...932 °F)

PT100 WW:

-200 °C ...600 °C

(-328 °F ...1.112 °F)

PT100 TF:

-50 °C ...400 °C

(-58 °F ...752 °F)

Max. process pressure (static)

at 20 °C: 100 bar (1.450 psi)

Accuracy

class A acc. to IEC 60751

class AA acc. to IEC 60751

Response time

depending on configuration

t₅₀ = 4 st₉₀ = 8 s

Integration head transmitteryes (4 ... 20 mA; HART; PROFIBUS PA; FOUNDATION
FIELDBUS)

Thermometer

Ex - approvals

ATEX II

IECEX

NEPSI

EAC Ex

Explosion proof

Certification

Gost Metrology

SIL (transmitter only)

Marine approval

More information www.sg.endress.com/TR63