

# Proline Promass I 100 Coriolis flowmeter

Combines in-line viscosity and flow measurement with an ultra-compact transmitter



More information and current pricing:

[www.sg.endress.com/811B](http://www.sg.endress.com/811B)

## Benefits:

- Energy-saving – full bore design enables minimal pressure loss
- Fewer process measuring points – multivariable measurement (flow, density, temperature)
- Space-saving installation – no in/outlet run needs
- Space-saving transmitter – full functionality on smallest footprint
- Time-saving local operation without additional software and hardware – integrated web server
- Integrated verification – Heartbeat Technology

## Specs at a glance

- **Max. measurement error** Mass flow (liquid):  $\pm 0.1\%$  Volume flow (liquid):  $\pm 0.1\%$  Mass flow (gas):  $\pm 0.5\%$  Density (liquid):  $\pm 0.0005 \text{ g/cm}^3$
- **Measuring range** 0 to 180 000 kg/h (0 to 6600 lb/min)
- **Medium temperature range**  $-50$  to  $+150 \text{ }^\circ\text{C}$  ( $-58$  to  $+302 \text{ }^\circ\text{F}$ )
- **Max. process pressure** PN 100, Class 600, 63K
- **Wetted materials** Measuring tube: Titanium grade 9 Connection: Titanium grade 2

**Field of application:** The straight single-tube design of the Promass I 100, provides the regular Coriolis flowmeter outputs of mass flow, density and temperature, additionally it provides in-line viscosity measurement as an optional output. Combined with the smallest transmitter housing available today it delivers full performance on the smallest footprint. Promass I 100 will be the preferred choice for system integrators, skid builders and equipment manufacturers.

---

## Features and specifications

---

### Density/Concentration

**Measuring principle**

Coriolis

**Product headline**

Combines in-line viscosity and flow measurement with an ultra-compact transmitter.

Measuring liquids and gases in applications requiring low pressure loss and gentle fluid treatment.

**Sensor features**

Energy - saving – full-bore design enables minimal pressure loss. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space - saving installation – no in-/outlet run needs. Straight, easy-to-clean single-tube system. TMB technology. Measuring tube made of Titanium.

**Transmitter features**

Space - saving transmitter – full functionality on the smallest footprint. Time - saving local operation without additional software and hardware – integrated web server. Integrated verification – Heartbeat Technology. Robust, ultra-compact transmitter housing. Highest degree of protection: IP69. Local display available.

**Nominal diameter range**

DN 8 to 80 ( $\frac{3}{8}$  to 3")

**Wetted materials**

Measuring tube: Titanium grade 9

Connection: Titanium grade 2

**Measured variables**

Mass flow, density, temperature, volume flow, corrected volume flow, reference density, concentration, viscosity

---

---

**Density/Concentration****Max. measurement error**Mass flow (liquid):  $\pm 0.1\%$ Volume flow (liquid):  $\pm 0.1\%$ Mass flow (gas):  $\pm 0.5\%$ Density (liquid):  $\pm 0.0005\text{ g/cm}^3$ 

---

**Measuring range**0 to 180 000 kg/h (0 to 6600 lb/min)

---

**Max. process pressure**PN 100, Class 600, 63K

---

**Medium temperature range** $-50$  to  $+150\text{ }^\circ\text{C}$  ( $-58$  to  $+302\text{ }^\circ\text{F}$ )

---

**Ambient temperature range**Standard:  $-40$  to  $+60\text{ }^\circ\text{C}$  ( $-40$  to  $+140\text{ }^\circ\text{F}$ )Option:  $-50$  to  $+60\text{ }^\circ\text{C}$  ( $-58$  to  $+140\text{ }^\circ\text{F}$ )

---

**Sensor housing material**1.4301/1.4307 (304L), corrosion resistant

---

**Transmitter housing material**

Compact: AlSi10Mg, coated

Compact/ultra - compact: 1.4301 (304)

---

**Degree of protection**

Standard: IP66/67, type 4X enclosure

Option: IP69

---

**Display/Operation**

4 - line backlit display available (no local operation)

Configuration via web browser and operating tools possible

---

**Outputs**

4 - 20 mA HART (active)

Pulse/frequency/switch output (passive)

---

---

**Density/Concentration****Inputs**

None

---

**Digital communication**

HART, Modbus RS485, EtherNet/IP, PROFIBUS DP, PROFINET

---

**Power supply**

DC 20 to 30 V

---

**Hazardous area approvals**

ATEX, IECEx, cCSAus, INMETRO, NEPSI, EAC

---

**Product safety**

CE, C-Tick, EAC marking

---

**Metrological approvals and certificates**

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

---

**Pressure approvals and certificates**

PED, CRN

---

**Material certificates**

3.1 material

---

**Hygienic approvals and certificates**

3-A, EHEDG, cGMP

---

**Gas****Measuring principle**

Coriolis

## Gas

**Product headline**

Combines in-line viscosity and flow measurement with an ultra-compact transmitter.

Measuring liquids and gases in applications requiring low pressure loss and gentle fluid treatment.

**Sensor features**

Energy - saving – full-bore design enables minimal pressure loss. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space - saving installation – no in-/outlet run needs. Straight, easy-to-clean single-tube system. TMB technology. Measuring tube made of Titanium.

**Transmitter features**

Space - saving transmitter – full functionality on the smallest footprint. Time - saving local operation without additional software and hardware – integrated web server. Integrated verification – Heartbeat Technology. Robust, ultra-compact transmitter housing. Highest degree of protection: IP69. Local display available.

**Nominal diameter range**

DN 8 to 80 ( $\frac{3}{8}$  to 3")

**Wetted materials**

Measuring tube: Titanium grade 9

Connection: Titanium grade 2

**Measured variables**

Mass flow, density, temperature, volume flow, corrected volume flow, reference density, concentration, viscosity

**Max. measurement error**

Mass flow (liquid):  $\pm 0.1$  %

Volume flow (liquid):  $\pm 0.1$  %

Mass flow (gas):  $\pm 0.5$  %

Density (liquid):  $\pm 0.0005$  g/cm<sup>3</sup>

## Gas

**Measuring range**

0 to 180 000 kg/h (0 to 6600 lb/min)

---

**Max. process pressure**

PN 100, Class 600, 63K

---

**Medium temperature range**

-50 to +150 °C (-58 to +302 °F)

---

**Ambient temperature range**

Standard: -40 to +60 °C (-40 to +140 °F)

Option: -50 to +60 °C (-58 to +140 °F)

---

**Sensor housing material**

1.4301/1.4307 (304L), corrosion resistant

---

**Transmitter housing material**

Compact: AlSi10Mg, coated

Compact/ultra - compact: 1.4301 (304)

---

**Degree of protection**

Standard: IP66/67, type 4X enclosure

Option: IP69

---

**Display/Operation**

4 - line backlit display available (no local operation)

Configuration via web browser and operating tools possible

---

**Outputs**

4 - 20 mA HART (active)

Pulse/frequency/switch output (passive)

---

**Inputs**

None

---

**Digital communication**

HART, Modbus RS485, EtherNet/IP, PROFIBUS DP, PROFINET

---

---

**Gas****Power supply**

DC 20 to 30 V

---

**Hazardous area approvals**

ATEX, IECEx, cCSAus, INMETRO, NEPSI

---

**Metrological approvals and certificates**

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

---

**Pressure approvals and certificates**

PED, CRN

---

**Material certificates**

3.1 material

---

**Hygienic approvals and certificates**

3-A, EHEDG, cGMP

---

**Viscosity****Measuring principle**

Coriolis

---

**Product headline**

Combines in-line viscosity and flow measurement with an ultra-compact transmitter.

Measuring liquids and gases in applications requiring low pressure loss and gentle fluid treatment.

---

**Sensor features**

Energy - saving – full-bore design enables minimal pressure loss. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space - saving installation – no in-/outlet run needs. Straight, easy-to-clean single-tube system. TMB technology. Measuring tube made of Titanium.

## Viscosity

---

### Transmitter features

Space - saving transmitter – full functionality on the smallest footprint.  
Time - saving local operation without additional software and hardware – integrated web server. Integrated verification – Heartbeat Technology.  
Robust, ultra-compact transmitter housing. Highest degree of protection: IP69. Local display available.

---

### Nominal diameter range

DN 8 to 80 ( $\frac{3}{8}$  to 3")

---

### Wetted materials

Measuring tube: Titanium grade 9  
Connection: Titanium grade 2

---

### Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow, reference density, concentration, viscosity

---

### Max. measurement error

Mass flow (liquid):  $\pm 0.1$  %  
Volume flow (liquid):  $\pm 0.1$  %  
Mass flow (gas):  $\pm 0.5$  %  
Density (liquid):  $\pm 0.0005$  g/cm<sup>3</sup>

---

### Measuring range

0 to 180 000 kg/h (0 to 6600 lb/min)

---

### Max. process pressure

PN 100, Class 600, 63K

---

### Medium temperature range

-50 to +150 °C (-58 to +302 °F)

---

### Ambient temperature range

Standard: -40 to +60 °C (-40 to +140 °F)  
Option: -50 to +60 °C (-58 to +140 °F)

---



---

## Viscosity

**Sensor housing material**

1.4301/1.4307 (304L), corrosion resistant

---

**Transmitter housing material**

Compact: AlSi10Mg, coated

Compact/ultra - compact: 1.4301 (304)

---

**Degree of protection**

Standard: IP66/67, type 4X enclosure

Option: IP69

---

**Display/Operation**

4 - line backlit display available (no local operation)

Configuration via web browser and operating tools possible

---

**Outputs**

4 - 20 mA HART (active)

Pulse/frequency/switch output (passive)

---

**Inputs**

None

---

**Digital communication**

HART, Modbus RS485, EtherNet/IP, PROFIBUS DP, PROFINET

---

**Power supply**

DC 20 to 30 V

---

**Hazardous area approvals**

ATEX, IECEx, cCSAus, INMETRO, NEPSI, EAC

---

**Product safety**

CE, C-Tick, EAC marking

---

## Viscosity

### **Metrological approvals and certificates**

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

---

### **Pressure approvals and certificates**

PED, CRN

---

### **Material certificates**

3.1 material

---

### **Hygienic approvals and certificates**

3-A, EHEDG, cGMP

---

## Liquids

### **Measuring principle**

Coriolis

---

### **Product headline**

Combines in-line viscosity and flow measurement with an ultra-compact transmitter.

Measuring liquids and gases in applications requiring low pressure loss and gentle fluid treatment.

---

### **Sensor features**

Energy - saving – full-bore design enables minimal pressure loss. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space - saving installation – no in-/outlet run needs. Straight, easy-to-clean single-tube system. TMB technology. Measuring tube made of Titanium.

---

## Liquids

### Transmitter features

Space - saving transmitter – full functionality on the smallest footprint.  
Time - saving local operation without additional software and hardware  
– integrated web server. Integrated verification – Heartbeat Technology.  
Robust, ultra-compact transmitter housing. Highest degree of protection:  
IP69. Local display available.

---

### Nominal diameter range

DN 8 to 80 ( $\frac{3}{8}$  to 3")

---

### Wetted materials

Measuring tube: Titanium grade 9

Connection: Titanium grade 2

---

### Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow,  
reference density, concentration, viscosity

---

### Max. measurement error

Mass flow (liquid):  $\pm 0.1$  %

Volume flow (liquid):  $\pm 0.1$  %

Mass flow (gas):  $\pm 0.5$  %

Density (liquid):  $\pm 0.0005$  g/cm<sup>3</sup>

---

### Measuring range

0 to 180 000 kg/h (0 to 6600 lb/min)

---

### Max. process pressure

PN 100, Class 600, 63K

---

### Medium temperature range

-50 to +150 °C (-58 to +302 °F)

---

### Ambient temperature range

Standard: -40 to +60 °C (-40 to +140 °F)

Option: -50 to +60 °C (-58 to +140 °F)

---

### Sensor housing material

1.4301/1.4307 (304L), corrosion resistant

---

## Liquids

---

### Transmitter housing material

Compact: AlSi10Mg, coated

Compact/ultra - compact: 1.4301 (304)

---

### Degree of protection

Standard: IP66/67, type 4X enclosure

Option: IP69

---

### Display/Operation

4 - line backlit display available (no local operation)

Configuration via web browser and operating tools possible

---

### Outputs

4 - 20 mA HART (active)

Pulse/frequency/switch output (passive)

---

### Inputs

None

---

### Digital communication

HART, Modbus RS485, EtherNet/IP, PROFIBUS DP, PROFINET

---

### Power supply

DC 20 to 30 V

---

### Hazardous area approvals

ATEX, IECEx, cCSAus, INMETRO, NEPSI, EAC

---

### Product safety

CE, C-Tick, EAC marking

---

### Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

---

## Liquids

### **Pressure approvals and certificates**

PED, CRN

---

### **Material certificates**

3.1 material

---

### **Hygienic approvals and certificates**

3-A, EHEDG, cGMP

---

More information [www.sg.endress.com/8I1B](http://www.sg.endress.com/8I1B)