

## Radiometric level and density measurement Gamma Source FSG60

Gamma radiation source ( $^{137}\text{Cs}$ ) for radiometric level, point level, density and interface measurement



### Benefits:

- Specially constructed source capsule conforms to strictest safety requirements:  
Typically class C66646 to ISO 2919
- Point source in special source container ensures simple handling and easy installation
- Choice of activity ensures optimized dosage for your application
- High cost-effectiveness due to long half-life time

### Specs at a glance

- **Process pressure absolute / max. overpressure limit** Any

More information and current pricing:

[www.si.endress.com/FSG60](http://www.si.endress.com/FSG60)

**Field of application:** The Gamma Source FSG60 has a very long lifetime thanks to its long half-life time. Common used standard isotope in the industrial process measurement.

## Features and specifications

Continuous / Liquids

### Measuring principle

Radiometric

### Characteristic / Application

Source

Isotope: Caesium 137

Half-life: 30 years

---

**Continuous / Liquids**

---

**Specialities**

Double seal

Steel: 1.4541 (321 S 18)

Classification C66646 ISO 2919

---

**Ambient temperature**

-20°C ... +250 °C

(-4°F ... 482 °F)

---

**Process pressure absolute / max. overpressure  
limit**

Any

---

**Pressure measuring range**

Any

---

**Components**

Installed in source container

---

**Continuous / Solids**

---

**Measuring principle**

Radiometric

---

**Characteristic / Application**

Source

Isotope: Caesium 137

Half-life: 30 years

---

**Specialities**

Double seal

Steel: 1.4541 (321 S 18)

Classification C66646 ISO 2919

Activity calculation with

Applicator

---

**Continuous / Solids****Ambient temperature**

-20°C ... +250 °C

(-4°F ... 482 °F)

---

**Process pressure absolute / max. overpressure****limit**

Any

---

**Components**

Installed in source container

---

**Density****Measuring principle**

Radiometric Density

---

**Characteristic / Application**

Source

Isotope: Caesium 137

Half-life: 30 years

---

**Ambient temperature**

-20 °C ... +250 °C

---

**Specialities**

Double seal

Steel: 1.4541 (321 S 18)

Classification: C66646 ISO

2919

Activity calculation with

Applicator

---

**Components**

Installed in source container

---

**Point Level / Liquids****Measuring principle**

Radiometric Limit

---

**Point Level / Liquids****Characteristic / Application**

Source  
Isotope: Caesium 137  
Half-life: 30 years

---

**Specialities**

Double seal  
Steel: 1.4541 (321 S 18)  
Classification C66646 ISO 2919  
Activity calculation with  
Applicator

---

**Ambient temperature**

-20°C ... +250 °C  
(-4°F ... 482 °F)

---

**Process pressure absolute / max. overpressure  
limit**

Any

---

**Components**

Installed in source container

---

**Point Level / Solids****Measuring principle**

Radiometric Limit

---

**Characteristic / Application**

Source  
Isotope: Caesium 137  
Half-life: 30 years

---

**Specialities**

Double seal  
Steel: 1.4541 (321 S 18)  
Classification C66646 ISO 2919  
Activity calculation with  
Applicator

---

## Point Level / Solids

---

### Ambient temperature

-20°C ... +250 °C  
(-4°F ... 482 °F)

---

### Process pressure absolute / max. overpressure

**limit**

Any

---

### Components

Installed in source container

---

More information [www.si.endress.com/FSG60](http://www.si.endress.com/FSG60)