

Dosimag Electromagnetic flowmeter

Flowmeter with hygienic design, highest repeatability and an ultra-compact sensor



More information and current pricing:

www.sg.endress.com/5BH

Benefits:

- High process safety – high measuring accuracy and repeatability in shortest filling time
- Energy-saving flow measurement – no pressure loss due to cross-section constriction
- Maintenance-free – no moving parts
- Versatile and time-saving wiring – plug connector
- Industry-optimized – ultra-compact design
- For hygiene requirements – stainless steel housing

Specs at a glance

- **Max. measurement error** $\pm 0.25\%$ o.r. ± 1 to 4 m/s (3.3 to 13 ft/s) $\pm 0.5\%$ o.r. ± 1 mm/s (0.04 in/s) $\pm 5\%$ o.r.
- **Measuring range** 0.14 to 1.66 l/s (0.035 to 0.44 gal/s)
- **Medium temperature range** Seal material EPDM: -20 to $+130$ °C (-4 to $+266$ °F) Seal material Silicone: -20 to $+130$ °C (-4 to $+266$ °F) Seal material Viton: 0 to $+150$ °C ($+32$ to $+302$ °F)
- **Max. process pressure** PN 16
- **Wetted materials** Liner: PFA Electrodes: 1.4435 (316L); Alloy C22, 2.4602 (UNS N06022), Tantalum, Platinum

Field of application: Dosimag is specially designed for filling and bottling applications of conductive liquids. It measures volume directly. Designed for applications where space is a premium, Dosimag will be the preferred choice for system integrators, skid builders and equipment manufacturers.

Features and specifications

Liquids

Measuring principle

Electromagnetic

Product headline

Flowmeter with hygienic design, highest repeatability and an ultra-compact sensor. For demanding dosing and filling applications.

Sensor features

High process safety – high measuring accuracy and repeatability in shortest filling time. Energy-saving flow measurement – no pressure loss due to cross section constriction. Maintenance-free – no moving parts. Wetted materials CIP, SIP cleanable. Nominal diameter: DN 4 to 25 ($\frac{1}{8}$ to 1").

Transmitter features

Versatile and time-saving wiring – plug connector. Industry-optimized – ultra-compact design. For hygienic requirements – stainless steel housing. Pulse/frequency/switch output, Modbus RS485. Custody transfer approvals (MID, NTEP).

Nominal diameter range

DN 4 ($\frac{5}{32}$ "), 8 ($\frac{5}{16}$ "), 15 ($\frac{1}{2}$ "), 25 (1")

Wetted materials

Liner: PFA

Electrodes: 1.4435 (316L); Alloy C22, 2.4602 (UNS N06022),
Tantalum,
Platinum

Measured variables

Volume flow

Max. measurement error

± 0.25 % o.r. ± 1 to 4 m/s (3.3 to 13 ft/s)

± 0.5 % o.r. ± 1 mm/s (0.04 in/s)

± 5 % o.r.

Measuring range

0.14 to 1.66 l/s (0.035 to 0.44 gal/s)

Liquids

Max. process pressure

PN 16

Medium temperature range

Seal material EPDM: -20 to +130 °C (-4 to +266 °F)

Seal material Silicone: -20 to +130 °C (-4 to +266 °F)

Seal material Viton: 0 to +150 °C (+32 to +302 °F)

Ambient temperature range

-40 to +60 °C (-40 to +140 °F)

Sensor housing material

1.4308 (304)

Transmitter housing material

1.4308 (304)

Degree of protection

IP66/67, type 4X enclosure

Display/Operation

No local Operation

Configuration via operating tools possible

Outputs

Pulse/frequency/switch output (passive)

Inputs

None

Digital communication

Modbus RS485

Power supply

DC 20 to 30 V

Hazardous area approvals

ATEX, IECEx, cCSAus

Liquids

Product safety

CE

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc.to ISO/IEC 17025)

NTEP

Material certificates

3.1 material

Hygienic approvals and certificates

Sanitary approval: 3-A, EHEDG, seals acc. to FDA (except EPDM)

More information www.sg.endress.com/5BH