

4-channel transmitter

Liquiline CM444

Expandable multiparameter field device for all industries



More information and current pricing:

www.si.endress.com/CM444

Benefits:

- **Clever simplicity:**
One controller for all parameters and applications, intuitive user interface, automatic sensor recognition, hot plug & play with pre-calibrated Memosens sensors.
- **Highest flexibility:**
Universal modules for all parameters minimize spare part stock and allow for easy 1-click extension to up to 8 channels at any time.
- **Seamless system integration:**
Unique portfolio of communication standards suits every distributed control system (DCS).
- **Simple and safe commissioning:**
Saving configuration on SD card enables fast set-up on duplicate installations.
- **Process control from a distance:**
Integrated web server that allows the operator to remotely view diagnostic data, perform configurations, or access device parameters in any web browser - even via Smartphone.
- **Higher availability, lower costs:**
Heartbeat Technology enables status-oriented maintenance and easy verification of the entire measuring point and helps to carry out optimization measures.

Specs at a glance

- **Input** 1 to 4x Memosens digital input 2x 0/4 to 20mA Input optional 2 to 4x Digital input optional

Output / communication 2 to 8x 0/4 to 20 mA current outputs, alarmrelay, 4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

- **Ingres protection** IP66 / IP 67

Field of application: The Liquiline CM444 transmitter allows you to connect up to 4 Memosens sensors of your choice from over 12 measurement parameters. It offers automatic sensor recognition, flexible expandability, and standardized spare parts with all other devices of the Liquiline platform. With its inputs, outputs, controllers, and math modules, you can even control cleaning systems or dosing pumps. Heartbeat Technology helps you find the ideal balance between measuring point availability and maintenance costs.

Features and specifications

Conductivity

Measuring principle

Conductive

Application

Modular 4 wire controller

Multichannel: 1 to 4 digital channels for Memosens protocol

Multiparameter: pH, redox, ISFET, conductivity inductive and conductive, dissolved oxygen, nitrate and turbidity

4 sensors connectable in any combination

Functionality modular extendable at any time

Plug and play for modules and sensors

Characteristic

Robust plastic housing

All non-ex applications

Design

2 to 4x Memosens input, 2 to 8x current output

Alarmrelay, 4x relay, SD card for software update and copy & paste of setup

Conductivity

Material

Housing base: PC-FR

Housing seal: EPDM

Dimension

237 x 194 x 162 mm

9.33 x 7.64 x 6.38 inch

Process temperature

-20 to 55 °C (0 to 130 °F)

Ingres protection

IP66 / IP 67

Input

1 to 4x Memosens digital input

2x 0/4 to 20mA Input optional

2 to 4x Digital input optional

Output / communication

2 to 8x 0/4 to 20 mA current outputs, alarmrelay,

4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

Additional certifications

EAC, cCSAus

pH

Measuring principle

Potentiometric

Application

Modular 4 wire controller

Multichannel: 1 to 4 digital channels for Memosens protocol

Multiparameter: pH, redox, ISFET, conductivity inductive and conductive, dissolved oxygen, nitrate and turbidity

4 sensors connectable in any combination

Functionality modular extendable at any time

Plug and play for modules and sensors

pH

Characteristic

Robust plastic housing
All non-ex applications

Design

2 to 4x Memosens input, 2 to 8x current output
Alarmrelay, 4x relay, SD card for software update and copy & paste of setup

Material

Housing base: PC-FR
Housing seal: EPDM

Dimension

237 x 194 x 162 mm
9.33 x 7.64 x 6.38 inch

Process temperature

-20 to 55 °C (0 to 130 °F)

Ingres protection

IP66 / IP 67

Input

1 to 4x Memosens digital input
2x 0/4 to 20mA Input optional
2 to 4x Digital input optional

Output / communication

2 to 8x 0/4 to 20 mA current outputs, alarmrelay,
4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

Additional certifications

EAC, cCSAus

Disinfection

Measuring principle

Free chlorine

Disinfection

Application

Modular 4 wire controller

Multichannel: 1 to 4 digital channels for Memosens protocol

Multiparameter: pH, redox, ISFET, conductivity inductive and conductive, dissolved oxygen, nitrate and turbidity

4 sensors connectable in any combination

Functionality modular extendable at any time

Plug and play for modules and sensors

Characteristic

Robust plastic housing

All non-ex applications

Design

2 to 4x Memosens input, 2 to 8x current output

Alarmrelay, 4x relay, SD card for software update and copy & paste of setup

Material

Housing base: PC-FR

Housing seal: EPDM

Dimension

237 x 194 x 162 mm

9.33 x 7.64 x 6.38 inch

Process temperature

-20 to 55 °C (0 to 130 °F)

Input

1 to 4x Memosens digital input

2x 0/4 to 20mA Input optional

2 to 4x Digital input optional

Output / communication

2 to 8x 0/4 to 20 mA current outputs, alarmrelay,

4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

Disinfection**Additional certifications**EAC, cCSAus

Sludge Level**Measuring principle**Ultrasonic sensor

Application

Modular 4 wire controller

Multichannel: 1 to 4 digital channels for Memosens protocol

Multiparameter: pH, redox, ISFET, conductivity inductive and conductive, dissolved oxygen, nitrate and turbidity

4 sensors connectable in any combination

Functionality modular extendable at any time

Plug and play for modules and sensors

Characteristic

Robust plastic housing

All non-ex applications

Design

2 to 4x Memosens input, 2 to 8x current output

Alarmrelay, 4x relay, SD card for software update and copy & paste of setup

Material

Housing base: PC-FR

Housing seal: EPDM

Dimension

237 x 194 x 162 mm

9.33 x 7.64 x 6.38 inch

Process temperature-20 to 55 °C (0 to 130 °F)

Ingres protectionIP66 / IP 67

Sludge Level

Input

1 to 4x Memosens digital input

2x 0/4 to 20mA Input optional

2 to 4x Digital input optional

Output / communication

2 to 8x 0/4 to 20 mA current outputs, alarmrelay,

4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

Additional certifications

EAC, cCSAus

Analyser

Measuring principle

Potentiometric / ISE

Characteristic

Robust plastic housing

All non-ex applications

Design

2 to 4x Memosens input, 2 to 8x current output

Alarmrelay, 4x relay, SD card for software update and copy & paste of setup

Process temperature

-20 to 55 °C (0 to 130 °F)

Application

Modular 4 wire controller

Multichannel: 1 to 4 digital channels for Memosens protocol

Multiparameter: pH, redox, ISFET, conductivity inductive and conductive, dissolved oxygen, nitrate and turbidity

4 sensors connectable in any combination

Functionality modular extendable at any time

Plug and play for modules and sensors

Analyser

Output / communication

2 to 8x 0/4 to 20 mA current outputs, alarmrelay,
4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

Input

1 to 4x Memosens digital input
2x 0/4 to 20mA Input optional
2 to 4x Digital input optional

Oxygen

Measuring principle

Amperometric oxygen measurement

Application

Modular 4 wire controller
Multichannel: 1 to 4 digital channels for Memosens protocol
Multiparameter: pH, redox, ISFET, conductivity inductive and conductive,
dissolved oxygen, nitrate and turbidity
4 sensors connectable in any combination
Functionality modular extendable at any time
Plug and play for modules and sensors

Characteristic

Robust plastic housing
All non-ex applications

Design

2 to 4x Memosens input, 2 to 8x current output
Alarmrelay, 4x relay, SD card for software update and copy & paste of
setup

Material

Housing base: PC-FR
Housing seal: EPDM

Dimension

237 x 194 x 162 mm
9.33 x 7.64 x 6.38 inch

Oxygen

Process temperature

-20 to 55 °C (0 to 130 °F)

Input

1 to 4x Memosens digital input

2x 0/4 to 20mA Input optional

2 to 4x Digital input optional

Output / communication

2 to 8x 0/4 to 20 mA current outputs, alarmrelay,

4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Etherne

Additional certifications

EAC, cCSAus

ORP / Redox

Measuring principle

Sensor ORP / Redox

Application

Modular 4 wire controller

Multichannel: 1 to 4 digital channels for Memosens protocol

Multiparameter: pH, redox, ISFET, conductivity inductive and conductive, dissolved oxygen, nitrate and turbidity

4 sensors connectable in any combination

Functionality modular extendable at any time

Plug and play for modules and sensors

Characteristic

Robust plastic housing

All non-ex applications

Design

2 to 4x Memosens input, 2 to 8x current output

Alarmrelay, 4x relay, SD card for software update and copy & paste of setup

ORP / Redox

Material

Housing base: PC-FR

Housing seal: EPDM

Dimension

237 x 194 x 162 mm

9.33 x 7.64 x 6.38 inch

Process temperature

-20 to 55 °C (0 to 130 °F)

Ingres protection

IP66 / IP 67

Input

1 to 4x Memosens digital input

2x 0/4 to 20mA Input optional

2 to 4x Digital input optional

Output / communication

2 to 8x 0/4 to 20 mA current outputs, alarmrelay,

4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

Additional certifications

EAC, cCSAus

Turbidity

Measuring principle

Single beam scattered light

Application

Modular 4 wire controller

Multichannel: 1 to 4 digital channels for Memosens protocol

Multiparameter: pH, redox, ISFET, conductivity inductive and conductive, dissolved oxygen, nitrate and turbidity

4 sensors connectable in any combination

Functionality modular extendable at any time

Plug and play for modules and sensors

Turbidity

Characteristic

Robust plastic housing
All non-ex applications

Design

2 to 4x Memosens input, 2 to 8x current output
Alarmrelay, 4x relay, SD card for software update and copy & paste of setup

Material

Housing base: PC-FR
Housing seal: EPDM

Dimension

237 x 194 x 162 mm
9.33 x 7.64 x 6.38 inch

Process temperature

-20 to 55 °C (0 to 130 °F)

Ingres protection

IP66 / IP 67

Input

1 to 4x Memosens digital input
2x 0/4 to 20mA Input optional
2 to 4x Digital input optional

Output / communication

2 to 8x 0/4 to 20 mA current outputs, alarmrelay,
4x relay, ProfibusDP, Modbus RS485, Modbus TCP, Ethernet

Additional certifications

EAC, cCSAus

More information www.si.endress.com/CM444