

## Solitrend MMP20 – Flexible mobile moisture measurement

Proven Solitrend technology in a battery powered handheld device



### Benefits:

- Deep material permeation (130 mm)
- Large measuring field volume (up to 1 l)
- Wide moisture range from 0-100 % possible
- Variant probe design for different media
- Surface and capillary moisture measurement

More information and current pricing:

[www.sg.endress.com/MMP20](http://www.sg.endress.com/MMP20)

**Field of application:** Increase your product quality due to reliable moisture measurement. Our new mobile device delivers measuring values within a couple of moments compared to the standard laboratory devices in bulk solids and fresh concrete.

### Features and specifications

#### Moisture in bulk solids

#### Measuring principle

Guided radar

#### Application

Moisture measurement in heterogeneous bulk solids of any grain size

---

## Moisture in bulk solids

---

### Measuring method

Handheld device with two rods or lance probe

---

### Measurement range

Recommended moisture range %/ vol.: 0...100 %

---

### Material permeation depth

Up to 130 mm

(0.43 ft)

---

### Consistency of the sample

Conductivity range:

0...max. 20 mS/ cm

---

### Temperature sensor

None

---

### Process temperature

0...+50°C

(+32°F...+122°F)

---

### Accuracy

Up to +/-0.2 % abs.

---

### Output / communication

None

---

### Options

Telescopic extension (for S2 probe)

Carrying case

---

More information [www.sg.endress.com/MMP20](http://www.sg.endress.com/MMP20)