

Vibronic

Point level detection

Liquiphant FTL70

Point level switch for liquids in high-temperature applications



Prednosti:

- Use in safety systems requiring functional safety to SIL2 in accordance with IEC 61508/IEC 61511-1
- With welded gas tight feedthrough maximum safety in the event of damaged sensor
- Wide variety of electronics, e.g. NAMUR, relay, thyristor, PFM signal output: the right connection for every process control system
- Large number of process connections to choose from: universal usage
- No calibration: quick, low-cost start-up
- No mechanically moving parts: no maintenance, no wear, long operating life.
- Monitoring of fork for damage: guaranteed function
- FDA approved materials (PFA Edlon)

Več informacij in aktualne cene:

www.si.endress.com/FTL70

Lastnosti na dlani

- **Process temperature** -60 °C...+280 °C (-76 °F...+540 °F, (300°C / 572 °F 50h, cumulated
- **Process pressure absolute / max. overpressure limit**
Vacuum...100 bar (Vacuum...1450 psi)

Področje uporabe: Liquiphant FT70 is a point level switch for use in hazardous areas with all international certificates. FTL70 is especially designed for applications with high process temperatures up to 280°C and can be used for Safety Instrumented Systems up to SIL2, in homogeneous redundancy up to SIL3. An integrated second line of defense offers the highest degree of safety. Reliable measurement

values, not affected by: changing media properties, flow, turbulences, gas bubbles, foam, vibrations or build-up.

Lastnosti in specifikacije

Point Level / Liquids

Merilni princip

Vibration Liquids

Characteristic / Application

Modular housing concept

High process temperatures up to 280°C

wide range of process connections

Analogue and bus interfaces

Extensive certificate range (e.g. Ex, WHG)

compact, e.g. pipes

Dual Sealing / Second line of defense

Specialities

Foam detection

Detect a density change

second line of defense

Supply / Communication

PROFIBUS PA

19...253V AC

10...55V DC-PNP

19...253V AC bzw 10...55V DC

8/16mA, 11...36V DC

NAMUR

PFM

Ambient temperature

-50 °C...+70 °C

(-58 °F...+158 °F)

Point Level / Liquids**Process temperature**

-60 °C...+280 °C
(-76 °F...+540 °F,
(300°C / 572 °F 50h, cumulated

Process pressure absolute / max. overpressure limit

Vacuum...100 bar
(Vacuum...1450 psi)

Main wetted parts

316L / Alloy
PFA and Enamel on request

Process connection

Thread:
G3/4A, G1A, R3/4", R1, NPT3/4, NPT1
Flange:
DIN DN25...DN100,
ASME 1"...4",
JIS 25A...100A

Sensor length

65mm (2.56")

Communication

PROFIBUS PA
19...253V AC
10...55V DC-PNP
19...253V AC bzw 10...55V DC
8/16mA, 11...36V DC
NAMUR
PFM

Certificates / Approvals

ATEX, FM, CSA C/US, IEC Ex, TIIS, INMETRO, NEPSI

Safety approvals

SIL

Point Level / Liquids

Design approvals

EN 10204-3.1
NACE MR0175, MR0103
ASME B31.3
AD2000

Marine approval

GL/ ABS

Options

Heavy duty stainless steel housing mainly for the oil and gas industry

Components

FTL325P/FTL375P Interface PFM
FTL325N/FTL375N Interface NAMUR

Več informacij www.si.endress.com/FTL70