

Dosimag electromagnetic flowmeter

Flowmeter with hygienic design, highest repeatability and an ultra-compact sensor



Več informacij in aktualne cene:

www.si.endress.com/5BH

Prednosti:

- High process safety – high measuring accuracy and repeatability in shortest filling time
- Energy-saving flow measurement – no pressure loss due to cross-section constriction
- Maintenance-free – no moving parts
- Versatile and time-saving wiring – plug connector
- Industry-optimized – ultra-compact design
- For hygiene requirements – stainless steel housing

Lastnosti na dlani

- **Max. measurement error** $\pm 0.25\%$ o.r. ± 1 to 4 m/s (3.3 to 13 ft/s) $\pm 0.5\%$ o.r. ± 1 mm/s (0.04 in/s) $\pm 5\%$ o.r.
- **Measuring range** 0.14 to 1.66 l/s (0.035 to 0.44 gal/s)
- **Medium temperature range** Seal material EPDM: -20 to $+130\text{ }^{\circ}\text{C}$ (-4 to $+266\text{ }^{\circ}\text{F}$) Seal material Silicone: -20 to $+130\text{ }^{\circ}\text{C}$ (-4 to $+266\text{ }^{\circ}\text{F}$) Seal material Viton: 0 to $+150\text{ }^{\circ}\text{C}$ ($+32$ to $+302\text{ }^{\circ}\text{F}$)
- **Max. process pressure** PN 16
- **Wetted materials** Liner: PFA Electrodes: 1.4435 (316L); Alloy C22, 2.4602 (UNS N06022), Tantalum, Platinum

Področje uporabe: Dosimag is specially designed for filling and bottling applications of conductive liquids. It measures volume directly. Designed for applications where space is a premium, Dosimag will be the preferred choice for system integrators, skid builders and equipment manufacturers.

Lastnosti in specifikacije

Liquids

Merilni princip

Electromagnetic

Product headline

Flowmeter with hygienic design, highest repeatability and an ultra-compact sensor.

For demanding dosing and filling applications.

Sensor features

High process safety – high measuring accuracy and repeatability in shortest filling time. Energy - saving flow measurement – no pressure loss due to cross section constriction. Maintenance - free – no moving parts.

Wetted materials CIP, SIP cleanable. Nominal diameter: DN 4 to 25 ($\frac{1}{8}$ to 1"). Measuring device conform to FDA.

Transmitter features

Versatile and time-saving wiring – plug connector. Industry-optimized – ultra-compact design. For hygienic requirements – stainless steel housing.

Pulse/frequency/switch output, Modbus RS485. Custody transfer approvals (MID, NTEP). Excellent, easily cleanable transmitter.

Nominal diameter range

DN 4 ($\frac{5}{32}$ "), 8 ($\frac{5}{16}$ "), 15 ($\frac{1}{2}$ "), 25 (1")

Wetted materials

Liner: PFA

Electrodes: 1.4435 (316L); Alloy C22, 2.4602 (UNS N06022), Tantalum, Platinum

Measured variables

Volume flow

Liquids

Max. measurement error

±0.25 % o.r. ± 1 to 4 m/s (3.3 to 13 ft/s)

±0.5 % o.r. ± 1 mm/s (0.04 in/s)

±5 % o.r.

Measuring range

0.14 to 1.66 l/s (0.035 to 0.44 gal/s)

Max. process pressure

PN 16

Medium temperature range

Seal material EPDM: -20 to +130 °C (-4 to +266 °F)

Seal material Silicone: -20 to +130 °C (-4 to +266 °F)

Seal material Viton: 0 to +150 °C (+32 to +302 °F)

Ambient temperature range

-40 to +60 °C (-40 to +140 °F)

Sensor housing material

1.4308 (304)

Transmitter housing material

1.4308 (304)

Degree of protection

IP66/67, type 4X enclosure

Display/Operation

No local Operation

Configuration via operating tools possible

Outputs

Pulse/frequency/switch output (passive)

Inputs

None

Liquids

Digital communication

Modbus RS485

Power supply

DC 20 to 30 V

Hazardous area approvals

ATEX, IECEx, cCSAus

Product safety

CE

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc.to ISO/IEC 17025)

NTEP

Material certificates

3.1 material

Hygienic approvals and certificates

Sanitary approval: 3-A, EHEDG, seals acc. to FDA (except EPDM)

Več informacij www.si.endress.com/5BH