

RNB22 system power supply unit

Safely power system interfaces on the DIN rail bus



Benefits:

- Safe and reliable, single-phase output in the power range up to 100 W
- Smart system function monitoring for fault prevention for high system availability
- Powerful reserve capacity for lower power ranges
- Transient surge protection, short-circuit proof, no-load proof
- Tool-free installation, suited for vertical or horizontal mounting

Specs at a glance

- **Output** 24...28 V DC
- **Power Supply** 100...240 V AC/DC

from **€155.00**

Price as of 19.05.2022

More information and current pricing:

www.si.endress.com/RNB22

Field of application: The RNB22 is a compact, high-efficiency primary switch mode power supply for DIN rail interface systems. It delivers a reliable, single-phase, **24 V_{DC} / 2.5 A** output and runs on a wide-range input from 100 to 240 V_{AC} / 110 to 250 V_{DC}, with a dynamic and static boost of 5 A and 3.125 A respectively. When run in parallel with the **RNF22** error message module, the RNB22 provides redundancy, increased capacity, as well as function monitoring to report critical operating states before errors occur.

Features and specifications

Power supplies & barrier

Measuring principle

Active barrier

Measuring principle

Power supply

Power supplies & barrier

Function

System power supply 24 V
DC

Loop power supply

24...28 V DC

Power Supply

100...240 V AC/DC

Output

24...28 V DC

Certificates

DNV

Operation

Rotary selector

More information www.si.endress.com/RNB22