

## RNB130

### Primary switched-mode power supply for DIN rail

Power supply for one 4 wire sensor or transmitter.



#### Prednosti:

- Small housing, 35 mm width
- High availability
- Wide range input - can be used world-wide
- Power reserve (Power Boost)
- Power supply without wiring: Supply via DIN rail bus connector
- Space saving DIN rail mounting as per IEC 60715

#### Lastnosti na dlani

- **Input** Not defined
- **Output** 24 VDC, 1,5 A
- **Power Supply** Not defined

od **142,23 €**

Cena na dan 10.05.2021

Več informacij in aktualne cene:

[www.si.endress.com/RNB130](http://www.si.endress.com/RNB130)

**Področje uporabe:** The power supply has one output for supplying voltage to 4 wire sensors and transmitters. Connection to mono-phased a.c. networks or to two phase conductors of three-phase supply networks (TN-, TT- or IT-networks as per VDE 0100 T 300/IEC 364-3) with 100-240 V AC nominal voltage possible.

#### Lastnosti in specifikacije

#### Power supplies & barrier

##### Merilni princip

Power supply

##### Measuring principle

Power supply

## Power supplies &amp; barrier

**Function**

Power supply for one 4-wire sensor or transmitter

---

**Loop power supply**

85...250 V AC

45...65 Hz

---

**Power Supply**

Not defined

---

**Auxiliary power supply / Loop power supply**

85...250 V AC

45...65 Hz

---

**Input**

Not defined

---

**Output**

24 VDC, 1,5 A

---

**Software functions**

Not defined

---

**Certificates**

Not defined

---

**SIL**

Not defined

---

**Operation**

DIP switch

---

## Acquisition / Evaluation

**Merilni princip**

Power supply

---

Acquisition / Evaluation

**Function**

Power

---

**Output**

24 VDC, 1,5 A

---

**Auxiliary power supply / Loop power supply**

85...250 V AC

45...65 Hz

---

**Dimensions (wxhxd)**

35 x 99 x 102.5 mm

(1.39" x 3.9" x 4.04")

---

**Operation**

DIP switch

---

Več informacij [www.si.endress.com/RNB130](http://www.si.endress.com/RNB130)