

Radar measurement

Micropilot FMR60

The standard sensor for highest demands in liquid level measurement with 80GHz technology



Več informacij in aktualne cene:

www.si.endress.com/FMR60

Prednosti:

- Hardware and software developed according to IEC 61508 up to SIL3 in homogeneous redundancy
- Heartbeat Technology for a cost-effective and safe plant operation during the entire life cycle
- HistoROM data management concept for fast and easy commissioning, maintenance and diagnostics
- Highest reliability even with obstructions in vessels due to small beam angle and Multi-Echo Tracking evaluation
- Reduction of engineering effort due to an easier integration of the 80GHz radar instrument into the process
- Innovative drip-off antenna of PTFE for maximum system availability
- The world's easiest proof test concept for SIL and WHG saves time and costs

Lastnosti na dlani

- **Accuracy** +/- 1 mm (0.04 in)
- **Process temperature** -40...+130 °C (-40...+266 °F)
- **Process pressure absolute / max. overpressure limit** Vacuum ... 16 bar (Vacuum ... 232 psi)
- **Max. measurement distance** 50 m (164 ft)
- **Main wetted parts** PTFE antenna PP or 316L process connections

Področje uporabe: Micropilot FMR60 is the first 80GHz radar developed according to the international functional safety directive IEC 61508. The free space radar offers maximum reliability due to the drip-off antenna, improved algorithms and small beam angle. It is used for continuous

non-contact level measurement of liquids, pastes and slurries. The measurement is not affected by changing media, temperature changes, gas blankets or vapors. It also possesses the smart sensor functionality Heartbeat Technology.

Lastnosti in specifikacije

Continuous / Liquids

Merilni princip

Level radar

Characteristic / Application

For basic level measurement in liquids, pastes and slurries;
non affected by changing media, temperature changes, gas blankets or vapor;
For applications with many obstacles due to the very small beam angle.

Specialities

Heartbeat Technology,
SIL 2/3 according to IEC 61508,
Bluetooth® commissioning,
Operation and maintenance SmartBlue App,
Safety and reliability with Multi-Echo Tracking
HistoROM
RFID TAG for easy identification

Supply / Communication

2-wire (HART)
Bluetooth® wireless technology and App (optional)

Frequency

W-band (~80 GHz)

Accuracy

+/- 1 mm (0.04 in)

Ambient temperature

-40...+80 °C
(-40...+176 °F)

Continuous / Liquids

Process temperature

-40...+130 °C
(-40...+266 °F)

Process pressure absolute / max. overpressure limit

Vacuum ...16 bar
(Vacuum ... 232 psi)

Main wetted parts

PTFE antenna
PP or 316L process connections

Process connection

Thread:
G1-1/2", MNPT1-1/2";
Flange:
UNI DN80...DN150 (3"...6")

Max. measurement distance

50 m (164 ft)

Communication

4...20 mA HART,
Additional switch,
Bluetooth® wireless technology

Certificates / Approvals

ATEX, FM, CSA C/US, IEC Ex, JPN Ex, INMETRO, NEPSI, KC, EAC, UK Ex

Safety approvals

Overfill protection WHG
SIL 2, SIL 3

Design approvals

EN 10204-3.1

Continuous / Liquids

Options

Display,
Customized parameterization,
Remote operation via SmartBlue App using Bluetooth®,
Gas-tight feed through,
PWIS free

Application limits

Process temp. > 130 °C (266 °F) -> FMR62
Very aggressive media -> FMR62
Strong turbulences and foam, stilling well and bypass -> FMR5x, FMP5x

Več informacij www.si.endress.com/FMR60