

Proline Cubemass C 500 Coriolis flowmeter

Compact sensor for smallest quantities, with a remote transmitter version with up to 4 I/Os



More information and current pricing:

www.th.endress.com/8C5B

Benefits:

- Space-saving installation – compact single-tube design
- Fewer process measuring points – multivariable measurement (flow, density, temperature)
- Suitable for skids – lightweight sensor
- Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses
- Reduced complexity and variety – freely configurable I/O functionality
- Integrated verification – Heartbeat Technology

Specs at a glance

- **Max. measurement error** Mass flow (liquid): $\pm 0.10\%$ Volume flow (liquid): $\pm 0.10\%$ Mass flow (gas): $\pm 0.50\%$ Density (liquid): $\pm 0.0005 \text{ g/cm}^3$
- **Measuring range** 0 to 1000 kg/h (0 to 37 lb/min)
- **Medium temperature range** -50 to $+205 \text{ }^\circ\text{C}$ (-58 to $+401 \text{ }^\circ\text{F}$)
- **Max. process pressure** PN 40, Class 300, 10K, 400 bar (5800 psi)
- **Wetted materials** Measuring tube: 1.4539 (904L) Connection: 1.4539 (904L); 1.4404 (316/316L)

Field of application: Cubemass C is the ideal sensor for the measurement of smallest flow rates in skids, test rigs and industrial robotics. Neither high pressure nor alternating flow conditions compromise its accuracy. With its innovative remote transmitter Cubemass C 500 maximizes installation flexibility and operational safety in demanding environments. Heartbeat Technology ensures measurement reliability and compliant verification.

Features and specifications

Gas

Measuring principle

Coriolis

Product headline

Compact sensor for smallest quantities, with a transmitter remote version with up to 4 I/Os.

Measuring accurately smallest quantities of liquids and gases.

Sensor features

Space-saving installation – compact single-tube design. Fewer process measuring points – multivariable measurement (flow, density, temperature). Suitable for skids – lightweight sensor.

Nominal diameter: DN 1 to 6 ($\frac{1}{2}$ " to $\frac{1}{4}$ "). Process pressure up to 400 bar (5800 psi). Medium temperature up to +205 °C (+401 °F).

Transmitter features

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology.

Remote version with up to 4 I/Os. Backlit display with touch control and WLAN access. Standard cable between sensor and transmitter.

Nominal diameter range

DN 1 to 6 ($\frac{1}{2}$ " to $\frac{1}{4}$ ")

Wetted materials

Measuring tube: 1.4539 (904L)

Connection: 1.4539 (904L); 1.4404 (316/316L)

Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow, reference density, concentration

Gas

Max. measurement errorMass flow (liquid): ± 0.10 %Volume flow (liquid): ± 0.10 %Mass flow (gas): ± 0.50 %Density (liquid): ± 0.0005 g/cm³**Measuring range**

0 to 1000 kg/h (0 to 37 lb/min)

Max. process pressure

PN 40, Class 300, 10K, 400 bar (5800 psi)

Medium temperature range

-50 to +205 °C (-58 to +401 °F)

Ambient temperature range

Standard: -40 to +60 °C (-40 to +140 °F)

Option: -50 to +60 °C (-58 to +140 °F)

Sensor housing material

1.4301 (304), corrosion resistant

Sensor connection housing (standard): AlSi10Mg, coated

Sensor connection housing (option): 1.4301 (304); 1.4404 (316L)

Transmitter housing material

AlSi10Mg, coated; 1.4409 (CF3M) similar to 316L; Polycarbonat

Degree of protection

Sensor remote version (standard): IP66/67, type 4X enclosure

Transmitter remote version: IP66/67, Type 4X enclosure

Display/Operation

4-line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Gas**Outputs**

4 outputs:

4-20 mA HART (active/passive)

4-20 mA WirelessHART

4-20 mA (active/passive)

Pulse/frequency/switch output (active/passive)

Double pulse output (active/passive)

Relay output

Inputs

Status input

4-20 mA input

Digital communication

HART, PROFIBUS DP, PROFIBUS PA, FOUNDATION Fieldbus, Modbus RS485, Profinet, Ethernet/IP, OPC-UA

Power supply

DC 24 V

AC 100 to 230 V

AC 100 to 230 V / DC 24 V (non-hazardous area)

Hazardous area approvals

ATEX, IECEx, cCSAus, NEPSI, INMETRO, EAC

Product safety

CE, C-tick, EAC marking

Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

Gas**Pressure approvals and certificates**CRN

Material certificates3.1 material

Liquids**Measuring principle**Coriolis

Product headline

Compact sensor for smallest quantities, with a transmitter remote version with up to 4 I/Os.

Measuring accurately smallest quantities of liquids and gases.

Sensor features

Space-saving installation – compact single-tube design. Fewer process measuring points – multivariable measurement (flow, density, temperature). Suitable for skids – lightweight sensor.

Nominal diameter: DN 1 to 6 ($\frac{1}{24}$ to $\frac{1}{4}$ "). Process pressure up to 400 bar (5800 psi). Medium temperature up to +205 °C (+401 °F).

Transmitter features

Full access to process and diagnostic information – numerous, freely combinable I/Os and fieldbuses. Reduced complexity and variety – freely configurable I/O functionality. Integrated verification – Heartbeat Technology.

Remote version with up to 4 I/Os. Backlit display with touch control and WLAN access. Standard cable between sensor and transmitter.

Nominal diameter rangeDN 1 to 6 ($\frac{1}{24}$ to $\frac{1}{4}$ ")

Wetted materials

Measuring tube: 1.4539 (904L)

Connection: 1.4539 (904L); 1.4404 (316/316L)

Liquids

Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow, reference density, concentration

Max. measurement error

Mass flow (liquid): ± 0.10 %

Volume flow (liquid): ± 0.10 %

Mass flow (gas): ± 0.50 %

Density (liquid): ± 0.0005 g/cm³

Measuring range

0 to 1000 kg/h (0 to 37 lb/min)

Max. process pressure

PN 40, Class 300, 10K, 400 bar (5800 psi)

Medium temperature range

-50 to +205 °C (-58 to +401 °F)

Ambient temperature range

Standard: -40 to +60 °C (-40 to +140 °F)

Option: -50 to +60 °C (-58 to +140 °F)

Sensor housing material

1.4301 (304), corrosion resistant

Sensor connection housing (standard): AlSi10Mg, coated

Sensor connection housing (option): 1.4301 (304); 1.4404 (316L)

Transmitter housing material

AlSi10Mg, coated; 1.4409 (CF3M) similar to 316L; Polycarbonat

Degree of protection

Sensor remote version (standard): IP66/67, type 4X enclosure

Transmitter remote version: IP66/67, Type 4X enclosure

Display/Operation

4-line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Liquids

Outputs

4 outputs:

4-20 mA HART (active/passive)

4-20 mA WirelessHART

4-20 mA (active/passive)

Pulse/frequency/switch output (active/passive)

Double pulse output (active/passive)

Relay output

Inputs

Status input

4-20 mA input

Digital communication

HART, PROFIBUS DP, PROFIBUS PA, FOUNDATION Fieldbus, Modbus RS485, Profinet, Ethernet/IP, OPC-UA

Power supply

DC 24 V

AC 100 to 230 V

AC 100 to 230 V / DC 24 V (non-hazardous area)

Hazardous area approvals

ATEX, IECEx, cCSAus, NEPSI, INMETRO, EAC

Product safety

CE, C-tick, EAC marking

Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

Liquids

Pressure approvals and certificates

CRN

Material certificates

3.1 material

More information www.th.endress.com/8C5B