

Vibronic

Point level detection

Liquiphant FTL50H

Compact vibration point level switch for liquids especially in the food and life sciences industry



Več informacij in aktualne cene:

www.si.endress.com/FTL50H

Prednosti:

- International hygienic certificates (3-A, EHEDG, ASME BPE). FDA-conformed material
- Electro-polished and passivated surface finishing
- International explosion protection certificates and overfill prevention certificate (WHG)
- No mechanically moving parts: no maintenance, no wear, long operating life.
Monitoring of fork for damage: guaranteed function
- Use in safety systems requiring functional safety to SIL2/SIL3 in accordance with IEC 61508/IEC 61511-1
- No calibration required, easy to start up
- Variety of standardized hygienic process connections for hygiene sensitive applications

Lastnosti na dlani

- **Process temperature** -50 °C...+150 °C (-58 °F...+302 °F)
- **Process pressure / max. overpressure limit** Vacuum...64 bar (Vacuum...928 psi)
- **Min. density of medium** 0.5g/cm³(0.4g/cm³ optional)

Področje uporabe: Liquiphant FTL50H is a point level switch for use in hazardous areas with all international certificates. Especially useable in the food and life sciences industry with hygienic certificates (3-A, EHEDG, ASME BPE). FTL50H offers functional safety SIL2/SIL3. Reliable

measurement values, not affected by: changing media properties, flow, turbulences, gas bubbles, foam, vibrations or build-up.

Lastnosti in specifikacije

Point Level / Liquids

Merilni princip

Vibration Liquids

Characteristic / Application

Modular & completely welded housing concept

Focus Food & Pharma

surface up to 0,38µm electro polished

wide range of process connections

Analogue and bus interfaces

Extensive certificate range (e.g. EHEDG,3A)

Compact, e.g. pipes

Specialities

Foam detection

Detect changes of the density

Supply / Communication

PROFIBUS PA

19...253V AC

10...55V DC-PNP

19...253V AC or 10...55V DC

8/16mA, 11...36V DC

NAMUR

PFM

Ambient temperature

-50 °C...+70 °C

(-58 °F...+158 °F)

Process temperature

-50 °C...+150 °C

(-58 °F...+302 °F)

Point Level / Liquids**Process pressure / max. overpressure limit**

Vacuum...64 bar
(Vacuum...928 psi)

Min. density of medium

0.5g/cm³(0.4g/cm³ optional)

Main wetted parts

316L

Process connection

Thread:

G3/4A, G1A, R3/4", R1, NPT3/4, NPT1

Flange:

DN25...DN100,

ASME 1"...4",

JIS 25A...100A

Process connection hygienic

Tri-Clamp ISO2852

Dairy coupling

Aseptic

DRD

SMS

Varivent

Communication

PROFIBUS PA

19 ..253V AC

10...55V DC-PNP

19...253V AC or 10...55V DC

8/16mA, 11...36V DC

NAMUR

PFM

Certificates / Approvals

ATEX, FM, CSA C/US, IEC Ex, TIIS, INMETRO,

NEPSI

Point Level / Liquids**Safety approvals**SIL2/ SIL3

Design approvals

EN 10204-3.1

AD2000

Hygienic approvalsCoC ASME-BPE

Marine approvalGL/ ABS/ DNV

Components

FTL325P/FTL375P Interface PFM

FTL325N/FTL375N Interface NAMUR

Density**Merilni princip**Vibration Density

Characteristic / Application

Liquiphant M Density

with Density Computer FML621

Temperature and pressure measurement

Modular & completely welded housing concept

Focus Food & Pharma

Surface up to 0.3 μ

Supply / CommunicationTransmitter power supply (MUS)

Ambient temperature

-50...70°C

-50...60°C for hazardous applications

Density

Process temperature

0...80°C (validity of accuracy data)

-50...0°C/80...150°C (with reduced technical data)

Process pressure

0...25 bar

>25...64 bar (with reduced technical data)

Wetted parts

316L

Hygienic

3A

EHEDG

Sensor length

Compact: 50.5 mm

Output

Pulse

Certificates / ApprovalsATEX, FM, CSA C/US, IEC Ex, TIIS, INMETRO,
NEPSI**Specialities**

Commissioning with ReadWin2000

Components

Density Computer FML621

Other approvals and certificates

SIL2/ SIL3

Več informacij www.si.endress.com/FTL50H