

iTHERM TMS31 MultiSens Bundle

Flexible metal rope multipoint for silos and storage tank applications



Benefits:

- Easy installation and process integration thanks to a high degree of customization
- Flexible rope that adapts to different silos or tank operating conditions (filling, emptying, storage, ...)
- Intrinsically safe device for use in Ex areas
- Highly robust design for a long product lifetime and continuous monitoring in all conditions

Specs at a glance

- **Accuracy** class 1 acc. to IEC 60584 class 2 acc. to IEC 60584 class Special ASTM E230 and ANSI MC 96.1 IEC60751 Class A IEC60751 Class AA
- **Response time** TC t50 = 1 s t90 = 2 s RTD t50 = 3 s t90 = 6 s
- **Max. process pressure (static)** at 20 °C: 40 bar (580 psi)
- **Operating temperature range** Type K: -270 °C ...800 °C (-454 °F ...1.472 °F) Type J: -210 °C ...520 °C (-346 °F ...968 °F) Pt100 WW; 3mm; 316L; -200...600oC Pt100 StrongSens; 6mm; 316L; -50...500oC Pt100 TF; 3mm; 316L; -50...400oC
- **Max. immersion length on request** up to 60.000,00 mm (2.360")

More information and current pricing:

www.th.endress.com/TMS31

Field of application: The iTHERM TMS31 is a versatile, modular multipoint temperature assembly designed for temperature average detection and profiling in grain, organic bulk material storage silos and in oil, fuel storage tanks. The device's mechanical robustness and accurate temperature sensors offer the necessary characteristics for safe, reliable and economic product storage operations. In its standard configuration it is available with up to 20 thermocouple (TC) or RTD sensors fitted to a primary metal rope.

Features and specifications

Thermometer

Measuring principle

Resistance Temperature Detector

Characteristic / Application

metric style
imperial style
easy-to-use
suitable for hazardous areas
process connection: flanged
Storage applications
linear sensor distribution
modular design

Thermowell / protection tube

without (not intended to use with thermowell)

Insert / probe

mineral insulated (MI), flexible

Outer diameter protection tube / Insert

25 mm
37 mm

Max. immersion length on request

up to 60.000,00 mm (2.360")

Material protection tube/ thermowell

1.4401 (316)
1.4435 (316L)

Thermometer**Process connection**

flange:

1 1/2" ASME/ANSI B16.5 150

...300

2" ASME/ANSI B16.5 150

...300

3" ASME/ANSI B16.5 150

..300

4"ASME/ANSI B16.5 150

..300

DN40 EN/DIN 1092.1 PN16

...PN40

DN50 EN/DIN 1092.1 PN16

...PN40

DN80 EN/DIN 1092.1 PN16

...PN40

DN100 EN/DIN 1092.1 PN16

...PN40

Tip shape

straight

Operating temperature range

Type K:

-270 °C ...800 °C

(-454 °F ...1.472 °F)

Type J:

-210 °C ...520 °C

(-346 °F ...968 °F)

Pt100 WW; 3mm; 316L; -200...600oC

Pt100 StrongSens; 6mm; 316L; -50...500oC

Pt100 TF; 3mm; 316L; -50...400oC

Max. process pressure (static)

at 20 °C: 40 bar (580 psi)

Thermometer

Accuracy

class 1 acc. to IEC 60584

class 2 acc. to IEC 60584

class Special ASTM E230 and ANSI MC 96.1

IEC60751 Class A

IEC60751 Class AA

Response time

TC

t50 = 1 s

t90 = 2 s

RTD

t50 = 3 s

t90 = 6 s

Integration head transmitter

yes (4 ... 20 mA; HART; PROFIBUS PA; FOUNDATION
FIELDBUS)

Ex - approvals

ATEX

IECEX

UL

FM

CSA

Certification

SIL (transmitter only)

More information www.th.endress.com/TMS31