

# TMT162R

## Pt100 Thermometer, Field transmitter

Safe monitoring of process temperatures in challenging applications e. g. in the Oil & Gas industry



Daha fazla bilgi ve güncel fiyatlandırma:

[www.tr.endress.com/TMT162R](http://www.tr.endress.com/TMT162R)

### Avantajlar:

- Dual compartment housing
- Backlit display with large measured value, bar graph and fault condition indication
- Galvanic isolation 2 kV (sensor input to the output)
- Wide range of threaded thermowell connections available as standard
- Replaceable measuring insert comprising a mineral insulated tube (SS 316L/1.4404)
- Approvals for hazardous areas: Flameproof enclosure (Ex d), Intrinsic safety (Ex ia), Non-sparking (Ex nA); marine approval
- Aluminum or stainless steel housing, degree of protection IP67, NEMA 4x

### Özelliklere genel bakış

- **Accuracy** class A acc. to IEC 60751 class AA acc. to IEC 60751
- **Response time** depending on configuration  $t_{50} = 4 \text{ s}$   $t_{90} = 8 \text{ s}$
- **Max. process pressure (static)** at 20 °C: 500 bar (7.252 psi)
- **Operating temperature range** PT 100: -200 °C ...600 °C (-328 °F ... 1.112 °F)
- **Max. immersion length on request** Not defined

**Uygulama alanı:** The robust thermometer is designed for use in demanding and safety relevant applications e.g. in the Chemical, Oil & Gas and Energy industry. The thermometer fulfills the corresponding safety requirements due to various certificates and tests. The use of a transmitter leads to higher accuracy and reliability in comparison to directly wired sensors.

---

## Özellikler ve şartlar

---

### Thermometer

**Measuring principle**

Resistance Temperature Detector

---

**Characteristic / Application**

US style metrical  
modular temperature assembly  
for heavy duty applications  
suitable for hazardous areas  
to use with thermowell  
backlit display

---

**Thermowell / protection tube**

to be used with thermowell

---

**Insert / probe**

mineral insulated (MI), flexible

---

**Outer diameter protection tube / Insert**

Insert Diameter  
6,0 mm (0,24")

---

**Max. immersion length on request**

Not defined

---

**Material protection tube/ thermowell**

Not defined

---

**Optional coating**

Not defined

---

---

**Thermometer****Process connection**

Thermowell connection

male thread:

G1/2"

NPT1/2"

NPT3/4"

cap nut:

NPT1/2"

M24x1.5

---

**Tip shape**

Not defined

---

**Surface roughness Ra**

Not defined

---

**Operating temperature range**

PT 100:

-200 °C ...600 °C

(-328 °F ... 1.112 °F)

---

**Max. process pressure (static)**

at 20 °C: 500 bar (7.252 psi)

---

**Accuracy**

class A acc. to IEC 60751

class AA acc. to IEC 60751

---

**Response time**

depending on configuration

t<sub>50</sub> = 4 st<sub>90</sub> = 8 s

---

**Integration head transmitter**yes (4 ... 20 mA; HART; PROFIBUS PA; FOUNDATION  
FIELDBUS)

Thermometer

**Ex - approvals**

ATEX II

Explosion proof

---

**Certification**

Gost Metrology

Marine approval

---

Ayrıntılı bilgi [www.tr.endress.com/TMT162R](http://www.tr.endress.com/TMT162R)