

Radar measurement Time-of-Flight Micropilot FMR56

Economically efficient basis model for level measurement in solids



Daha fazla bilgi ve güncel fiyatlandırma:

www.tr.endress.com/FMR56

Avantajlar:

- Reliable measurement even for changing product and process conditions
- HistoROM data management concept for fast and easy commissioning, maintenance and diagnostics
- Highest reliability even in the presence of obstructions in the vessel due to new Multi-Echo Tracking evaluation
- Hardware and software developed according to IEC 61508 up to SIL3 (in homogeneous redundancy)
- Heartbeat Technology for a cost-effective and safe plant operation during the entire life cycle
- Seamless integration into control or asset management systems and intuitive, menu-guided operation concept (on-site or via the control system)
- World's easiest proof test concept for SIL and WHG saves time and cost

Özelliklere genel bakış

- **Accuracy** +/- 3 mm (0.12 in)
- **Process temperature** -40 °C...+80 °C (-40 °F...+176 °F)
- **Process pressure absolute / max. overpressure limit** Vacuum...3 bar (Vacuum...43.5 psi)
- **Max. measurement distance** 30 m (98 ft)
- **Main wetted parts** PP, UP

Uygulama alanı: Micropilot FMR56 is particularly designed for light-duty process conditions as they occur in silos or bins for solids. Micropilot free space radar is used for continuous, non-contact level measurement in

powdery to granular bulk solids. Dust, filling noises, temperature layers and gas layers do not affect the measurement.

Özellikler ve şartlar

Continuous / Solids

Measuring principle

Level radar solid

Characteristic / Application

For simple applications:

Reliable non-contact level measurements in silos or storage tanks for bulk solids

Specialities

Heartbeat Technology,

Bluetooth® commissioning,

Operation and maintenance SmartBlue App,

Safety and reliability with Multi- Echo Tracking,

HistoROM,

RFID TAG for easy identification,

Supply / Communication

2-wire (HART/ PROFIBUS PA/ FOUNDATION Fieldbus)

4-wire (HART)

Bluetooth® wireless technology and App (optional)

Frequency

K-band (~26 GHz)

Continuous / Solids**Antenna**

Horn DN80/3", PP plated

Horn DN100/4", PP plated

Accuracy+/- 3 mm (0.12 in)

Ambient temperature

-40 °C...+80 °C

(-40 °F...+176 °F)

Process temperature

-40 °C...+80 °C

(-40 °F...+176 °F)

Process pressure absolute / max. overpressure limit

Vacuum...3 bar

(Vacuum...43.5 psi)

Main wetted partsPP, UP

Process connection

Flange:

UNI DN80...DN150

(3"...6")

Mounting bracket

Max. measurement distance30 m (98 ft)

Continuous / Solids**Communication**

4...20 mA HART

PROFIBUS PA

FOUNDATION Fieldbus

Bluetooth® wireless technology

Certificates / Approvals

ATEX, FM, CSA, CSA C/US, IEC Ex, INMETRO, NEPSI, KC

Safety approvals

SIL

Options

Display,

Customized parameterization

Remote operation via SmartBlue App using Bluetooth®

Application limits

DK < 1.6

Reduction of the max. possible measuring range through:

Media with poor reflection properties

Angle of repose

Extremely loose surfaces of bulk solids, e.g. bulk solids with low bulk weight for pneumatic filling

Build-up, above all of moist products

Ayrıntılı bilgi www.tr.endress.com/FMR56