

Capacitance Point level detection Solicap FTI55

Point level detection for fine-grained to coarse-grained bulk solids



Avantajlar:

- Highest safety and reliability due to robust design for demanding process conditions
- Cost savings thanks to easy and fast commissioning as calibration is performed at the press of a button
- Universal application thanks to wide range of certificates and approvals
- Two-stage overvoltage protection against static discharges from the silo
- Active build-up compensation for bulk solids with caking tendency (under development)
- Increased safety due to permanent automatic monitoring of electronics
- Reduction in storage costs thanks to easy-to-shorten rod model (for partial insulation) and rope model (for partial and full insulation)

Daha fazla bilgi ve güncel fiyatlandırma:

www.tr.endress.com/FTI55

Özelliklere genel bakış

- **Process temperature** -50°C ... 180°C (-58°F ... 356°F)
- **Process pressure absolute / max. overpressure limit** Vacuum ... 25 bar (Vacuum ... 362 psi)

Uygulama alanı: Solicap FTI55 is a fully/partly insulated and robust rod probe for point level detection of fine-grained to coarse-grained bulk solids. It offers maximum reliability due to its active build-up compensation and is suited for a wide range of applications thanks to numerous certificates and approvals. Due to its robust construction, it can also be used to provide accurate measurements in applications with very high lateral loads up to 300Nm.

Özellikler ve şartlar

Point Level / Solids

Measuring principle

Capacitive Solid

Characteristic / Application

Fully / partly insulated rod probe for small-grain / large-grain bulk solids

Simple calibration

Suitable for abrasive media

Very robust probe

Specialities

Inactive length

Active build-up compensation

High lateral loading

Extremely robust probe

Supply / Communication

19 ... 253V AC

10 ... 55V DC-PNP

19...253V AC bzw 10...55V DC

8/16mA, 11 ... 36V DC

PFM

3-wire

Ambient temperature

-50°C ... 70°C

(-58°F ... 158°F)

Process temperature

-50°C ... 180°C

(-58°F ... 356°F)

Process pressure absolute / max. overpressure limit

Vacuum ... 25 bar

(Vacuum ... 362 psi)

Point Level / Solids**Main wetted parts**PE, PPS, 316L, Steel

Process connection

Thread R1 1/2, NPT1 1/2

Flanges from DN50.../ASME 2".../JIS...

Sensor length

0.2m ... 4m

(8" ... 157")

Inactive length: 0.1m ...1m

(2" ... 39")

Communication

2- wire 19-253 VAC

DC PNP

Relais DPDT

PFM

3-wire

8/16 mA

Certificates / ApprovalsATEX, FM, CSA, IEC Ex, JPN Ex, NEPSI

Safety approvalsSIL

Design approvalsEN 10204-3.1

Components

PFM: FTC325, FTC625, FTC470Z, FTC471Z

3-wire: FTC325

Application limitsDK min 2

Ayrıntılı bilgi www.tr.endress.com/FTI55