

# Proline Promass A 200 Coriolis flowmeter

Genuine loop-powered flowmeter for accurate measurement of lowest flow rates



Daha fazla bilgi ve güncel fiyatlandırma:

[www.tr.endress.com/8A2B](http://www.tr.endress.com/8A2B)

## Avantajlar:

- Space-saving installation – compact, lightweight sensor
- Highest product quality – self-drainable measuring tube design in all line sizes
- Optimum process safety – resistant to corrosive ambient conditions and internal clogging
- Convenient device wiring – separate connection compartment
- Safe operation – no need to open the device due to display with touch control, background lighting
- Integrated verification – Heartbeat Technology

## Özelliklere genel bakış

- **Max. measurement error** Mass flow (liquid):  $\pm 0.1\%$  Volume flow (liquid):  $\pm 0.1\%$  Mass flow (gas):  $\pm 0.35\%$  Density (liquid):  $\pm 0.0005 \text{ g/cm}^3$
- **Measuring range** 0 to 450 kg/h (0 to 16.54 lb/min)
- **Medium temperature range** -50 to 205 °C (-58 to 401 °F)
- **Max. process pressure** 430.9 bar (6250 psi)
- **Wetted materials** Measuring tube: stainless steel, 1.4435 (316/316L); Alloy C22

**Uygulama alanı:** The compact Promass A is ideal for continuous process control in demanding applications. Its unique self-drainable single-tube system enables accurate measurement of liquids and gases at lowest flow rates and high pressure. With its cost-effective genuine loop-powered technology and intrinsically safe design (Ex ia), Promass A 200 offers highest operational safety in hazardous areas. Heartbeat Technology ensures safe processes.

---

## Özellikler ve şartlar

---

Gas

**Measuring principle**

Coriolis

---

**Product headline**

Genuine loop-powered flowmeter for accurate measurement of lowest flow rates.

Suitable for applications with smallest flow quantities in the chemical industry.

---

**Sensor features**

Space-saving installation – compact, lightweight sensor. Highest product quality – self-drainable measuring tube design in all line sizes. Optimum process safety – resistant to corrosive ambient conditions and internal clogging.

Nominal diameter: DN 1 to 4 ( $\frac{1}{24}$  to  $\frac{1}{8}$ " ). Process pressure up to 430.9 bar (6250 psi). Medium temperature up to +205 °C (+401 °F).

---

**Transmitter features**

Convenient device wiring – separate connection compartment. Safe operation – no need to open the device due to display with touch control, background lighting. Integrated verification – Heartbeat Technology. Loop-powered technology. Robust dual-compartment housing. Plant safety: worldwide approvals (SIL, Haz. area).

---

**Nominal diameter range**

DN 1 to 4 ( $\frac{1}{24}$  to  $\frac{1}{8}$ " )

---

**Wetted materials**

Measuring tube: stainless steel, 1.4435 (316/316L); Alloy C22

---

**Measured variables**

Mass flow, density, temperature, volume flow, corrected volume flow, reference density

---

## Gas

**Max. measurement error**Mass flow (liquid):  $\pm 0.1$  %Volume flow (liquid):  $\pm 0.1$  %Mass flow (gas):  $\pm 0.35$  % Density (liquid):  $\pm 0.0005$  g/cm<sup>3</sup>**Measuring range**

0 to 450 kg/h (0 to 16.54 lb/min)

**Max. process pressure**

430.9 bar (6250 psi)

**Medium temperature range**

-50 to 205 °C (-58 to 401 °F)

**Ambient temperature range**

-40 to 60 °C (-40 to +140 °F)

**Sensor housing material**

Stainless steel, 1.4404 (316L)

**Transmitter housing material**

Stainless steel, CF-3M (316L, 1.4404)

AlSi10MG, coated

**Degree of protection**

IP66/67, Type 4X enclosure

**Display/Operation**

4-line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Remote display available

**Outputs**

4 - 20 mA HART (passive)

4 - 20 mA (passive)

Pulse/frequency/switch output (passive)

**Inputs**

None

---

**Gas****Digital communication**

HART, PROFIBUS PA, FOUNDATION Fieldbus

---

**Power supply**

DC 18 to 35 V (4 - 20 mA HART with/without pulse/frequency/switch)

DC 18 to 30 V (20 mA HART, 4 - 20 mA)

DC 9 to 32 V (PROFIBUS PA)

---

**Hazardous area approvals**

ATEX, IECEx, cCSAus, INMETRO, NEPSI, UK Ex

---

**Product safety**

CE, C-TICK

---

**Functional safety**

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

---

**Metrological approvals and certificates**

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

---

**Pressure approvals and certificates**

CRN

---

**Material certificates**

3.1 material

---

**Hygienic approvals and certificates**

3-A, cGMP

---

**Liquids****Measuring principle**

Coriolis

---

## Liquids

### Product headline

Genuine loop-powered flowmeter for accurate measurement of lowest flow rates.

Suitable for applications with smallest flow quantities in the chemical industry.

### Sensor features

Space-saving installation – compact, lightweight sensor. Highest product quality – self-drainable measuring tube design in all line sizes. Optimum process safety – resistant to corrosive ambient conditions and internal clogging.

Nominal diameter: DN 1 to 4 ( $\frac{1}{24}$  to  $\frac{1}{8}$ "). Process pressure up to 430.9 bar (6250 psi). Medium temperature up to +205 °C (+401 °F).

### Transmitter features

Convenient device wiring – separate connection compartment. Safe operation – no need to open the device due to display with touch control, background lighting. Integrated verification – Heartbeat Technology. Loop-powered technology. Robust dual-compartment housing. Plant safety: worldwide approvals (SIL, Haz. area).

### Nominal diameter range

DN 1 to 4 ( $\frac{1}{24}$  to  $\frac{1}{8}$ ")

### Wetted materials

Measuring tube: stainless steel, 1.4435 (316/316L); Alloy C22

### Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow, reference density

### Max. measurement error

Mass flow (liquid):  $\pm 0.1$  %

Volume flow (liquid):  $\pm 0.1$  %

Mass flow (gas):  $\pm 0.35$  % Density (liquid):  $\pm 0.0005$  g/cm<sup>3</sup>

### Measuring range

0 to 450 kg/h (0 to 16.54 lb/min)

---

## Liquids

**Max. process pressure**430.9 bar (6250 psi)

---

**Medium temperature range**-50 to 205 °C (-58 to 401 °F)

---

**Ambient temperature range**-40 to 60 °C (-40 to +140 °F)

---

**Sensor housing material**Stainless steel, 1.4404 (316L)

---

**Transmitter housing material**Stainless steel, CF-3M (316L, 1.4404)  
AlSi10MG, coated

---

**Degree of protection**IP66/67, Type 4X enclosure

---

**Display/Operation**4-line backlit display with touch control (operation from outside)  
Configuration via local display and operating tools possible  
Remote display available

---

**Outputs**4 - 20 mA HART (passive)  
4 - 20 mA (passive)  
Pulse/frequency/switch output (passive)

---

**Inputs**None

---

**Digital communication**HART, PROFIBUS PA, FOUNDATION Fieldbus

---

---

## Liquids

**Power supply**

DC 18 to 35 V (4 - 20 mA HART with/without pulse/frequency/switch)

DC 18 to 30 V (20 mA HART, 4 - 20 mA)

DC 9 to 32 V (PROFIBUS PA)

---

**Hazardous area approvals**

ATEX, IECEx, cCSAus, INMETRO, NEPSI, UK Ex

---

**Product safety**

CE, C-TICK

---

**Functional safety**

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

---

**Metrological approvals and certificates**

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

---

**Pressure approvals and certificates**

CRN

---

**Material certificates**

3.1 material

---

**Hygienic approvals and certificates**

3-A, cGMP

---

## Density/Concentration

**Measuring principle**

Coriolis

---

## Density/Concentration

### Product headline

Genuine loop-powered flowmeter for accurate measurement of lowest flow rates.

Suitable for applications with smallest flow quantities in the chemical industry.

### Sensor features

Space-saving installation – compact, lightweight sensor. Highest product quality – self-drainable measuring tube design in all line sizes. Optimum process safety – resistant to corrosive ambient conditions and internal clogging.

Nominal diameter: DN 1 to 4 ( $\frac{1}{24}$  to  $\frac{1}{8}$ "). Process pressure up to 430.9 bar (6250 psi). Medium temperature up to +205 °C (+401 °F).

### Transmitter features

Convenient device wiring – separate connection compartment. Safe operation – no need to open the device due to display with touch control, background lighting. Integrated verification – Heartbeat Technology. Loop-powered technology. Robust dual-compartment housing. Plant safety: worldwide approvals (SIL, Haz. area).

### Nominal diameter range

DN 1 to 4 ( $\frac{1}{24}$  to  $\frac{1}{8}$ ")

### Wetted materials

Measuring tube: stainless steel, 1.4435 (316/316L); Alloy C22

### Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow, reference density

### Max. measurement error

Mass flow (liquid):  $\pm 0.1$  %

Volume flow (liquid):  $\pm 0.1$  %

Mass flow (gas):  $\pm 0.35$  % Density (liquid):  $\pm 0.0005$  g/cm<sup>3</sup>

### Measuring range

0 to 450 kg/h (0 to 16.54 lb/min)



---

**Density/Concentration****Max. process pressure**430.9 bar (6250 psi)

---

**Medium temperature range**-50 to 205 °C (-58 to 401 °F)

---

**Ambient temperature range**-40 to 60 °C (-40 to +140 °F)

---

**Sensor housing material**Stainless steel, 1.4404 (316L)

---

**Transmitter housing material**

Stainless steel, CF-3M (316L, 1.4404)

AlSi10MG, coated

---

**Degree of protection**IP66/67, Type 4X enclosure

---

**Display/Operation**

4-line backlit display with touch control (operation from outside)

Configuration via local display and operating tools possible

Remote display available

---

**Outputs**

4 - 20 mA HART (passive)

4 - 20 mA (passive)

Pulse/frequency/switch output (passive)

---

**Inputs**None

---

**Digital communication**HART, PROFIBUS PA, FOUNDATION Fieldbus

---

## Density/Concentration

### Power supply

DC 18 to 35 V (4 - 20 mA HART with/without pulse/frequency/switch)

DC 18 to 30 V (20 mA HART, 4 - 20 mA)

DC 9 to 32 V (PROFIBUS PA)

---

### Hazardous area approvals

ATEX, IECEx, cCSAus, INMETRO, NEPSI, UK Ex

---

### Product safety

CE, C-TICK

---

### Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

---

### Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025)

Heartbeat Technology complies with the requirements for measurement traceability according to ISO 9001:2015 – Section 7.1.5.2 a (TÜV SÜD attestation)

---

### Pressure approvals and certificates

PED, CRN

---

### Material certificates

3.1 material

---

### Hygienic approvals and certificates

3-A, cGMP

---

Ayrıntılı bilgi [www.tr.endress.com/8A2B](http://www.tr.endress.com/8A2B)