

Conductive Point level detection Liquipoint FTW32

Rope probe for multipoint detection for up to 5 switch points



F L E X

Avantajlar:

- Cost-effective probe for conductive liquids with detection of up to five point levels with one probe
- No calibration required
- Standard setting for the most common conductive liquids
- No moving parts in the tank - long service life, reliable operation with no wear or blockages

Özelliklere genel bakış

- **Process temperature** -40 °C ... 70 °C (-40 °F ... 158 °F)
- **Process pressure absolute / max. overpressure limit** Vacuum ... 10 bar (Vacuum ... 145 psi)
- **Min. conductivity of medium** 10 µS/cm

Fiyatı en az **€100,00**

05.07.2022 tarihinden itibaren fiyat

Daha fazla bilgi ve güncel fiyatlandırma:

www.tr.endress.com/FTW32

Uygulama alanı: The Liquipoint FTW32 offers simple and safe point level detection in conductive liquids. It offers numerous measuring possibilities due to multipoint detection (up to 5 rods).

Özellikler ve şartlar

Point Level / Liquids

Measuring principle

Conductive

Characteristic / Application

Compact rope probe with multi point detection possible up to 5 switch points. Simple rope shortening possible

Point Level / Liquids**Supply / Communication**

DC PNP 10,8V ... 45V
Relay 20V ... 230V AC
Relay 20V ... 55V DC

Ambient temperature

-40 °C ... 70 °C
(-40 °F ... 158 °F)

Process temperature

-40 °C ... 70 °C
(-40 °F ... 158 °F)

Process pressure absolute / max. overpressure limit

Vacuum ... 10 bar
(Vacuum ... 145 psi)

Min. conductivity of medium

10 µS/cm

Main wetted parts

316L, FEP, PPS

Max. tensile strength

500 N

Process connection

G 1 1/2
NPT1 1/2"

Sensor length

0.25m ... 15m
(10" ... 590")

Communication

DC PNP
Relay

Point Level / Liquids

Certificates / Approvals

ATEX, EAC Ex

Safety approvals

Leakage Detection

Components

Transmitter: FTW325

Application limits

Observe min. medium conductivity

Ayrıntılı bilgi www.tr.endress.com/FTW32