

# TC13

## Modular TC thermometer

TC Thermometer, explosion-protected with thermowell and a variety of different flanges



Daha fazla bilgi ve güncel fiyatlandırma:

[www.tr.endress.com/TC13](http://www.tr.endress.com/TC13)

### Avantajlar:

- High degree of flexibility thanks to modular design with standard terminal heads as per DIN EN 50446 and customer-specific immersion lengths
- High degree of insert compatibility and design as per DIN 43772
- Extension neck to protect the head transmitter from overheating
- Fast response time with reduced/tapered tip form
- Types of protection for use in hazardous locations: Intrinsic safety (Ex ia), non-sparking (Ex nA)
- Head transmitter with easy selection: Analog output 4 to 20 mA, HART®, PROFIBUS® PA or FOUNDATION Fieldbus™

### Özelliklere genel bakış

- **Accuracy** class 1 acc. to IEC 60584
- **Response time** depending on configuration  $t_{50} = 6$  s  $t_{90} = 13$  s
- **Max. process pressure (static)** at 20 °C: 50 bar (725 psi)
- **Operating temperature range** Type K: -40 °C ... 1.100 °C (-40 °F ... 2.012 °F) Type J: -40 °C ... 750 °C (-40 °F ... 1.382 °F)
- **Max. immersion length on request** up to 10.000,00 mm (393,70")

**Uygulama alanı:** The high modular and robust thermometer finds its use in several applications in almost all industries. An optional head transmitter, with all common communication protocols, makes the device ready to use with enhanced measurement accuracy and reliability compared to directly wired sensors. A variety of process connections, dimensions and materials offer flexible application possibilities.

### Özellikler ve şartlar

## Thermometer

**Measuring principle**

Thermocouple

**Characteristic / Application**

metric style

modular temperature assembly

universal range of application

suitable for hazardous areas

flanged process connection

without neck

incl. thermowell / protection tube (metal)

**Thermowell / protection tube**

welded protection tube

**Insert / probe**

mineral insulated (MI), flexible

**Outer diameter protection tube / Insert**

9,0 mm (0,35")

11,0 mm (0,43")

12,0 mm (0,47")

**Max. immersion length on request**

up to 10.000,00 mm (393,70")

## Thermometer

**Material protection tube/ thermowell**

1.4404 (316L)

1.4571 (316Ti)

Alloy 600 (2.4816)

Alloy C276 (2.4819)

**Optional coating**

Not defined

**Process connection**

flange:

DN25 PN40 B1 (EN1092)

DN40 PN40 B1(EN1092)

DN50 PN40 B1 (EN1092)

ASME 1" 150 RF (B16.5)

ASME 1" 300 RF (B16.5)

**Tip shape**

straight

reduced

tapered

**Surface roughness Ra**

0,8 µm (31,5 µin.)

## Thermometer

**Operating temperature range**

Type K:

-40 °C ... 1.100 °C

(-40 °F ...2.012 °F)

Type J:

-40 °C ...750 °C

(-40 °F ...1.382 °F)

---

**Max. process pressure (static)**at 20 °C: 50 bar (725 psi)

---

**Accuracy**class 1 acc. to IEC 60584

---

**Response time**

depending on configuration

t50 = 6 s

t90 = 13 s

---

**Integration head transmitter**yes (4 ... 20 mA; HART; PROFIBUS PA; FOUNDATION  
FIELDBUS)

---

Thermometer

**Ex - approvals**

ATEX II

ATEX IECEX

NEPSI

IECEX Ex

EAC Ex

---

**Certification**

Gost Metrology

SIL (transmitter only)

---

Ayrıntılı bilgi [www.tr.endress.com/TC13](http://www.tr.endress.com/TC13)