

TC65

Explosion-proof thermocouple thermometer

Safe monitoring of process temperatures in challenging applications e. g. in the Oil & Gas industry



Daha fazla bilgi ve güncel fiyatlandırma:

www.tr.endress.com/TC65

Avantajlar:

- Types of protection for use in hazardous locations: Intrinsic safety (Ex ia), flameproof (Ex d), non-sparking (Ex nA)
- High degree of insert compatibility and design as per DIN 43772
- High degree of flexibility thanks to modular design with standard terminal heads as per DIN EN 50446 and customer-specific immersion lengths
- For plug-in/screw-in with sliding compression fitting

Özelliklere genel bakış

- **Accuracy** class 1 acc. to IEC 60584
- **Response time** depending on configuration $t_{50} = 3$ s $t_{90} = 7$ s
- **Max. process pressure (static)** at 20 °C: 80 bar (1,160 psi)
- **Operating temperature range** Type K: -40 °C ...1.100 °C (-40 °F ...2.012 °F) Type J: -200 °C ...750 °C (-328 °F ...1.382 °F)
- **Max. immersion length on request** up to 30.000,00 mm (1.181,10")

Uygulama alanı: The robust thermometer is designed for use in demanding and safety relevant applications e.g. in the Chemical, Oil & Gas and Energy industry. An optional head transmitter with all common communication protocols makes the device ready to use with enhanced measurement accuracy and reliability compared to directly wired sensors. The sensor may be used direct contact without thermowell or where the application requires it, spring load inside of a separate thermowell. Flexible configuration possible.

Özellikler ve şartlar

Thermometer

Measuring principle

Thermocouple

Characteristic / Application

metric style

modular temperature assembly

for heavy duty applications

suitable for hazardous areas

threaded process connection

without neck

Thermowell / protection tube

without (not intended to use with thermowell)

Insert / probe

mineral insulated (MI), flexible

Outer diameter protection tube / Insert

3,0 mm (0,12")

6,0 mm (0,24")

Max. immersion length on request

up to 30.000,00 mm (1.181,10")

Material protection tube/ thermowell

1.4404 (316L)

Alloy 600 (2.4816)

Thermometer

Process connection

male thread:

NPT1/2"

NPT3/4"

compression fitting:

NPT1/2"

NPT3/4"

Tip shape

straight

tapered

Operating temperature range

Type K:

-40 °C ...1.100 °C

(-40 °F ...2.012 °F)

Type J:

-200 °C ...750 °C

(-328 °F ...1.382 °F)

Max. process pressure (static)

at 20 °C: 80 bar (1,160 psi)

Accuracy

class 1 acc. to IEC 60584

Thermometer

Response time

depending on configuration

t50 = 3 s

t90 = 7 s

Integration head transmitter

yes (4 ... 20 mA; HART; PROFIBUS PA; FOUNDATION
FIELDBUS)

Ex - approvals

ATEX II

IECEX

NEPSI

EAC Ex

Explosion proof

Certification

Gost Metrology

SIL (transmitter only)

Ayrıntılı bilgi www.tr.endress.com/TC65