

Promass 80P



More information and current pricing:

www.uk.endress.com/80P

Benefits:

- Highest process quality – fully compliant to industry requirements
- Fewer process measuring points – multivariable measurement (flow, density, temperature)
- Space-saving installation – no in/outlet run needs
- Cost-effective – dedicated design for standard applications
- Safe operation – display provides easy readable process information
- Fully industry compliant – IEC/EN/NAMUR

Specs at a glance

- **Max. measurement error** Mass flow (liquid): $\pm 0.15\%$ Volume flow (liquid): $\pm 0.15\%$ Mass flow (gas): $\pm 0.5\%$ Density (liquid): $\pm 0.0005 \text{ g/cm}^3$
- **Measuring range** 0 to 70 000 kg/h (0 to 2570 lb/min)
- **Medium temperature range** -50 to $+200 \text{ }^\circ\text{C}$ (-58 to $+392 \text{ }^\circ\text{F}$)
- **Max. process pressure** PN 63, Class 300, 40K
- **Wetted materials** Measuring tube: 1.4435 (316L) Connection: 1.4435 (316L); 1.4404 (316/316L)

Field of application: Promass P offers the enhanced performance of a bent tube meter and the drainability of a straight tube meter without any compromise, between accuracy and drainability. Combined with the proven Promass 80 transmitter with push buttons, Promass 80P offers a cost effective solution for applications in sterile environments in the life sciences industry.

Features and specifications

Density

Measuring principle

Coriolis

Density

Characteristic / Application

Coriolis mass flowmeter complying with ASME BPE, ISPE, FDA, 3-A

Ambient temperature

-20...+65°C
(-4...+140°F)

Process temperature

-50...+200°C
(-58...+392°F)

Process pressure absolute

PN 16...40
CI 150...300
JIS 20...40K

Wetted parts

316L/1.4435

Output

4...20mA
Pulse/Frequency
Status

Certificates / Approvals

ATEX
FM
CSA IECEx TIIS NEPSI

Density/Concentration

Measuring principle

Coriolis

Product headline

The specialist for life sciences with a compact or remote transmitter. Dedicated for applications under sterile conditions in the life sciences industry.

Density/Concentration

Sensor features

Highest process quality – fully compliant to industry requirements. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space - saving installation – no in/outlet run needs. ASME BPE, 3-A and EHEDG conform & low delta ferrite. Electropolished measuring tube in 1.4435 (316L).

Transmitter features

Cost - effective – dedicated design for standard applications. Safe operation – display provides easy readable process information. Fully industry compliant – IEC/EN/NAMUR. 2 - line backlit display with push buttons. Device in compact or remote version.

Nominal diameter range

DN 8 to 50 ($\frac{3}{8}$ to 2")

Wetted materials

Measuring tube: 1.4435 (316L)

Connection: 1.4435 (316L); 1.4404 (316/316L)

Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow, reference density

Max. measurement error

Mass flow (liquid): ± 0.15 %

Volume flow (liquid): ± 0.15 %

Mass flow (gas): ± 0.5 %

Density (liquid): ± 0.0005 g/cm³

Measuring range

0 to 70 000 kg/h (0 to 2570 lb/min)

Max. process pressure

PN 63, Class 300, 40K

Medium temperature range

-50 to +200 °C (-58 to +392 °F)

Density/Concentration**Ambient temperature range**

Standard: -20 to +60 °C (-4 to +140 °F)

Option: -40 to +60 °C (-40 to +140 °F)

Sensor housing material1.4301 (304), corrosion resistant

Transmitter housing material

Powder - coated die - cast aluminium

1.4301 (304), sheet

CF3M (316L), cast

Degree of protectionIP67, type 4X enclosure. Remote transmitter: IP67, type 4X enclosure

Display/Operation

2 - line backlit display with push buttons

Configuration via local display and operating tools possible

Outputs

3 outputs:

0 - 20 mA (active)/4 - 20 mA (active/passive)

Pulse/frequency/switch output (passive)

InputsStatus input

Digital communication

HART

PROFIBUS PA

Power supply

DC 16 to 62 V

AC 85 to 260 V (45 to 65 Hz)

AC 20 to 55 V (45 to 65 Hz)

Hazardous area approvalsATEX, IECEx, FM, CSA, NEPSI

Density/Concentration**Product safety**

CE, C-tick, EAC marking

Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025), NAMUR

Pressure approvals and certificates

PED, CRN

Material certificates

3.1 material

Hygienic approvals and certificates

3-A, FDA, ASME BPE, ISPE

Gas**Measuring principle**

Coriolis

Product headline

The specialist for life sciences with a compact or remote transmitter. Dedicated for applications under sterile conditions in the life sciences industry.

Sensor features

Highest process quality – fully compliant to industry requirements. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space - saving installation – no in/outlet run needs. ASME BPE, 3-A and EHEDG conform & low delta ferrite. Electropolished measuring tube in 1.4435 (316L).

Gas

Transmitter features

Cost - effective – dedicated design for standard applications. Safe operation – display provides easy readable process information. Fully industry compliant – IEC/EN/NAMUR. 2 - line backlit display with push buttons. Device in compact or remote version.

Nominal diameter range

DN 8 to 50 ($\frac{3}{8}$ to 2")

Wetted materials

Measuring tube: 1.4435 (316L)

Connection: 1.4435 (316L); 1.4404 (316/316L)

Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow, reference density

Max. measurement error

Mass flow (liquid): ± 0.15 %

Volume flow (liquid): ± 0.15 %

Mass flow (gas): ± 0.5 %

Density (liquid): ± 0.0005 g/cm³

Measuring range

0 to 70 000 kg/h (0 to 2570 lb/min)

Max. process pressure

PN 63, Class 300, 40K

Medium temperature range

-50 to +200 °C (-58 to +392 °F)

Ambient temperature range

Standard: -20 to +60 °C (-4 to +140 °F)

Option: -40 to +60 °C (-40 to +140 °F)

Sensor housing material

1.4301 (304), corrosion resistant

Gas

Transmitter housing material

Powder - coated die - cast aluminium
1.4301 (304), sheet
CF3M (316L), cast

Degree of protection

IP67, type 4X enclosure. Remote transmitter: IP67, type 4X enclosure

Display/Operation

2 - line backlit display with push buttons
Configuration via local display and operating tools possible

Outputs

3 outputs:
0 - 20 mA (active)/4 - 20 mA (active/passive)
Pulse/frequency/switch output (passive)

Inputs

Status input

Digital communication

HART
PROFIBUS PA

Power supply

DC 16 to 62 V
AC 85 to 260 V (45 to 65 Hz)
AC 20 to 55 V (45 to 65 Hz)

Hazardous area approvals

ATEX, IECEX, FM, CSA, NEPSI

Other approvals and certificates

3.1 material, calibration performed on accredited calibration facilities
(acc. to ISO/IEC 17025), NAMUR, SIL
PED, CRN
3-A, FDA, ASME BPE, ISPE

Gas**Product safety**

CE, C-tick, EAC marking

Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025), NAMUR

Pressure approvals and certificates

PED, CRN

Material certificates

3.1 material

Hygienic approvals and certificates

3-A, FDA, ASME BPE, ISPE

Liquids**Measuring principle**

Coriolis

Product headline

The specialist for life sciences with a compact or remote transmitter. Dedicated for applications under sterile conditions in the life sciences industry.

Sensor features

Highest process quality – fully compliant to industry requirements. Fewer process measuring points – multivariable measurement (flow, density, temperature). Space - saving installation – no in/outlet run needs. ASME BPE, 3-A and EHEDG conform & low delta ferrite. Electropolished measuring tube in 1.4435 (316L).

Liquids

Transmitter features

Cost - effective – dedicated design for standard applications. Safe operation – display provides easy readable process information. Fully industry compliant – IEC/EN/NAMUR. 2 - line backlit display with push buttons. Device in compact or remote version.

Nominal diameter range

DN 8 to 50 ($\frac{3}{8}$ to 2")

Wetted materials

Measuring tube: 1.4435 (316L)

Connection: 1.4435 (316L); 1.4404 (316/316L)

Measured variables

Mass flow, density, temperature, volume flow, corrected volume flow, reference density

Max. measurement error

Mass flow (liquid): ± 0.15 %

Volume flow (liquid): ± 0.15 %

Mass flow (gas): ± 0.5 %

Density (liquid): ± 0.0005 g/cm³

Measuring range

0 to 70 000 kg/h (0 to 2570 lb/min)

Max. process pressure

PN 63, Class 300, 40K

Medium temperature range

-50 to +200 °C (-58 to +392 °F)

Ambient temperature range

Standard: -20 to +60 °C (-4 to +140 °F)

Option: -40 to +60 °C (-40 to +140 °F)

Sensor housing material

1.4301 (304), corrosion resistant

Liquids

Transmitter housing material

Powder - coated die - cast aluminium
1.4301 (304), sheet
CF3M (316L), cast

Degree of protection

IP67, type 4X enclosure. Remote transmitter: IP67, type 4X enclosure

Display/Operation

2 - line backlit display with push buttons
Configuration via local display and operating tools possible

Outputs

3 outputs:
0 - 20 mA (active)/4 - 20 mA (active/passive)
Pulse/frequency/switch output (passive)

Inputs

Status input

Digital communication

HART
PROFIBUS PA

Power supply

DC 16 to 62 V
AC 85 to 260 V (45 to 65 Hz)
AC 20 to 55 V (45 to 65 Hz)

Hazardous area approvals

ATEX, IECEX, FM, CSA, NEPSI

Other approvals and certificates

3.1 material, calibration performed on accredited calibration facilities
(acc. to ISO/IEC 17025), NAMUR, SIL
PED, CRN
3-A, FDA, ASME BPE, ISPE

Liquids

Product safety

CE, C-tick, EAC marking

Functional safety

Functional safety according to IEC 61508, applicable in safety-relevant applications in accordance with IEC 61511

Metrological approvals and certificates

Calibration performed on accredited calibration facilities (acc. to ISO/IEC 17025), NAMUR

Pressure approvals and certificates

PED, CRN

Material certificates

3.1 material

Hygienic approvals and certificates

3-A, FDA, ASME BPE, ISPE

More information www.uk.endress.com/80P